



PAR38 LED Single Optic Lamps with AirFlux Technology

19PAR38/F25 2700 DIM AF SO 6/1

Philips PAR38 LED Single Optic Lamps with AirFlux Technology improves shopping experience with superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

Product data

• General Characteristics

Cap-Base	E26
Bulb	PAR38 [PAR38 mm]
Rated Avg. Life (Hours)	50000 hr

• Light Technical Characteristics

Color Code	WW
Color Designation	Warm White
Beam Angle	25 D
Beam Description	25D [Medium beam]
Correlated Color Temperature	2700 K
Approximate Lumens	1200 Lm
Approx. MBCP	6800 cd
CRI	80
Luminous Efficacy Lamp	63.16 Lm/W
Color Temp. (Kelvin)	2700 K [CCT 2700K]
Rated Luminous Flux	1200 Lm

• Electrical Characteristics

Wattage	19 W
Wattage Technical	19 W
Voltage	120 V
Line Frequency	60 Hz

Power Factor	0.9 -
Lamp Current mA	182 mA
Dimmable	Yes
Wattage Equivalent	100 W
Starting Time	0.5 s

• Measuring Conditions

Switching cycle	20000X
-----------------	--------

• Product Dimensions

Overall Length C	130 mm
Diameter D	120 mm

• Product Data

Product number	429084
Full product name	19PAR38/F25 2700 DIM AF SO 6/1
Short product name	19PAR38/F25 2700 DIM AF RO 6/1
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677429089
Bar code on case	50046677429084
Logistics code(s)	929000246904
eop_net_weight_pp	0.370 kg

- Not for use in totally enclosed luminaires.

Warnings and Safety


- Suitable for use in damp locations.



PHILIPS

PAR38 LED Single Optic Lamps with AirFlux Technology

Dimensional drawing



E26

19PAR38/F25 2700 DIM AF SO 6/1

Product	C (Norm)	C1 (Max)	D (Norm)	D1 (Norm)
LED 19W E26 2700K PAR38 25D DIM	130	-	120	-



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, April 8
data subject to change