




HDC | HDC HE

TE Internal #: T2059482101-000

Rectangular Contact Inserts, HE, Pin, 48, Crimp Terminal, 48  
Position, 26 – 12 AWG Wire Size, .14 – 4 mm<sup>2</sup> Wire Size, Power &  
Signal, HDC HE

[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **HE**

Contact Type: **Pin**

Contact Insert Pole Configuration: **48**

Termination Method to Wire & Cable: **Crimp Terminal**

Number of Positions: **48**

**Features**

**Product Type Features**

Product Type	Insert
Rectangular Connector Insert Type	HE
Sealable	No

**Configuration Features**

Number of Positions	48
---------------------	----

**Contact Features**

Contact Type	Pin
Contact Insert Pole Configuration	48

**Termination Features**

Termination Method to Wire & Cable	Crimp Terminal
------------------------------------	----------------

**Dimensions**

Wire Size	.14 – 4 mm <sup>2</sup>
-----------	-------------------------

**Operation/Application**

--	--

Circuit Application

Power &amp; Signal

## Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)  
Candidate List Declared Against: JUNE 2022 (224)  
Does not contain REACH SVHC

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # T1010241200-000  
H24B-KDTP



TE Part # T1210160132-000  
H16B-TS-M32





TE Part # T2059482201-000  
HEEE-048-F



TE Part # T3609320102-000  
DLX-32-M



## Also in the Series | HDC HE



## Documents

### Product Drawings

[HEEE-048-M](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_T2059482101-000\\_B.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T2059482101-000\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T2059482101-000\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[HEAVY DUTY CONNECTORS](#)

English

### Product Specifications

[Application Specification](#)

English

T2059482101-000

Rectangular Contact Inserts, HE, Pin, 48, Crimp Terminal, 48 Position, 26 – 12 AWG  
Wire Size, .14 – 4 mm<sup>2</sup> Wire Size, Power & Signal, HDC HE

