



Red Devil
RED DEVIL EQUIPMENT CO.

**MANUFACTURED
IN MINNESOTA**

Red Devil Equipment Company
14900 21st Avenue North
Plymouth, Minnesota 55447
www.reddevilequipment.com

Toll-free 800-221-1083
Intl 763-533-2969
Fax 763-852-1811
info@reddevilequipment.com





1400/1410 Classic Shakers

- Shakes a variety of containers of all sizes and shapes (including odd sized or dented containers) ranging from 3½" to 11" in height
- Suitable for a wide range of mixing applications
- 18 lb standard load capacity
- Features a heavy-duty clamp assembly and full safety enclosure
- Limit switch stops cycle when safety enclosure is opened
- Counter or Pedestal Base also required for use

Speed Demon 5™

- Dual-Axis vortex mixing motion
- Extremely quiet operation for use on the sales floor
- Smallest five gallon vortex mixer in the market
- Low lift height for easy loading and unloading
- Optional one gallon adapter is also available for mixing gallon containers



Explosion-Proof

Red Devil Equipment offers a full-line of explosion-proof mixing equipment that is rated for classified mixing environments and complies with UL/CSA/ETL safety requirements and regulations. Available explosion-proof models include:

- 1400 Classic Twin-Arm Shaker
- 1400/1410 Classic Air-Driven Shaker
- 1025 Red D Mix Gyroscopic Mixer
- 5025 Red D Mix Gyroscopic Mixer
- Speed Demon 5 Vortex Mixer



1025 Red D Mix™

- Thorough gyroscopic mixing action for one gallon containers
- Includes adapter for mixing quarts and containers ranging from 4¾ to 6¼"
- Gear drive design eliminates the replacement of belts, pulleys and friction drives
- One-step clamping system for easy set-up every time
- 25 lb standard load capacity
- Optional Base is available for placement at counter height

5025 Red D Mix™

- Exceptional gyroscopic mixing motion for five gallon containers
- Heavy-duty 125 lb standard load capacity
- Built-in roller assists with loading and unloading
- Gear drive design eliminates the replacement of belts, pulleys and friction drives
- One-step clamping system for quick loading
- Riser leg kits are also available to match dispenser height and roller rack



5925 DynoMix™

- Gyroscopic mixing action turns containers end-over-end while simultaneously spinning
- Adjustable legs for flexible load height and equipment alignment
- Accepts containers from one gallon to five gallons
- Double roller for easy loading and unloading
- 100 lb standard load capacity
- Automatic stop-lock feature positions containers upright after each mixing cycle



Agitar™

- Designed for high volume, commercial production & heavy duty environments
- Patented intelligent clamping system automatically adjusts for a variety of container sizes
- Mixes pints up to five gallon containers, including cases
- Industrial grade strut & spring composition absorbs vibration for a long life of mixing
- Minimal vibration during operation
- Built-in roller assists with container movement
- Kevlar reinforced drive belt prevents stretching and slippage
- Built-in wheels for easy placement

XVL-55

- Designed for high volume consumer locations
- Patented intelligent clamping system automatically adjusts for container size
- Built-in roller assists with loading and unloading
- Increased longevity with Kevlar reinforced drive belt
- Extends mixing life with industrial grade strut & spring composition



Model 5000

- Designed for medium traffic retail outlets
- Accepts pints up to five gallon containers, including cases
- Rubber cushioned bearings absorb vibration and extend life
- Innovative counterweight design reduces stress
- Large viewing window
- Kevlar reinforced drive belt to assist belt from stretching and gear slippage

**NEW
IN 2012**



Speed Demon 1™

- Features digital display timer
- Ideal for heavy volume, continuous use environments
- Quiet operation placement in a sales area without interrupting customer interaction
- Easy drop-in loading
- Utilizes gear drive system, ensuring superior repeatability and reliability
- Built with industrial grade cast-iron components for an extensive mixing life
- All welded exterior enclosure
- Includes quart & pint adapter for versatility
- Optional Base is available to stack two mixers in the space of one

XVL-10

- Easy to use push button timer
- Ideal for mixing all types of architectural paints and primers
- Mixes round one gallon, quart & pint containers
- Quiet operation for minimal interruption
- Easy drop-in loading for gallons – no need for latches
- Smallest footprint of any one gallon mixer on the market – allows unit to fit under or on top of a countertop surface
- Kevlar reinforced drive belt prevents stretching and slippage




Model 1000

- Versatile manual timer
- Ideal for mixing all types of architectural paints and primers
- Mixes round one gallon, quart & pint containers
- Quiet operation for minimal interruption
- Easy drop-in loading – no need for latches
- Kevlar reinforced drive belt prevents stretching and gear slippage



Production Systems



No matter the size or configuration of your operation, we can work with you to develop a mock layout based on your product flow, tint area, facility size, sales volume and customer interaction.

Please call us at 800-221-1083 for additional information.

Drying Systems



3100-PB
Dry-N-View



4050
Dryer Box



A3525
Draw Down Drying Tower

Draw Down Accessories



Draw Down Bar
Draw Down Cards
Draw Down Glass Plate

Accessories



A3522
Magnetic Mallet Holder



5070-00
Five-Gallon Lid Press



5080-04
Lid Press with Base Plate

