

WATER-RESISTANT FIRE-SAFE®

OA5848



PROTECTION FEATURES:

- UL Classified Fire Endurance (2 hour at 1850°F)
 - Protects documents, records and valuables against catastrophic loss
- Impact: UL Classified 30 foot Drop Test
 - Contents remain intact and locked upon impact
- ETL verified for 2 hour fire protection of CDs, DVDs, Memory Sticks and USB Drives up to 1850°F
- ETL verified for water-resistance

SECURITY FEATURES:

- Advanced LCD electronic lock system with backlit keypad, programmable PIN access and tubular key lock
 - allows up to (7) users: (1) manager with program override capability and (6) additional users
 - each user has an individual PIN
 - PINS may be created using 4-8 digits
 - 5 digit factory access code setting when shipped
- 7 live-locking bolts
- Bolt-down hardware included

INTERIOR FEATURES:

- Multi-position drawer and file rack
- Door pocket, key rack and compartment for small items

EXTERIOR FEATURES:

- Metal handle

Dimensions (H x W x D)	Capacity	Ship. Weight
Exterior 23.8" x 18.6" x 19.3" 60.3 cm x 47.2 cm x 49.1 cm	2.0 cu. ft. 57 liters	206 lbs. 93 kg
Interior 19.5" x 14.8" x 11.9" 49.9 cm x 37.6 cm x 30.2 cm		

USA MADE UNSURPASSED PROTECTIVE STORAGE SINCE 1930