

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : CH126

Chlorhexidine Gluconate Solution, BP

CAS# :

Formula : C₂₂H₃₀Cl₂N₁₀·2C₆H₁₂O₇

Formula Weight : FW 897.77

| Test | Limit | |
|---|------------------|------|
| | Min. | Max. |
| ASSAY(C ₂₂ H ₃₀ Cl ₂ N ₁₀ ·2C ₆ H ₁₂ O ₇ ;w/v) | 19.0 - 21.0% | |
| pH of a 20-fold dilution | 5.5 - 7.0 | |
| RELATIVE DENSITY | 1.06 - 1.07 G/ML | |
| RELATED SUBSTANCES | TO PASS TEST | |
| CHLOROANILINE | TO PASS TEST | |
| IDENTIFICATION | TO PASS TEST | |
| EXPIRATION DATE | | |
| RESIDUAL SOLVENTS | TO PASS TEST | |