

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : P1177

Polysorbate 20, FCC

CAS# : 9005-64-5

Test

Limit
Min. Max.

Test	Limit
	Min. Max.
ASSAY (ANHYDROUS BASIS)	70.0 - 74.0 %
HYDROXYL VALUE	96 - 108
LAURIC ACID	15 - 17 g/100 g
SAPONIFICATION VALUE	40 - 50
ACID VALUE	-- 2
1,4-DIOXANE	-- 10 MG/KG
LEAD (Pb)	-- 2 MG/KG
RESIDUE ON IGNITION	-- 0.25 %
WATER	-- 3.0 %
IDENTIFICATION	--TO PASS TEST
EXPIRATION DATE	