

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : P1179

Polysorbate 80, FCC

CAS# : 9005-65-6

Test	Limit	
	Min.	Max.
ASSAY (DRIED BASIS)	65.0 - 69.5 %	
HYDROXYL VALUE	65 - 80	
OLEIC ACID	22 - 24 g/100 g	
SAPONIFICATION VALUE	45 - 55	
ACID VALUE	-- 2	
1,4-DIOXANE	--	10 MG/KG
LEAD (Pb)	--	2 MG/KG
RESIDUE ON IGNITION	--	0.25 %
WATER	--	3.0 %
IDENTIFICATION	--TO PASS TEST	
RETEST DATE		
CERTIFIED KOSHER		