

T4112002041-000 ✓ ACTIVE



## M12 Connector

TE Internal #: T4112002041-000

Standard Circular Connectors, Wire-to-Wire, 4 Position, Sealable, Wire & Cable, Signal, PBT, A Polarization Code, Polyamide 66 GF25, M12 Connector

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > M12 Field Installable Unshielded



Connector System: **Wire-to-Wire**

Number of Positions: **4**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **4 A**

[All M12 Field Installable Unshielded \(102\)](#)

## Features

### Product Type Features

Prewired	No
Product Type	Connector
Accessory Color	Black
Assembly Type	Electrical Connector
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Plastic

### Configuration Features

Factory Installed Backshell	No
Keying	A
Number of Positions	4



Number of Power Positions	0
Number of Signal Positions	4
Contacts Preloaded	Yes

### Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

### Body Features

Peripheral Seal Material	Silicone
Environmental Protection	IP67
O-Ring Material	Silicone
Environmental Protection Type	Elastomer Sealed
Shell Base Material	PBT
Circular Connector Insulation Material Type	Polyamide 66 GF25

### Contact Features

Contact Current Rating (Max)	4 A
Reverse Gender	No
Circular Connector Contact Type	Socket

### Mechanical Attachment

Mating Retention Type	Threaded Coupling
Mating Alignment	With
Polarization Code	A
Mating Alignment Type	Keyed

### Housing Features

Circular Connector Shell Size	20
-------------------------------	----

### Dimensions

Wire Size	.82 – .2 mm <sup>2</sup>
-----------	--------------------------

### Usage Conditions

IP Dust Sealing Level	6
IP Water Sealing Level	IP67
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]

### Operation/Application

Durability Rating	100 Cycles
-------------------	------------



## Circuit Application

## Signal

Shielded

No

## Industry Standards

UL Flammability Rating

UL 94HB

## Packaging Features

Packaging Quantity

1

## Other

Field Serviceable

Yes

## Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

SVHC &gt; Threshold:

Pb (4% in Component Part)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl &gt; 900 ppm.

Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # T4113002041-000  
M12,MALE,RA,A CODE,4P,PG9,GOLD



TE Part # 225252-E  
M12 M 4 A L90H T \* 301 \* 188 \* \* \* \* 000



TE Part # 225255-E  
M12 M 4 A L90H T \* 301 \* 188 \* Y \* \* 000



TE Part # 235221-E  
M12 M 4 UNI L90H T \* 301 \* 188 \* \* \* Y 9



TE Part # 235265-E  
M12 M 4 A L90F T \* 301 \* 188 \* \* Y SNI 0



TE Part # 254188-E  
M12 M 4 A H S \* 201 17,0 094 \* \* \* \* 001



TE Part # 284809-E  
M12 M 4 A \* S \* S \* 201 10,5 094 \* \* \* ODV 9



TE Part # 364781-E  
M12 M 4 A \* T 3,1 301 10,5 094 \* \* \* 999



TE Part # 384812-E  
M12 M 4 A \* T 3,1 301 10,5 094 \* \* \* 999



TE Part # 454829-E  
M12 M 4 A H S \* 201 17,0 094 \* \* \* \* 000



TE Part # 474329-E  
M12 M 4 A \* S \* S \* 201 10,5 094 \* \* \* OKV8



TE Part # 484790-E  
M12 M 4 A \* S \* S \* 201 10,5 094 \* \* \* ODV 9




TE Part # 494167-E  
M12 M 4 A \* S \* S \* 201 10,5 094 \* \* Y-VG OD



TE Part # 534073-E  
M12 M 4 A \* S \* S \* 201 10,5 094 \* \* Y-VG OD

Also in the Series | **M12 Connector**



M8/M12 Cable Assemblies(230)



Standard Circular Connectors(519)

Documents



### Product Drawings

[M12,FEMALE,RA,A CODE,4P,PG9,GOLD](#)

English

---

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_T4112002041-000\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T4112002041-000\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_T4112002041-000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[M8 / M12 Connector System Catalog](#)

English

---

### Product Specifications

[Application Specification](#)

English