

SAFETY DATA SHEET

PASSIVATION TESTER REAGENT

Section 1. Identification

GHS product identifier : PASSIVATION TESTER REAGENT
Product code : 54-A 050
SDS no. : S-08E
Product type : Liquid.

Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Solution to distinguish stainless steel passivation degree (use with passivation tester).

Manufacturer : Walter Surface Technologies Inc.
 810 Day Hill Road
 Windsor, CT 06095
 United States
 General Information: 1-866-592-5837
 info.us@walter.com
 www.walter.com

Emergency telephone number (with hours of operation) : INFOTRAC® 1-800-535-5053. International call collect: 1-352-323-3500
 24 hours/day, 7 days/week.

Section 2. Hazards identification

OSHA/HCS status : This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Classification of the substance or mixture : SKIN CORROSION/IRRITATION - Category 1
 SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 1

GHS label elements

Hazard pictograms :



Signal word : Danger

Hazard statements : H314 - Causes severe skin burns and eye damage.

Precautionary statements

Prevention : P280 - Wear protective gloves. Wear eye or face protection. Wear protective clothing.
 P264 - Wash hands thoroughly after handling.

Response : P304 + P340 + P310 - IF INHALED: Remove person to fresh air and keep comfortable for breathing. Immediately call a POISON CENTER or physician.
 P301 + P310 + P330 + P331 - IF SWALLOWED: Immediately call a POISON CENTER or physician. Rinse mouth. Do NOT induce vomiting.
 P303 + P361 + P353 + P363 + P310 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower. Wash contaminated clothing before reuse. Immediately call a POISON CENTER or physician.
 P305 + P351 + P338 + P310 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or physician.

Section 2. Hazards identification

- Storage** : P405 - Store locked up.
- Disposal** : P501 - Dispose of contents and container in accordance with all local, regional, national and international regulations.
- Hazards not otherwise classified** : None known.

Section 3. Composition/information on ingredients

- Substance/mixture** : Mixture
- Product code** : 54-A 050

Ingredient name	%	CAS number
Sulfuric acid	≥1 - ≤3	7664-93-9

The exact percentage (concentration) in the composition has been withheld as a trade secret in accordance with paragraph (i) of §1910.1200.

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

Section 4. First aid measures

Description of necessary first aid measures

- Eye contact** : Get medical attention immediately. Call a poison center or physician. Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 20 minutes. Chemical burns must be treated promptly by a physician.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Get medical attention if adverse health effects persist or are severe. If unconscious, place in recovery position and get medical attention immediately.
- Skin contact** : Get medical attention immediately. Call a poison center or physician. Wash contaminated skin with soap and water. Wash contaminated clothing thoroughly with water before removing it, or wear gloves. Continue to rinse for at least 20 minutes. Chemical burns must be treated promptly by a physician. Wash clothing before reuse. Clean shoes thoroughly before reuse.
- Ingestion** : Get medical attention immediately. Call a poison center or physician. Wash out mouth with water. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Do not induce vomiting unless directed to do so by medical personnel. Chemical burns must be treated promptly by a physician. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately.

Most important symptoms/effects, acute and delayed

Potential acute health effects

- Eye contact** : Causes serious eye damage.
- Inhalation** : No known significant effects or critical hazards.

Section 4. First aid measures

- Skin contact** : Causes severe burns.
- Ingestion** : No known significant effects or critical hazards.

Over-exposure signs/symptoms

- Eye contact** : Adverse symptoms may include the following:
pain
watering
redness
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : Adverse symptoms may include the following:
pain or irritation
redness
blistering may occur
- Ingestion** : Adverse symptoms may include the following:
stomach pains

Indication of immediate medical attention and special treatment needed, if necessary

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. If it is suspected that fumes are still present, the rescuer should wear an appropriate mask or self-contained breathing apparatus. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Wash contaminated clothing thoroughly with water before removing it, or wear gloves.

See toxicological information (Section 11)

Section 5. Fire-fighting measures

Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.

- Specific hazards arising from the chemical** : No specific fire or explosion hazard.

- Hazardous thermal decomposition products** : Decomposition products may include the following materials:
sulfur oxides

- Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

- Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

Section 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Do not breathe vapor or mist. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.
- For emergency responders** : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

- Environmental precautions** : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods and materials for containment and cleaning up

- Spill** : Stop leak if without risk. Move containers from spill area. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). The spilled material may be neutralized with sodium carbonate, sodium bicarbonate or sodium hydroxide. Dispose of via a licensed waste disposal contractor. Contaminated absorbent material may pose the same hazard as the spilled product. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

Section 7. Handling and storage

Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8). Do not get in eyes or on skin or clothing. Do not breathe vapor or mist. Do not ingest. If during normal use the material presents a respiratory hazard, use only with adequate ventilation or wear appropriate respirator. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Keep away from alkalis. Empty containers retain product residue and can be hazardous. Do not reuse container.

- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. See also Section 8 for additional information on hygiene measures.

- Conditions for safe storage, including any incompatibilities** : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Store locked up. Separate from alkalis. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination. See Section 10 for incompatible materials before handling or use.

Section 8. Exposure controls/personal protection

Control parameters

Occupational exposure limits

Ingredient name	Exposure limits
Sulfuric acid	NIOSH REL (United States, 10/2013). TWA: 1 mg/m ³ 10 hours. OSHA PEL (United States, 6/2016). TWA: 1 mg/m ³ 8 hours. ACGIH TLV (United States, 3/2016). TWA: 0.2 mg/m ³ 8 hours. Form: thoracic fraction

- Appropriate engineering controls** : No personal respiratory protective equipment normally required. Avoid breathing dust/fume/gas/mist/vapors/spray. When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation.
- Individual protection measures**
- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing.
- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: chemical splash goggles and/or face shield. If inhalation hazards exist, a full-face respirator may be required instead.
- Skin protection**
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. Considering the parameters specified by the glove manufacturer, check during use that the gloves are still retaining their protective properties. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. In the case of mixtures, consisting of several substances, the protection time of the gloves cannot be accurately estimated.
- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Use a NIOSH/MSHA approved respirator if there is a risk of exposure at levels exceeding the exposure limits. Advice should be sought from respiratory protection specialists.

Section 9. Physical and chemical properties

Appearance

- Physical state** : Liquid.
- Color** : Colorless.
- Odor** : Odorless.
- Odor threshold** : Not available.
- pH** : 0.5 [Conc. (% w/w): 5%]

Section 9. Physical and chemical properties

Melting point	: Not available.
Boiling point	: 100°C (212°F)
Flash point	: Closed cup: >93.3°C (>199.9°F)
Evaporation rate	: Not applicable.
Flammability (solid, gas)	: Not available.
Lower and upper explosive (flammable) limits	: Not available.
Vapor pressure	: Not available.
Vapor density	: Not available.
Relative density	: 1.08 g/ml @ 20°C (68°F)
Solubility	: Soluble in the following materials: cold water and hot water.
Partition coefficient: n-octanol/water	: Not available.
Auto-ignition temperature	: Not available.
Decomposition temperature	: Not available.
Viscosity	: Not available.
Flow time (ISO 2431)	: Not available.
VOC content	: 0 % (w/w)

Section 10. Stability and reactivity

Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
Chemical stability	: The product is stable.
Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
Conditions to avoid	: No specific data.
Incompatible materials	: Reactive or incompatible with the following materials: reducing materials, organic materials, alkalis and moisture.
Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

Section 11. Toxicological information

Information on toxicological effects

Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
Sulfuric acid	LD50 Oral	Rat	2140 mg/kg	-

Irritation/Corrosion

Product/ingredient name	Result	Species	Score	Exposure	Observation
Sulfuric acid	Eyes - Severe irritant	Rabbit	-	250 µg	-
	Eyes - Severe irritant	Rabbit	-	0.5 minutes 5 mg	-

Sensitization

Section 11. Toxicological information

There is no data available.

Mutagenicity

There is no data available.

Carcinogenicity

There is no data available.

Reproductive toxicity

There is no data available.

Teratogenicity

There is no data available.

Specific target organ toxicity (single exposure)

There is no data available.

Specific target organ toxicity (repeated exposure)

There is no data available.

Aspiration hazard

There is no data available.

Information on the likely routes of exposure : Dermal contact. Eye contact. Inhalation. Ingestion.

Potential acute health effects

Eye contact : Causes serious eye damage.
Inhalation : No known significant effects or critical hazards.
Skin contact : Causes severe burns.
Ingestion : No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

Eye contact : Adverse symptoms may include the following:
pain
watering
redness
Inhalation : No known significant effects or critical hazards.
Skin contact : Adverse symptoms may include the following:
pain or irritation
redness
blistering may occur
Ingestion : Adverse symptoms may include the following:
stomach pains

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

Potential immediate effects : No known significant effects or critical hazards.
Potential delayed effects : No known significant effects or critical hazards.

Long term exposure

Potential immediate effects : No known significant effects or critical hazards.
Potential delayed effects : No known significant effects or critical hazards.

Potential chronic health effects

Section 11. Toxicological information

General	: No known significant effects or critical hazards.
Carcinogenicity	: No known significant effects or critical hazards.
Mutagenicity	: No known significant effects or critical hazards.
Teratogenicity	: No known significant effects or critical hazards.
Developmental effects	: No known significant effects or critical hazards.
Fertility effects	: No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates

Route	ATE value
Oral	107000 mg/kg

Section 12. Ecological information

Toxicity

Product/ingredient name	Result	Species	Exposure
Sulfuric acid	Acute LC50 42500 µg/L Marine water Acute LC50 42 ppm Fresh water	Crustaceans - Pandalus montagui - Adult Fish - Gambusia affinis - Adult	48 hours 96 hours

Persistence and degradability

There is no data available.

Bioaccumulative potential

There is no data available.

Mobility in soil



Soil/water partition coefficient (K_{oc})	: Not available.
--	------------------

Other adverse effects	: No known significant effects or critical hazards.
------------------------------	---

Section 13. Disposal considerations

Disposal methods	: The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling empty containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.
-------------------------	---

Section 14. Transport information

	DOT Classification	IMDG	IATA
UN number	UN3082	Not regulated.	Not regulated.
UN proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Sulfuric acid)	-	-
Transport hazard class(es)	9  	-	-
Packing group	III	-	-
Environmental hazards	Yes.	No.	No.

AERG : 171
DOT-RQ Details

: Sulfuric acid

1000 lbs / 454 kg [66.262 gal / 250.83 L]

Additional information
DOT Classification

: Non-bulk packages of this product are not regulated as hazardous materials in package sizes less than the product reportable quantity, unless transported by inland waterway. The marine pollutant mark is not required when transported on inland waterways in sizes of ≤5 L or ≤5 kg.

Reportable quantity 50000 lbs / 22700 kg [5552.5 gal / 21018.5 L]. Package sizes shipped in quantities less than the product reportable quantity are not subject to the RQ (reportable quantity) transportation requirements.

Special precautions for user

: **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage. Protect from freezing. Freezing will damage product and render it unusable.

Section 15. Regulatory information

U.S. Federal regulations

: **United States inventory (TSCA 8b):** All components are listed or exempted.
Clean Water Act (CWA) 311: Sulfuric acid

Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs)

: Not listed

Clean Air Act Section 602 Class I Substances

: Not listed

Clean Air Act Section 602 Class II Substances

: Not listed

DEA List I Chemicals (Precursor Chemicals)

: Not listed

DEA List II Chemicals (Essential Chemicals)

: Listed

SARA 302/304


Section 15. Regulatory information

Composition/information on ingredients

Name	EHS	SARA 302 TPQ		SARA 304 RQ	
		(lbs)	(gallons)	(lbs)	(gallons)
Sulfuric acid	Yes.	1000	66.3	1000	66.3

SARA 304 RQ : 50000 lbs / 22700 kg [5552.5 gal / 21018.5 L]

SARA 311/312

Classification : SKIN CORROSION/IRRITATION - Category 1
SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 1

Composition/information on ingredients

Name	Classification
Sulfuric acid	SKIN CORROSION/IRRITATION - Category 1A SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 1

SARA 313

	Product name	CAS number
Form R - Reporting requirements	Sulfuric acid	7664-93-9
Supplier notification	Sulfuric acid	7664-93-9

SARA 313 notifications must not be detached from the SDS and any copying and redistribution of the SDS shall include copying and redistribution of the notice attached to copies of the SDS subsequently redistributed.

State regulations

Massachusetts : The following components are listed: Sulfuric acid
New York : The following components are listed: Sulfuric acid
New Jersey : The following components are listed: Sulfuric acid
Pennsylvania : The following components are listed: Sulfuric acid

California Prop. 65

No products were found.

International lists

National inventory

Australia : All components are listed or exempted.
Canada : All components are listed or exempted.
China : All components are listed or exempted.
Europe : All components are listed or exempted.
Malaysia : All components are listed or exempted.
New Zealand : All components are listed or exempted.
Philippines : All components are listed or exempted.
Republic of Korea : All components are listed or exempted.
Taiwan : All components are listed or exempted.

Section 16. Other information

Procedure used to derive the classification

Classification	Justification
SKIN CORROSION/IRRITATION - Category 1	On basis of test data
SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 1	On basis of test data

History

Date of issue mm/dd/yyyy : 08/15/2018
Date of previous issue : 11/30/2015
Version : 2
Prepared by : KMK Regulatory Services Inc.

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.