

Model: 6250XXXX



FEATURES

- Energy Efficient and Long-Lasting LED Lighting
- Acrylic Light Diffuser
- Smart Touch Control Switch
- 5mm Copper-free Mirror
- Durable Aluminum Frame
- Surface-Mount with French Cleat Mounting Bracket
- Hardwired (Junction box required)

LIGHTING


- LED (Light-Emitting Diode)
- Average Bulb Life of 50,000 hours
- CRI: 85+
- Dual Color Temperature: 3000K & 6000K
- Compatible with Wall Dimmers
- Brightness & Power Consumption: See Page 2
- Power Requirements: 110-130V AC, 60Hz

SAFETY

- Safety Backed Mirror
- IP44 Rated
- UL Listed

OVERVIEW

innoci-usa does not cut corners and only uses the highest quality components and bulbs to make sure that the mirror will be maintenance free and function like the day you purchased for average 50,000 hours of use. **innoci-usa** prides itself on providing unmatched price vs quality for all of our products. All mirrors come with a 5-year limited warranty.



Model #	A	B	C	Brightness (Lumen)	Power Consumption (Watt)
62504824	48	24	1 1/4	2010	33

innoci-usa Inc.
Newport Beach, CA 92660

www.innoci-usa.com
(866) 479-8076

customerservice@innoci-usa.com

innociusa
L I F E S T Y L E