



Available Colors: Burgundy, Gray, Blue, Brown and Black



Specialty



Encore™ is an entrance mat that uses a combination of scraping and looped pile Decalon® drying yarns in a linear pattern, to facilitate the scraping function and begin the drying process. It can be used as a stand-alone mat, or as part of the “Stages” coordinated entrance matting system.

Test	Test Description	*Results
ASTM D-6540-05	Accelerated Soiling	Based on Visual Inspection 4.8 - Vacuum Rating 5.0 - Rating After Extraction
-	Water Retention	Weight Gain = 38.3% (0.5 gals./yd ²)
ASTM D-5252-98	Accelerated Wear - Sim Floor Machine	Appearance Rating @ 6,000 cycles - 3.5
ASTM D3884	Abrasion Resistance	@ 3,000 cycles Primary backing visible
CPSC FF 1-70 (ASTM D-2859)	Surface Flammability of Carpets and Rugs Ignition Characteristics - Finished Textile Floor Covering Material	Pass

*All testing of NoTrax® floor matting has been performed by an independent testing laboratory.

07/2014

Appearance Rating Key

5	No change
4	Slight change
3	Noticeable change
2	Considerable change
1	Severe change

- Can be used alternatively to the Intermission mat
- Heavyweight vinyl non-slip backing
- Stock Sizes: 2' x 3', 3' x 4', 3' x 5', 3' x 6', 3' x 10', 4' x 6', 4' x 8'
- Roll Sizes: 3' x 60', 4' x 60', 6' x 60'
- Custom Sizes: In 3', 4', and 6' widths (up to 60')
- Recommended and approved product as part of the GreenTRAX™ program for “Green Cleaning” environments (When used as a part of the “Stages” system)



Custom Sizes

