

Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
	<p>Toxic compound, do not ingest or inhale. Avoid all contact with this material.</p> <p>Irritating to skin, eyes, and the respiratory system.</p> <p>Environmental hazard. This material is very toxic to aquatic organisms and may cause long term adverse effects to the aquatic environment.</p> <p>CARCINOGEN. MINIMIZE EXPOSURE.</p> <p>POSSIBLE MUTAGEN. MINIMIZE EXPOSURE.</p> <p>Light sensitive material.</p> <p>Store under argon.</p>	

Section I. Chemical Product and Company Identification

Chemical Name	4-Chloro-2-methylaniline		
Catalog Number	A0704	Supplier	TCI America 9211 N. Harborgate St. Portland OR 1-800-423-8616
Synonym	2-Amino-5-chlorotoluene; 4-Chloro-o-toluidine; Fast Red TR Base		
Chemical Formula	C ₇ H ₈ ClN		
CAS Number	95-69-2	In case of Emergency Call	Chemtrec® (800) 424-9300 (U.S.) (703) 527-3887 (International)

Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
4-Chloro-2-methylaniline	95-69-2	Min. 98.0 (GC,T)	This chemical is classified as a carcinogen. There is no acceptable exposure limit for a carcinogen. This compound is classified as a possible mutagen. There is no acceptable exposure limit for a mutagen.	Rat LD ₅₀ (oral) 1058 mg/kg Wild Bird LD ₅₀ (oral) 75 mg/kg

Section III. Hazards Identification

Acute Health Effects	<p>Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering.</p> <p>Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.</p>
Chronic Health Effects	<p>CARCINOGENIC EFFECTS : Not available.</p> <p>MUTAGENIC EFFECTS : Not available.</p> <p>TERATOGENIC EFFECTS : Tumorigenic effects.</p> <p>Mouse TDLo Oral 6720 mg/kg for 80 weeks continuous</p> <p>Toxic Effects:</p> <p>Tumorigenic - Equivocal tumorigenic agent by RTECS criteria</p> <p>Musculoskeletal - Tumors</p> <p>DEVELOPMENTAL TOXICITY: Not available.</p> <p>Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.</p>

Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Skin Contact	In case of contact, immediately flush skin with plenty of water for at least 15 minutes while removing contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention immediately.
Inhalation	If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive.

Section V. Fire and Explosion Data

Flammability	May be combustible at high temperature.	Auto-Ignition	Not available.
Flash Points	124 °C (255.2 °F)	Flammable Limits	Not available.
Combustion Products	These products are toxic carbon oxides (CO, CO ₂), halogenated compounds, nitrogen oxides (NO _x). WARNING: Highly toxic HCl gas is produced during combustion.		
Fire Hazards	Not available.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available.		
Fire Fighting Media and Instructions	SMALL FIRE: Use DRY chemical powder. LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet. Consult with local fire authorities before attempting large scale fire-fighting operations.		

Section VI. Accidental Release Measures

Spill Cleanup Instructions	Toxic material. Irritating material. Environmentally hazardous material. Carcinogenic material. Possibly mutagenic material. Light sensitive material. Stop leak if without risk. If the product is in its solid form: Use a shovel to put the material into a convenient waste disposal container. If the product is in its liquid form: DO NOT get water inside container. Absorb with an inert material and put the spilled material in an appropriate waste disposal. DO NOT touch spilled material. Use water spray to reduce vapors. Prevent entry into sewers, basements or confined areas; dike if needed. Eliminate all sources of ignition. Consult federal, state, and/or local authorities for assistance on disposal.
----------------------------	--

Section VII. Handling and Storage

Handling and Storage Information	TOXIC. IRRITANT. ENVIRONMENTAL HAZARD. CARCINOGEN. POSSIBLE MUTAGEN. LIGHT SENSITIVE. STORE UNDER ARGON. Keep locked up. Keep away from heat. Mechanical exhaust required. When not in use, tightly seal the container and store in a dry, cool place. Avoid excessive heat and light. DO NOT ingest. Do not breathe dust. Wear suitable protective clothing. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively. Always store away from incompatible compounds such as oxidizing agents, acids.
----------------------------------	---

Section VIII. Exposure Controls/Personal Protection

Engineering Controls	Use process enclosures, local exhaust ventilation, or other engineering controls to keep airborne levels below recommended exposure limits. If user operations generate dust, fume or mist, use ventilation to keep exposure to airborne contaminants below the exposure limit.
Personal Protection	Splash goggles. Lab coat. Dust respirator. Boots. Gloves. A MSHA/NIOSH approved respirator must be used to avoid inhalation of the product. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product. 
Exposure Limits	This chemical is classified as a carcinogen. There is no acceptable exposure limit for a carcinogen. This compound is classified as a possible mutagen. There is no acceptable exposure limit for a mutagen.

Section IX. Physical and Chemical Properties

Physical state @ 20°C	Solid. (White crystalline powder.)	Solubility	Very slightly soluble in water.
Specific Gravity	1.19 (water=1)		
Molecular Weight	141.60	Partition Coefficient	LOG P _{ow} : 2.27
Boiling Point	241 °C (465.8 °F)	Vapor Pressure	Not applicable.
Melting Point	25 °C (77 °F) (freezing point)	Vapor Density	Not available.
Refractive Index	Not available.	Volatility	Not available.
Critical Temperature	Not available.	Odor	Characteristic.
Viscosity	Not available.	Taste	Not available.

Section X. Stability and Reactivity Data

Stability	This material is stable if stored under proper conditions. (See Section VII for instructions)
Conditions of Instability	Avoid excessive heat and light. Sensitive to light.
Incompatibilities	Reactive with oxidizing agents, acids, acid chlorides, acid anhydrides, chloroformates.

Section XI. Toxicological Information

RTECS Number	XU5000000
Routes of Exposure	Eye Contact. Ingestion. Inhalation.
Toxicity Data	Rat LD ₅₀ (oral) 1058 mg/kg Wild Bird LD ₅₀ (oral) 75 mg/kg
Chronic Toxic Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Tumorigenic effects. Mouse TDLo Oral 6720 mg/kg for 80 weeks continuous Toxic Effects: Tumorigenic - Equivocal tumorigenic agent by RTECS criteria Musculoskeletal - Tumors DEVELOPMENTAL TOXICITY : Not available. Repeated exposure to a highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.
Acute Toxic Effects	Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

Section XII. Ecological Information

Ecotoxicity	Not available.
Environmental Fate	4-Chloro-o-toluidine's production and use as an intermediate in the production of pigments and chlordimeform, a pesticide, could result in its release to the environment through various waste streams. 4-Chloro-o-toluidine is also produced directly in the environment through the microbial and/or chemical degradation and photo-decomposition of various pesticides. If released to the atmosphere, 4-chloro-o-toluidine will degrade in the vapor-phase by reaction with photochemically produced hydroxyl radicals (estimated half-life of 9 hours); it may also undergo direct photolysis. 4-Chloro-o-toluidine released to soil should have moderate mobility with an estimated Koc of 410. The presence of humus or organic matter in the soil may cause strong binding to soil however, due to the high reactivity of the aromatic amino group. Photolysis of 4-chloro-o-toluidine on soil surfaces may occur. Biodegradation of 4-chloro-o-toluidine is possible with 20% mineralization of this compound over 6 weeks reported in a soil system. Biologically mediated polymerizing transformations of 4-chloro-o-toluidine may also occur in soil. Volatilization of 4-chloro-o-toluidine from water surfaces will be slow based on an estimated Henry's Law constant of 2X10 ⁻⁶ atm-cu m/mole. Strong sorption to organic materials in the water column may be expected for some portion of 4-chloro-o-toluidine released to water. Bioconcentration of 4-chloro-o-toluidine in aquatic organisms is not a major fate process. Limited biodegradation data suggest that biodegradation of 4-chloro-o-toluidine in water will be slow. 7% removal of TOC from an industrial wastewater was reported; however GC analysis showed that more extensive degradation of the parent compound occurred. Exposure to 4-chloro-o-toluidine may occur occupationally during production and use of this compound and may also result from exposure to pesticides which form this compound as metabolite.

Section XIII. Disposal Considerations

Waste Disposal	Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.
----------------	---

Section XIV. Transport Information

DOT Classification	DOT CLASS 6.1: Toxic material
PIN Number	UN2239
Proper Shipping Name	Chlorotoluidines, solid
Packing Group (PG)	III
DOT Pictograms	

Section XV. Other Regulatory Information and Pictograms

TSCA Chemical Inventory (EPA)	This compound is ON the EPA Toxic Substances Control Act (TSCA) inventory list.
WHMIS Classification (Canada)	CLASS D-1B: Material causing immediate and serious toxic effects (TOXIC). On NDSL.
EINECS Number (EEC)	202-441-6
EEC Risk Statements	R23/24/25- Toxic by inhalation, in contact with skin and if swallowed. R36/37/38- Irritating to eyes, respiratory system and skin. R45- May cause cancer. R46- May cause heritable genetic damage. R47- May cause birth defects. R50- Very toxic to aquatic organisms. R53- May cause long-term adverse effects in the aquatic environment.
Japanese Regulatory Data	ENCS No. 3-265

Continued on Next Page

Emergency phone number (800) 424-9300

Section XVI. Other Information

Version 1.0
Validated on 3/16/2011.
Printed 3/16/2011.

Notice to Reader

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, household, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.

Printed 3/16/2011.