



# Triad<sup>®</sup> AA



- 235 Lumens (ANSI Standard)
- 2.5 Hour Run Time
- Type III Hardcoat Anodizing
- Foamed Vinyl Grip
- Reversible Pocket Clip
- Intermittent · Locked · Constant Switch
- 6.75" Long
- Two Lithium AA
- Zippered Travel Case


AA batteries have the distinct advantage of being readily available in virtually every part of the world. Lithium power cells provide increased cold weather performance, extended shelf life and high energy density. The newly introduced Lithium AA batteries by Energizer and ASP function nine times (9x) longer than their alkaline counterparts. They are ideal for duty use.

The Triad<sup>®</sup> AA provides the unique features of the Triad light (foam grip, reversible pocket clip, three position locking switch) in an AA format. Machined from 6061 T6 aluminum, each light is Type III hardcoat anodized in a matte black finish. An aluminum reflector and gold plated circuit boards drive a Cree XPG2 R5 LED to a sustained output of 235 lumens as measured against the ANSI FL-1 Standard. A precision ground glass lens is optically coated on both sides. Each Triad AA comes encased in a zippered ballistic carrier that may be used to store spare batteries or the removable pocket clip.

The intensity and features of a world class duty light with the convenience of AA batteries. The Triad AA by ASP. Simply Brilliant.



# Triad AA . . . Simply Brilliant



## Background

Designed to professional law enforcement standards  
 Aerospace aluminum construction  
 Precision machined  
 No sharp edges  
 O-ring sealed for maximum water resistance  
 Distinct profile

## Specifications

Length	6.75"	171.4 mm
Diameter	1.4"	35.6 mm
Weight	6.1 ounces	172.4 grams
	(with batteries)	
System	3 volt	
Flashlight Output	235 lumens (ANSI Standard)	

## Body

6061 T6 high strength aluminum  
 Matte black finish  
 Type III hardcoat anodized  
 Coated threads for durability  
 Exterior and interior scratch and corrosion protection  
 Foamed vinyl grip  
 Front clip groove  
 Rear clip groove

## Pocket Clip

Detachable

## Power Cells (recommended)

Two 1.5 volt Lithium (AA)  
 PTC protected  
 Safety vent  
 Ten year shelf life  
 2.5 hours continuous run time  
 Leak proof  
 Vibration resistant  
 Link case

## Power Cell Tube

Foamed vinyl grip  
 O-ring sealed

## Locking Switch

Back mounted  
 Quick and positive switch location under stress  
 O-ring sealed activation button  
 Locked (center)  
 Constant on/off switch activation (right)  
 Intermittent switch activation (left)  
 O-ring sealed switch cover  
 PC board positive circuit contact  
 Sensitive and quiet switch activation  
 Computer micro switch controlled  
 Self-cleaning (no carbon buildup)  
 Fail safe (backup) switch circuits  
 Replaceable modular switch assemblies  
 Optional intermittent switch activation  
 O-ring sealed connection to the light body  
 Rotate one full turn to prevent accidental activation

## Reflector Assembly

Parabolic  
 Extremely durable  
 Computer calculated ray traces  
 Long distance penetrating beam  
 Room illuminating halo  
 Gasket sealed

## LED Assembly

Proprietary heat management  
 Custom driver  
 Smart chip technology  
 Gasket sealed

## Belt Case

Injection molded

## Accessory Case

Ballistic Weave  
 Zippered

## Warranty

Limited Lifetime



TLC Tactical Light Cases  
 protect and securely retain  
 the Triad®



Travel Cases  
 provide protection for the  
 Triad or accessories.

## SWITCH ACTIVATION



**ASP**  
 "Simply Brilliant"