




**GENERAL DESCRIPTION:**

Complete commercial shower system includes: an R120SS pressure balance valve and trim, a wall supply with 1/2" NPT female inlet and 1/2" NPSM male outlet, a 59" (1500mm) metal shower hose, vacuum breaker, a 3-function water-saving personal shower, slip-on diverter tub spout and a 36" Slide Bar.

Valve features a cast brass body, washerless 47mm ceramic disc valve cartridge with volume and temperature control, back-to-back capability, integrated check valves and hot limit safety stop. Pressure balancing cartridge maintains constant output temperature in response to changes in relative hot and cold supply pressure. One-half inch direct sweat inlets and outlets. With screwdriver stops. Rough-in plaster guard designed for use as thin-wall mounting adapter. Durable metal handle. 3-function water saving hand shower with 1.5gpm/5.7L/min. flow restrictor. Slide bar features an adjustable shower holder which can be set at any height or position along the bar and angle up to 45°.



**SUGGESTED SPECIFICATION:**

Shower system shall feature a wall supply with 1/2" NPT female inlets and 1/2" NPSM male outlet, 59" metal hose, vacuum breaker, 1.5 gpm/5.7L/min. 3-function water saving personal shower, slip-on diverter tub spout and a 36" Slide Bar. Pressure Balance valve shall feature a cast brass body. Shall feature ceramic disc valve cartridge which controls water temperature and volume. Shall also feature hot limit safety stop. Fitting shall be American Standard Model # 1662.215.002.

**MODEL NUMBER:**

☐ **1662.215 Commercial Shower System Kit**

Includes:

• Shower Valve with SS	R120SS
• Colony Soft Valve Only Trim	T675.500.002
• 3-F Hand Shower - 1.5 GPM	1660.502.002
• In-Line Vacuum Breaker	1660.400.002
• Metal Hose	8888.035.002
• Wall Supply	8888.037.002
• 36" Slide Bar	1660.236.002
• Slip-On Diverter Tub Spout	8888.026

**PRODUCT FEATURES:**

**VALVE:**

**Cast Brass Valve Body:** Durable.

**Ceramic Disc Valve Cartridge:** Assures a lifetime of drip-free performance. Allows control over water temperature and volume.

**Pressure Balancing Valve Cartridge:** Maintains constant output temperature in response to changes in hot and cold supply pressure. Diaphragm system with integrated check valves engineered to eliminate cross flow.

**Back-to-Back Capability:** Hot and cold can be reversed quickly and easily.

**Adjustable Hot Limit Safety Stop:** Limits the amount of hot water allowed to mix with cold. Reduces the risk of accidental scalding.

**Integral Plaster Guard and Mounting Plate:**

Protects valve during installation and serves as a mounting plate for thin-wall installations.

**PERSONAL SHOWER:**

**Water Saving:** Saves 40% in water usage.

**SLIDE BAR:**

**Simple Height Adjustment:** Allows positioning of the personal shower anywhere along the bar.

**CODES AND STANDARDS**

Install as required to comply with local code requirements.

ASME A112.18.1  
ASSE 1016  
CSA B 125

Product Number	Description	Finish
		Polished Chrome
		002

1662.215	FloWise® Commercial Shower System Kit. Contains pressure balance valve with volume and temperature control, trim kit, 3-function water saving hand shower, metal hose, vacuum breaker, slip-on diverter tub spout, wall supply and 36" slide bar. 1.5gpm/5.7L/min.
----------	--

**Available Modification:**

Part Suffix	Description
_SG	Commercial Shower System with 36" Slide-Grab Bar (1662.236) instead of 36" Slide Bar (1660.236)

