

Catalog Number	
Notes	Type

FEATURES & SPECIFICATIONS

INTENDED USE

The QUICK-FLEX Switch Drop, located above the primary switch location, introduces local switching to the QUICK-FLEX system. It provides local switched power for fixtures as well as the ability to carry on unswitched power through the use of a QUICK-FLEX Extender (QE).

ELECTRICAL

Rated for use on 20-amp branch circuits.

Safety-keying prevents accidental mating of components with different voltages.

All conductors are No. 12 AWG copper with 90°C thermoplastic insulation rated 600V.

All components provide a fully-rated No. 12 AWG grounding conductor.

SYSTEM FEATURES

Pin and socket contacts.

Color-coded labels for quick voltage identification.

Provides switched and unswitched power at every switch location.

INSTALLATION

Enables local switches to be integrated into the QUICK-FLEX system.

Located directly above each switch.

Cast snap-in connector provided on whip end for fast, easy installation into 1/2" trade size knockout; no locknut required.

Prestripped, solid copper leads for easy installation into push-in-type terminals on switches.

Prestripped 5/8" leads for ease of wiring.

LISTINGS

UL listed.

Built to UL Standard 183 for Manufactured Wiring Systems and suitable for air handling spaces above grid ceiling as described in NEC 300.22(C)

Listed and labeled to comply with Canadian Standards.


WARRANTY

One year from the date of purchase.

Recessed Ceiling Lighting System

QSD

QUICK-FLEX Switch Drop



QUICK-FLEX

ORDERING INFORMATION All configurations of this product are considered "standard" and have short lead times.

Example: QSD120 1LEVEL 07

QSD				
Series	Voltage	Conductors	Length	Options ¹
QSD	120 120V	1LEVEL Two 12 AWG conductors, plus 12AWG ground	01	HCF Meets healthcare facility requirements
	277 277V	2LEVEL Four 12 AWG conductors, plus 12AWG ground	07	
	347 347V	1LEVEL/N Two 12 AWG conductors, plus 12 AWG ground and 12 AWG neutral	09 13 15	


NOTES:

1 HCF is available with 2LEVEL and 1LEVEL/N conductors only.

QSD QUICK-FLEX® Switch Drop

DIMENSIONS

All dimensions are inches (millimeters).





- A UL-recognized connector body
- B Stamped 18-gauge galvanized CRS enclosure
- C Tin-plated copper contacts
- D Cast snap-in connector for 1/2" trade size knockout (no locknut required)
- E 6" leads prestripped 5/8"; No. 12 AWG with 90°C, 600V insulation
- F MC Cable standard and HCF MC optional.

NOTES:

- 1 One or two hot conductors in 120, 277 or 347V as required.
- 2 Prefabricated Quick-Flex switch drop carrying No. 12 AWG copper conductors, 600V, 90°C thermoplastic insulation and fully-rated grounding conductor. Rated for 20-amp capacity.

WIRING SCHEMATICS



SYSTEMVIEW

