

Cleans, Deodorizes & Sanitizes Surfaces without Chemicals

The AmeriVap® 50kW Industrial Steam Cleaner is one of our larger models. This 3-Phase electrically powered generator produces up to 173 lbs. of very dry steam per hour, 24/7.

The 50kW is ideal for cleaning and degreasing large pieces of equipment like rail cars, cleaning and sanitizing large beverage operations and bottling lines, sanitizing large tanks or powering larger Houdini™ conveyor belt cleaners.

The Xtreme Steam 50kW unit is ASME certified—required in the US and Mexico. This means it's built to last with redundant control manifolds and a boiler that weighs about 3 times that of imitations.



Hot Steam
(212°F at tip)

Dry Steam
(5%)

Powerful Steam
(up to 150psi)

PRODUCT FEATURES

- **Portable, can go most anywhere**
- **No long, hot steam lines**
- **Cleans and Sanitizes without toxic chemicals**
- **Uses a fraction of the water (quarts per hour vs. gallons per minute)**

50kW SPECIFICATIONS

Steam Production	173 lbs/hr
Water Tank Capacity	25 gal
Boiler Capacity	8.2 gal
Working Time	24 / 7
Working Pressure	0 - 180 psi
Boiler Temperature	380° F
Temperature at Tip	220° F
Net Weight	870 lbs
Available Voltages	From 380v to 575v
Amps	Based on Volts
Phase	3 Phase
Dimensions	72 x 30 x 42