



# GasAlert **MaxXT II**

**multi-gas detector**



## Go the distance, and save

GasAlertMax XT II is the smart, simple, economical way to compliance. Workers feel safe and incidents are minimized so everyone will be able to do more. That means savings realized from business continuity and productivity.

### Simple operation, with SmartSample pump.

GasAlertMax XT II reliably monitors up to four hazards and combines straightforward one-button operation with our robust, motorized pump for intelligent, remote sampling, ideal for confined spaces. The GasAlertMax XT II is fully compatible with MicroDock II automated test and calibration system.

H<sub>2</sub>S

CO

O<sub>2</sub>

LEL



**WATER  
RESISTANT** 

- Minimize costs and training with one-button operation
- More accurate sampling results with SmartSample pump technology
- Compact, comfortable and field tough

**BWF**  
Technologies  
by Honeywell

**Wear yellow. Work safe.**

### Standard features of BW products:

- Continuous LCD shows real-time gas concentrations
- Compact and lightweight design makes it comfortable to wear
- Water-resistant
- Simple automatic calibration procedure; compatible with BW MicroDock II automatic test and calibration station
- Full function self-test of sensor, battery status, circuit integrity and audible/visual alarms on start up
- Bright wide-angled visual alarm bars
- Built-in concussion-proof boot

### Additional GasAlertMax XT II features:

- Integrated sampling pump with reliable diaphragm technology
- Best in class block detection with semi-conductor pressure sensor
- Multi-language support in English, French, German, Spanish and Portuguese
- Conveniently manage your detector with Fleet Manager II
- Equipped with standard datalogging and event logging

### Options and Accessories



MicroDock II compatible



Belt holster



Multi-unit cradle charger



Concussion-proof boot

For a complete list of accessories, please contact BW Technologies by Honeywell.

### Sensor Specifications


Gas	Measuring Range	Resolution
H <sub>2</sub> S	0-200 ppm	1 ppm
CO	0-1000 ppm	1 ppm
O <sub>2</sub>	0-30.0%	0.1%
Combustible gases	0-100% LEL 0-5.0% v/v	1% 0.1%

Alarm setpoints for all sensors are user adjustable. Setpoint(s) are automatically displayed during instrument start-up.

### GasAlertMax XT II Specifications

<b>Size</b>	5.1 x 2.8 x 2.0 in. / 13.1 x 7.0 x 5.2 cm	
<b>Weight</b>	11.5 oz. / 328 g	
<b>Temperature</b>	-4 to 122°F / -20 to 50°C	
<b>Humidity</b>	10 - 100% RH (non-condensing)	
<b>Alarms</b>	- Visual, vibrating, audible (95dB) - Low, High, STEL, TWA, OL (over limit), Low Battery, Pump	
<b>Tests</b>	Audible/visual alarms on activation, sensors, battery, pump and circuitry (continuous)	
<b>Typical battery life</b>	13 hours @ 32°F / 0°C 8 hours @ -4°F / -20°C Recharges in 6 hours	
<b>Pump draw</b>	Sample from up to 75 ft. / 23 m	
<b>User options</b>	Confidence beep	Force calibration when overdue
	Safety (sensor) lock	
	Latching alarms	Sensor configuration
	Safe display mode	Detector identification
	Calibration IR lock	Low alarm acknowledge
	Location selection	Language choices (five)
	Force block test	Set custom start-up message
	Force bump test when overdue	Confidence interval Datalog interval
<b>Ratings</b>	EMI/RFI: Complies with EMC Directive 2004/108/EC	
<b>Ingress Protection</b>	IP66/67	
<b>Certifications and approvals</b>	Class I, Div. 1, Gr. A, B, C, D <b>IECEX:</b> Ga Ex ia IIC T4 <b>ATEX:</b> II 1 G Ga Ex ia IIC T4 Br Ex ia IIC T4	
<b>Warranty</b>	Full two year warranty including all sensors	

### Locally available from



DUE TO ONGOING RESEARCH AND PRODUCT IMPROVEMENT, SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE.



### Corporate Headquarters

2840 - 2 Avenue S.E.  
Calgary, AB, Canada T2A 7X9  
Phone: +1.403.248.9226  
Toll free: 1.800.663.4164

[www.gasmonitors.com](http://www.gasmonitors.com)

USA 1.888.749.8878  
Europe +44 (0)1295.700.300  
France +33 (0) 442.98.17.70  
Germany 49 (0) 2137.17.6522

[info@gasmonitors.com](mailto:info@gasmonitors.com)

Middle East +971.4.887.1766  
S.E. Asia +65.6580.3468  
China +86.10.6786.7305  
Australia +61.3.9464.2770

Latin America +55.11.3475.1873  
Other Countries +1.403.248.9226

6570-0-EN  
© 2010 Honeywell International Ltd. All Rights Reserved.