


Single Stage Performance Data

Head	1/3 HP	Shut off 27 psi. / 1.86 bar	PSI	15	20	25	30	35	40	50
Flow Rate		Max. Flow 36 gpm / 136 lpm	GPM	36	26	10	-	-	-	-
Head	1/2 HP	Shut off 30 psi. / 2.07 bar	PSI	15	20	25	30	35	40	50
Flow Rate		Max. Flow 34 gpm / 129 lpm	GPM	48	40	27	0	-	-	-
Head	3/4 HP	Shut off 33 psi. / 2.26 bar	PSI	15	20	25	30	35	40	50
Flow Rate		Max. Flow 60 gpm / 227 lpm	GPM	60	52	37	19	-	-	-
Head	1 HP	Shut off 40 psi. / 2.76 bar	PSI	15	20	25	30	35	40	50
Flow Rate		Max. Flow 64 gpm / 242 lpm	GPM	64	55	45	35	23	0	-
Head	1-1/2 HP	Shut off 44 psi. / 3.03 bar	PSI	15	20	25	30	35	40	50
Flow Rate		Max. Flow 75 gpm / 284 lpm	GPM	-	75	70	61	47	36	-
Head	2 HP	Shut off 42 psi. / 2.90 bar	PSI	15	20	25	30	35	40	50
Flow Rate		Max. Flow 78 gpm / 295 lpm	GPM	-	-	78	64	47	10	-



WARNING: Use only with nonflammable liquids compatible with pump component materials and in nonflammable/non-explosive atmospheres.

Call or visit your local branch or go to grainger.com/dayton for complete product line information



Exclusively from Grainger.