

### Precision Panel Convector

PPC Series



**Built-in Electronic Thermostat**



### Features

**Color**  
**Finish**  
**Voltage**  
**Wattage**  
**Construction**

**Heating element Control**


**Installation**  
**Warranty**

**Applications**

- White
- Polyester powder coated finish on body and grille
- 240V/208V 60Hz 1 phase
- 500/375W, 1000/750W, 1500/1125W, 2000/1500W
- 22-gauge steel front panel and back panel
- Hardwire connection
- Hinged wall mounting frame attached
- High-limit over-temperature protection with power interrupted reset
- Finned, steel sheathed element for durability and efficient heat transfer
- Built-in electronic thermostat, a RF receiver for wireless control, and whole-home synchronization. Optional Single-zone (DPCRWS) or Multi-zone (CX-MPC) CONNEX™ Controllers are available for easy, whole-home control. CSA-C828 compliant.
- Heater must be installed at least 6 inches from floor and side wall
- 2-year limited warranty on complete unit
- 10-year element warranty
- Family rooms, living rooms, bedrooms, home offices

**Precision Panel Convectors**

PPC Series



**Average Standard Watt Density 3.9W/cm<sup>2</sup>**

Watts	Volts	Cat No.	Qty	Dimensions			Weight	
				Width (A)	Height (B)	Depth (C)	kg	lb
500/375	240/208	PPC0500		450mm (17.7")	430mm (16.9")	108mm (4.3")	4.2	9.3
1000/750	240/208	PPC1000		620mm (24.4")	430mm (16.9")	108mm (4.3")	5.6	12.4
1500/1125	240/208	PPC1500		690mm (27.2")	430mm (16.9")	108mm (4.3")	5.9	12.9
2000/1500	240/208	PPC2000		860mm (33.9")	430mm (16.9")	108mm (4.3")	7.1	15.7

**Specifications may change without prior notice**

Project:		Approval Information
Consultant Engineer:		
Electrician Contractor:		
Distributor:		
Date :		
Contact at Dimplex:		
Comments:		