



Ask Any Pro!™

CS-600P CHAIN SAW

Professional Power, Quality Features and a Performance Cutting System

5 year
Consumer
Warranty

5 year consumer, 1 year commercial and 90 day rental warranty.

CHAIN SAWS



- Performance Cutting System Bar and Chain
- 59.8 cc Power Boost Vortex™ Engine for Outstanding Power
- Heavy-duty, Easy-access Air Filter Provides Exceptional Filtration
- Decompression Valve for Easier Starting
- Dual Post Chain Brake Handle for Increased Durability
- Side Access Chain Tensioner for Easy Chain Adjustment
- Clutch-driven Oiler Reduces Oil Consumption
- Digital Ignition System Automatically Adjusts Engine Timing

www.echo-usa.com

CS-600P CHAIN SAW



Ask Any Pro!™



The CS-600P Chain Saw is equipped with the Performance Cutting System bar and chain which increases bar life and improves cutting ability. It also features a 59.8cc Power Boost Vortex™ engine for outstanding power, a heavy-duty, easy-access air filter for exceptional filtration, a decompression valve for easier starting, a dual post chain brake handle, an easy to use side access chain tensioner, a clutch-driven oiler for reduced oil consumption, and a digital ignition system for automatic engine timing adjustments. The CS-600P is designed for the professional tree care operator and demanding landowner.



5 year consumer, 1 year commercial and 90 day rental warranty.



Decompression valve for easier starting.



Easy access to the air filter for simple routine maintenance.



Performance Cutting System bar and chain provides optimal cutting ability.

CHAIN SAW SPECIFICATIONS

Model	Engine Displacement (cc)	Engine Displacement (cu in)	Starting System	Ignition System	Oiling System	Vibration Reduction System	Available Bar Length (in)	Fuel Capacity (fl oz)	Oil Capacity (fl oz)	Dry Weight* lb (kg)
CS-310	30.5	1.86	i-30™	Digital	Automatic**	Standard	14	8.5	8.8	8.8
CS-330T	32.6	1.99	Standard	Digital	Adjustable Automatic	Standard	12, 14, 16	10.5	9.8	8.1
CS-330MX4	32.6	1.99	Standard	Digital	Adjustable Automatic	Standard	14	10.5	9.8	8.1
CS-341	33.4	2.04	Standard	SAIS	Adjustable Automatic	Standard	12, 14, 16	8.5	5.0	7.6
CS-360T	36.3	2.21	Standard	Digital	Adjustable Automatic	Standard	12, 14, 16	10.5	9.8	8.1
CS-370	36.3	2.21	i-30™	Digital	Adjustable Automatic	Standard	14, 16, 18	13.9	9.5	10.0
CS-400	40.2	2.45	i-30™	Digital	Adjustable Automatic	Standard	16, 18	13.9	9.5	10.1
CS-450	45.0	2.75	Standard	Digital	Adjustable Automatic**	Standard	16, 18, 20	15.2	9.5	11.2
CS-450P	45.0	2.75	Standard	Digital	Adjustable Automatic**	Standard	16, 18, 20	15.2	9.5	11.2
CS-530	50.1	3.06	Standard	SAIS	Adjustable Automatic	Standard	18, 20	20.3	9.5	11.2
CS-600P	59.8	3.65	Standard	Digital	Adjustable Automatic**	Standard	20, 24, 27	19.1	10.1	13
CS-680	66.8	4.07	Standard	SAIS	Adjustable Automatic***	Standard	20, 24, 27	22.5	13.0	14.5
CS-8000	80.7	4.92	Standard	SAIS	Adjustable Automatic***	Standard	24, 27, 32, 36	28.9	14.1	16.5

*without bar and chain
 **clutch-driven
 ***with manual over-ride