



TURBOBEAM™ MINI-LIGHTBARS

available in:



A Variety of Applications in One Affordable Platform

TurboBeam™ mini-lightbars are ideal for a variety of applications because of their aerodynamic look, exceptional warning capabilities, and their competitive price. These unique lightbars are ideal for personal vehicles, snowplows, utility vehicles, and tow trucks. When used in pairs, certain models meet NFPA upper level compliance for large fire apparatus.

Additional Applications

Not only do the TurboBeams meet the upper-level front and rear NFPA requirements, they are ideal lightbars for other applications as well. Models 415010/211906 are useful warning devices for volunteer firefighters, compact, specialty, and utility trucks. They are unique to these applications because of their economical pricing and long-lasting durability.

Reliable and Durable

TurboBeams are built with highly reliable components to maximize their effectiveness in the harshest conditions. They also feature impact-resistant polycarbonate domes and aluminum alloy extrusions to increase its service life. In addition, the TurboBeams powerful rotators, contain parabolic reflectors, providing exceptional performance and reliability.

Options and Installation

TurboBeams are available in 15" and 22" lengths. Model 211906 comes complete with a 10' cigarette plug adaptor and magnetic mounts for easy installation. Model 415510 has a raised base made from extruded aluminum that speeds installation and maintenance. TurboBeam lightbars are available in red, amber, blue, green or clear.

> Features

- Cost-effective mini-lightbar.
- Designed for multi-purpose flexibility.
- High quality, reliable warning.
- Easy to install and maintain.
- Available in red, amber, blue, green and clear.
- Available in 15" and 22" lengths

> Approvals

- SAE J845 Class 1 (SAE J1318 Class 1, 2009)
- NFPA 1901 compliant packages available

> How to Order

Select Model (specify color)

15", 12 VDC, (2) 95 FPM rotators, flush base

- 415010** Permanent mount
- 415011** Diamond mirror, permanent mount
- 211906** Diamond mirror, magnetic mount

15", 24 VDC, (2) 95 FPM rotators, flush base

- 211900** Permanent mount
- 211905** Diamond mirror, permanent mount

15", 12 VDC, (2) 95 FPM rotators, raised base

- 415510** Permanent mount

15", 24 VDC, (2) 95 FPM rotators, raised base

- 211902** Permanent mount

22", 12 VDC, (2) 95 FPM rotators, diamond mirror, flush base

- 415111** Permanent mount
- 211914** Magnetic mount

22", 24 VDC, (2) 95 FPM rotators, diamond mirror, flush base

- 211908** Permanent mount

22", 12 VDC, (2) 95 FPM rotators, diamond mirror, raised base

- 415611** Permanent mount

22", 24 VDC, (2) 95 FPM rotators, diamond mirror, raised base

- 211910** Permanent mount


Specify Mounting Kit

- 22PK** Permanent Mount Kit
- 22MK** Magnetic Mount Kit


Pre-Select Models



415510, 415010, 211900, 211902



21190, 211906, 41011



211908, 211910, 211914, 41111, 41611

Legend	
	95 FPM rotator
	175 FPM rotator
	Diamond mirror
	V-Mirror

	15"	22"
Specifications		
Flash Rate	190 per minute (380 with mirror)	
Voltage	12/24 VDC	
Candelas	80,000	
Physical Specifications		
Length	15.0 in (38.1 cm)	22.0 in (55.8 cm)
Width	9.0 in (22.9 cm)	9.0 in (22.9 cm)
Height	5.0 in (12.7 cm)	5.0 in (12.7 cm)
Ship Weight		
	5.0 lbs (2.2 kg)	6.0 lbs (2.7 kg) (add 2.0 lbs [0.9 kg] for magnetic mount)



Flush base TurboBeam™ Model 211906



2645 Federal Signal Drive, University Park, IL 60484
Tel.: (800) 264-3578 • Fax: (800) 682-8022
www.fedsig.com

TurboBeam is a trademark of Federal Signal Corporation.

©2010 Federal Signal Corporation. M1520 | 1210