

# accent



The bright white radiance of the GE energy smart® LED PAR16 lamps isn't just something you see, it's something you feel.

## GE energy smart® LED PAR16 lamps

For accent lighting applications, the GE energy smart® dimmable 4.5-watt LED PAR16 lamp offers the ideal solution.

### LOW-COST OPERATION

- Using only 4.5 watts of energy, save over \$83 in energy costs over the rated life of a lamp versus a 35-watt halogen lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources

### EXCELLENT COLOR RENDERING

- Available with a CRI of 80 to 82

### COLOR TEMPERATURE

- Halogen-like color
- Available in 3000K

### LONG LIFE

- 15,000 hours rated life (L70) for 4-watt PAR16
- 25,000 hours rated life (L70) for 4.5-watt PAR16

### MORE LIGHT

- The 4.5-watt lamp provides 50% more light with only a 0.5-watt increase from 4 watts

### DIMMABLE

- Dims from 100% to 10%

### BEAM PATTERNS

- Available in 25° and 30° beam patterns

### ENVIRONMENTALLY CONSCIOUS

- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS

### GE QUALITY AND RELIABILITY

- 3-year limited warranty

To learn more about saving money and energy, go to: [gelighting.com/ThinkLED](http://gelighting.com/ThinkLED)

When you Think LED lighting, Think GE.

ecomagination<sup>SM</sup>



imagination at work

**PERFORMANCE DATA**

GE energy smart® LED PAR16 lamps

BULB SHAPE	BASE TYPE	WATTS	GRAINGER ITEM NUMBER	ORDER CODE	DESCRIPTION	VOLTS	CASE QTY**	MOL (IN)	LUMENS INITIAL	CBCP	INITIAL COLOR TEMP	CRI	+RATED LIFE (YRS) 3HRS/DAY	*RATED LIFE L70(HRS)	*ESTIMATED ENERGY COST/YR	ENERGY STAR® STATUS	ADDITIONAL INFORMATION
<b>Compact PAR16 - Dimming</b>																	
PAR16	MED	4.5	34J754	66136	LED5DP16S/NFL/TP	120	3	3.00	180		3000	80	22.8	25,000	\$0.48		Accent, 25° Beam, Silver
<b>Compact PAR16 - Non-Dimming</b>																	
PAR16	MED	4	6CEC3	75848	LED4P16S830/30	120	6	2.87	100	230	3000	80	13.7	15,000	\$0.48		Accent, 30° Beam, Silver
		4.5	6XWL6	62905	LED5P16S/NFL/TP	120	3	2.87	200	800	3000	82	22.8	25,000	\$0.54	★	Accent, 25° Beam, Silver

For additional product and application information, please consult GE's website: [gelighting.com/ThinkLED](http://gelighting.com/ThinkLED)

- \* The life rating is based on the hours of operation the lamp will provide before reaching 70% of its original lumen rating (L70)
- \*\* Minimum order quantity = 6
- ★ ENERGY STAR® qualified
- ^ Estimated energy cost per year based on \$0.11 per kWh energy rate and 3 operating hours per day  
 Note: Product descriptions ending in "TP" indicate a card blister or clamshell package nested in a tray for shelf display.  
 Cards also designed for hook display.



Product is compliant with material restriction requirements of RoHS  
 energy smart® is a registered trademark of GE  
 ENERGY STAR® and the ENERGY STAR® logo are registered U.S. marks

