

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : ZEP HEAVY-DUTY BASEBOARD STRIPPER
20N18OZ_12CT

Material number : 00000000001042099

Manufacturer or supplier's details

Company : Zep Inc.

Address : 350 Joe Frank Harris Parkway, SE
Emerson, GA 30137

Telephone : Compliance Services - 877-428-9937

Emergency telephone numbers

For SDS Information : Compliance Services - 877-428-9937

For a Medical Emergency : 877-541-2016 Toll Free - All Calls Recorded

**For a Transportation
Emergency** : CHEMTREC: 800-424-9300 - All Calls Recorded.
In the District of Columbia 202-483-7616

Recommended use of the chemical and restrictions on use

SECTION 2. HAZARDS IDENTIFICATION

Emergency Overview

Appearance	Aerosol containing a liquefied gas
Colour	clear, colourless
Odour	slight, solvent-like

GHS Classification

Flammable aerosols : Category 1
Gases under pressure : Liquefied gas
Skin corrosion : Category 1B
Serious eye damage : Category 1

GHS label elements

Hazard pictograms :



Signal word : Danger

Hazard statements : H222 Extremely flammable aerosol.
H280 Contains gas under pressure; may explode if heated.
H314 Causes severe skin burns and eye damage.

Precautionary statements : **Prevention:**
P210 Keep away from heat/sparks/open flames/hot surfaces.
No smoking.

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

P211 Do not spray on an open flame or other ignition source.
P251 Pressurized container: Do not pierce or burn, even after use.
P260 Do not breathe dust or mist.
P264 Wash skin thoroughly after handling.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response:

P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

P303 + P361 + P353 IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower.

P304 + P340 + P310 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Immediately call a POISON CENTER or doctor/ physician.

P305 + P351 + P338 + P310 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER/doctor.

P363 Wash contaminated clothing before reuse.

Storage:

P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

Disposal:

P501 Dispose of contents/container in accordance with local regulation.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
2-butoxyethanol	111-76-2	>= 10 - < 20
2-aminoethanol	141-43-5	>= 5 - < 10
butane	106-97-8	>= 3 - < 5
ethane-1,2-diol	107-21-1	>= 1 - < 3
propane	74-98-6	>= 1 - < 3

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

General advice : Move out of dangerous area.
Consult a physician.
Show this safety data sheet to the doctor in attendance.
Do not leave the victim unattended.

If inhaled : If unconscious, place in recovery position and seek medical advice.

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

- If symptoms persist, call a physician.
- In case of skin contact : Wash off immediately with plenty of water for at least 15 minutes.
Remove contaminated clothing and shoes.
Wash contaminated clothing before reuse.
If skin irritation persists, call a physician.
- In case of eye contact : Small amounts splashed into eyes can cause irreversible tissue damage and blindness.
Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.
Continue rinsing eyes during transport to hospital.
Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : Keep respiratory tract clear.
DO NOT induce vomiting unless directed to do so by a physician or poison control center.
Never give anything by mouth to an unconscious person.
If symptoms persist, call a physician.
Take victim immediately to hospital.
- Most important symptoms and effects, both acute and delayed : Effects are dependent on exposure (dose, concentration, contact time).
Effects are immediate and delayed.
Symptoms may include blistering, irritation, burns, and pain.
Causes severe skin burns and eye damage.
Review section 2 of SDS to see all potential hazards.
- Notes to physician : Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during firefighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Hazardous combustion products : Carbon dioxide (CO₂)
Carbon monoxide
Smoke
Nitrogen oxides (NO_x)
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
- Further information : Collect contaminated fire extinguishing water separately. This must not be discharged into drains.

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
For safety reasons in case of fire, cans should be stored separately in closed containments.
Use a water spray to cool fully closed containers.

Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.
Ensure adequate ventilation.
Remove all sources of ignition.
Evacuate personnel to safe areas.
Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas.
- Environmental precautions : Prevent product from entering drains.
Prevent further leakage or spillage if safe to do so.
If the product contaminates rivers and lakes or drains, inform respective authorities.
- Methods and materials for containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Sweep up and shovel into suitable containers for disposal.

SECTION 7. HANDLING AND STORAGE

- Advice on safe handling : Do not breathe vapours or spray mist.
Avoid contact with skin and eyes.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Take precautionary measures against static discharges.
Provide sufficient air exchange and/or exhaust in work rooms.
Dispose of rinse water in accordance with local and national regulations.
Always replace cap after use.
- Conditions for safe storage : BEWARE: Aerosol is pressurized. Keep away from direct sun exposure and temperatures over 50 °C. Do not open by force or throw into fire even after use. Do not spray on flames or red-hot objects.
No smoking.
Keep in a dry, cool and well-ventilated place.
Observe label precautions.
Electrical installations / working materials must comply with the technological safety standards.
- Materials to avoid : Do not store near acids.
Oxidizing agents

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
2-butoxyethanol	111-76-2	TWA	20 ppm	ACGIH
		TWA	5 ppm 24 mg/m ³	NIOSH REL
		TWA	50 ppm 240 mg/m ³	OSHA Z-1
		TWA	25 ppm 120 mg/m ³	OSHA P0
		PEL	20 ppm 97 mg/m ³	CAL PEL
2-aminoethanol	141-43-5	TWA	3 ppm	ACGIH
		STEL	6 ppm	ACGIH
		TWA	3 ppm 8 mg/m ³	NIOSH REL
		ST	6 ppm 15 mg/m ³	NIOSH REL
		TWA	3 ppm 6 mg/m ³	OSHA Z-1
		STEL	6 ppm 15 mg/m ³	OSHA P0
		TWA	3 ppm 8 mg/m ³	OSHA P0
		PEL	3 ppm 8 mg/m ³	CAL PEL
		STEL	6 ppm 15 mg/m ³	CAL PEL
butane	106-97-8	TWA	800 ppm 1,900 mg/m ³	NIOSH REL
		TWA	800 ppm 1,900 mg/m ³	OSHA P0
		PEL	800 ppm 1,900 mg/m ³	CAL PEL
		STEL	1,000 ppm	ACGIH
ethane-1,2-diol	107-21-1	C	50 ppm 125 mg/m ³	OSHA P0
		C (Aerosol only)	100 mg/m ³	ACGIH
		C (Vapour)	40 ppm 100 mg/m ³	CAL PEL
propane	74-98-6	TWA	1,000 ppm 1,800 mg/m ³	NIOSH REL
		TWA	1,000 ppm 1,800 mg/m ³	OSHA Z-1
		TWA	1,000 ppm 1,800 mg/m ³	OSHA P0
		PEL	1,000 ppm 1,800 mg/m ³	CAL PEL

Biological occupational exposure limits

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

Component	CAS-No.	Control parameters	Biological specimen	Sampling time	Permissible concentration	Basis
2-BUTOXYETHANOL	111-76-2	Butoxyacetic acid (BAA)	Urine	End of shift (As soon as possible after exposure ceases)	200.mg/g Creatinine	ACGIH BEI

Engineering measures : effective ventilation in all processing areas

Personal protective equipment

Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.

Hand protection

Material

Remarks

: Protective gloves

: The suitability for a specific workplace should be discussed with the producers of the protective gloves.

Eye protection

: Access to clean water to rinse eyes must be available, options include: eye wash stations or showers, or eye wash bottles with pure water.

Tightly fitting safety goggles

Wear face-shield and protective suit for abnormal processing problems.

Skin and body protection

: Impervious clothing

Choose body protection according to the amount and concentration of the dangerous substance at the work place.

Hygiene measures

: When using do not eat or drink.

When using do not smoke.

Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : Aerosol containing a liquefied gas

Colour : clear, colourless

Odour : slight, solvent-like

Odour Threshold : No data available

pH : not determined

Melting point/freezing point : No data available

Boiling point : 98.3 °C

Flash point :

Not applicable

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

Evaporation rate	: < 1
Flammability (solid, gas, liquid)	: Extremely flammable aerosol.
Upper explosion limit	: No data available
Lower explosion limit	: No data available
Vapour pressure	: No data available
Relative vapour density	: No data available
Density	: 0.996 g/cm ³
Solubility(ies)	
Water solubility	: soluble
Solubility in other solvents	: not determined
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: not determined
Thermal decomposition	: No data available
Viscosity	
Viscosity, kinematic	: No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity	: Stable
Chemical stability	: Stable under normal conditions.
Possibility of hazardous reactions	: Vapours may form explosive mixture with air. No decomposition if stored and applied as directed.
Conditions to avoid	: Heat, flames and sparks. Extremes of temperature and direct sunlight.
Incompatible materials	: Oxidizing agents Acids
Hazardous decomposition products	: Carbon oxides Nitrogen oxides (NO _x)

SECTION 11. TOXICOLOGICAL INFORMATION

Potential Health Effects

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

Aggravated Medical Condition : None known.
Symptoms of Overexposure : Effects are dependent on exposure (dose, concentration, contact time).
Effects are immediate and delayed.
Symptoms may include blistering, irritation, burns, and pain.
Causes severe skin burns and eye damage.
Review section 2 of SDS to see all potential hazards.
Treat symptomatically. Symptoms may be delayed.

Carcinogenicity:

IARC No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

ACGIH Confirmed animal carcinogen with unknown relevance to humans
2-butoxyethanol 111-76-2

OSHA No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.

NTP No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Acute toxicity

Product:

Acute oral toxicity : Acute toxicity estimate : 3,230 mg/kg
Method: Calculation method

Acute inhalation toxicity : Acute toxicity estimate : 6 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist
Method: Calculation method

Acute dermal toxicity : Acute toxicity estimate : 4,197 mg/kg
Method: Calculation method

Components:

2-butoxyethanol:

Acute oral toxicity : LD50 Oral Rat: 880 mg/kg

Acute dermal toxicity : LD50 Dermal Rabbit: 1,060 mg/kg

2-aminoethanol:

Acute oral toxicity : LD50 Oral Mouse: 700 mg/kg
LD50 Oral Rat: 1,515 mg/kg

Acute inhalation toxicity : LC50 Mouse: > 1.21 mg/l

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

ethane-1,2-diol:

Acute oral toxicity

: Acute toxicity estimate Rat: 500 mg/kg
Method: Converted acute toxicity point estimate
Remarks: The acute toxicity estimate (ATE) value of 500 mg/kg has been assigned for GHS classification. LD50 values for oral toxicity on rats are reported in the literature to be > 4000 mg/kg, however rats can metabolize appreciable amounts of this chemical, while toxic effects on humans occur at much lower dosages.

Skin corrosion/irritation

Product:

Remarks: Extremely corrosive and destructive to tissue.

Serious eye damage/eye irritation

Product:

Remarks: Extremely corrosive and destructive to tissue.

Respiratory or skin sensitisation

No data available

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information

Product:

Remarks: No data available

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

Persistence and degradability

No data available

Bioaccumulative potential

Product:

Partition coefficient: n-octanol/water : Remarks: No data available

Components:

2-aminoethanol :

Partition coefficient: n-octanol/water : log Pow: -1.31

butane :

Partition coefficient: n-octanol/water : Pow: 2.89

ethane-1,2-diol :

Partition coefficient: n-octanol/water : Pow: 1.36

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

Remarks This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : Do not dispose of waste into sewer.
Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with local regulations.

Contaminated packaging : Empty remaining contents.
Dispose of as unused product.

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

Do not re-use empty containers.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
UN1950, Aerosols, flammable, 2.1, - Limited quantity

Transportation Regulation: IMDG (Vessel):
UN1950, AEROSOLS, 2.1, - Limited quantity

Transportation Regulation: IATA (Cargo Air):
UN1950, Aerosols, flammable, 2.1, - Limited quantity

Transportation Regulation: IATA (Passenger Air):
UN1950, Aerosols, flammable, 2.1, - Limited quantity

Transportation Regulation: TDG (Canada):
UN1950, AEROSOLS, FLAMMABLE, 2.1, - Limited quantity

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

TSCA list : No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

Components	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
ethane-1,2-diol	107-21-1	5000	*

*: Calculated RQ exceeds reasonably attainable upper limit.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Flammable (gases, aerosols, liquids, or solids)
Gases under pressure
Skin corrosion or irritation
Serious eye damage or eye irritation

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : The following components are subject to reporting levels established by SARA Title III, Section 313:

2-butoxyethanol	111-76-2	17 %
ethane-1,2-diol	107-21-1	2.388 %

California Prop. 65



WARNING: This product can expose you to chemicals including 2,2'-iminodiethanol, which is/are known to the State of California to cause cancer, and methanol, which is/are known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

The components of this product are reported in the following inventories:

TSCA On TSCA Inventory
DSL All components of this product are on the Canadian DSL

For information on the country notification status for other regions please contact the manufacturer's regulatory group.

Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SECTION 16. OTHER INFORMATION

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

Further information

NFPA:

HEALTH	3
FLAMMABILITY	4
INSTABILITY	0
SPECIAL HAZARD.	

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme

HMIS III:

HEALTH	3
FLAMMABILITY	4
PHYSICAL HAZARD	3

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA - GHS Label Information:

Hazard pictograms :



Signal word :

Hazard statements :

Precautionary statements :

Danger:

Extremely flammable aerosol. Contains gas under pressure; may explode if heated. Causes severe skin burns and eye damage.

Prevention: Keep away from heat/sparks/open flames/hot surfaces. No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Do not breathe dust or mist. Wash skin thoroughly after handling. Wear protective gloves/ protective clothing/ eye protection/ face protection.
Response: IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/show er. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Immediately call a POISON CENTER or doctor/ physician. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER/doctor. Wash contaminated clothing before reuse.
Storage: Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122

SAFETY DATA SHEET

ZEP HEAVY-DUTY BASEBOARD STRIPPER 20N18OZ_12CT

Version 2.1

Revision Date 10/01/2023

Print Date 10/09/2024

°F.

Disposal: Dispose of contents/container in accordance with local regulation.

Version:	2.1
Revision Date:	10/01/2023
Print Date:	10/09/2024

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.