

### **DIMENSIONAL SPECIFICATIONS**

---

#### **Overall Dimensions:**

Nominal Dimension: 42" x 24" x 29-1/2" (W-D-H)

Actual Dimension: 42-17/64" x 23-7/8" x 29-7/8" (W-D-H)

#### **Pedestals (Outside Dimensions with Drawer Front):**

Letter Width Return-14-7/8" x 22-3/4" x 15-1/8"

#### **Drawer (Inside Dimensions):**

Letter Width Return Box: 12-1/4" x 14-13/16" x 4-1/16" (W-D-H)

Letter Width Return File: 12-1/4" x 16-13/16" x 10-1/2" (W-D-H)

#### **Knee Space Between Pedestals:**

26-11/64" x 16-31/35 x 28-23/32" (W-D-H)

### **MATERIAL SPECIFICATIONS**

---

#### **Top:**

- 1-1/8" thick particleboard with melamine surface top and bottom, 2mm PVC edgebanding around all four edges.
- Top dimensions – 41-17/64" x 23-7/8" left side and 18" right side (W-D)

#### **End Panels:**

- 1-1/8" particleboard cores with melamine both front and back, .5mm PVC edgebanding the two side edges and .8mm (edge trim on bottom).
- End panel dimensions –23-7/8"x 28-1/8" (W-H)

#### **Full Height Skirt:**

- 3/4" particleboard cores with melamine both front and back
- Skirt dimensions- 41-3/32"x 28-7/32" (W-H)

#### **Inside Panel:**

- 3/4" particleboard with melamine both front and back.



## 10500 Series Model H105818L Technical Specifications

### Box Drawer Material:

- **FRONTS**-3/4" thick particleboard with melamine both front and back .5mm PVC edgbanding on both sides and top.
- **SIDES**-7/16" thick fiberboard, 3-5/8" high.
- **BACK**-7/16" thick fiberboard, 3-5/8" high.
- **BOTTOM**-3/16" thick printed hardboard.
- **SUBFRONT**-7/16" thick fiberboard, 3-5/8" high.
- **CONSTRUCTION**-Sides mortise/tenon into drawer front, stapled to back and subfront at corners. Bottom fits into slots on sides.

### File Drawer Material:

- **FRONTS**-3/4" thick particleboard with melamine both front and back .5mm edgbanding on both sides and top.
- **SIDES**-7/16" thick fiberboard, 9-1/2" high.
- **BACK**-7/16" thick fiberboard, 9-1/2" high.
- **BOTTOM**-3/16" thick printed hardboard.
- **SUBFRONT**-7/16" thick fiberboard, 9-1/2" high.
- **CONSTRUCTION**-Sides mortise/tenon into drawer front, stapled to back and subfront at corners. Bottom fits into slots on sides.

### Grommet:

- *Grommet Location:* 21-1/8" from the left edge of top, and 19-7/8" from the front edge of top.
- *Size:* DIA 3" THRU

### Hardware:

Hangrail Pack-262-4100

Hardware Pack-251-1365

Product Pack- 262-3530



## MODEL FEATURES

---

# 10500 Series Model H105818L Technical Specifications

- 9/32" Approach Side Top Overhang
- 3/4" Adjustable Glides
- 3/4" Extension Ball Bearing Box Drawer Slide
- Full Extension ball Bearing File Drawer Slide
- File Drawer: Letter and legal width side to side filing, letter width front to back filing. Hangrails are provided for all file drawers. Use Hanging folders with a maximum height of 9-3/4".
- 10500 Series Wood product meets and exceeds ISTA Shipping and ANSI/BIFMA X5.5 (latest Rev.) testing requirements for furniture.

**PARTICLEBOARD:** All particleboard is ANSI grade IM3 or better.

## CARTONING INFORMATION

---

**Carton-Outside Dimensions:** 52-13/16" x 31-3/8" x 3-9/16" (W-D-H)

**Cubes:** 20.5

**Carton #:** Top- 242-7531

Bottom- 242-7530

**Weight:** 134lb