

DIMENSIONAL SPECIFICATIONS

Overall Dimensions:

Nominal Dimension: 48" x 24" x 29-1/2" (W-D-H)

Actual Dimension: 47" x 23-7/8" x 29-1/8" (W-D-H)

Pedestals (Outside Dimensions with Drawer Fronts):

Letter Width Return: 14-7/8" x 22-3/4" x 27-15/16" (W-D-H)

Drawer (Inside Dimensions):

Letter Width Return File: 12-1/4" x 16-3/16" x 10-1/2" (W-D-H)

Letter Width Return Box: 12-1/4" x 16-3/16" x 4-1/16" (W-D-H)

Knee Space Between Pedestals:

32-11/64" x 22-53/64" x 28-7/32" (W-D-H)

MATERIAL SPECIFICATIONS

Top:

- 1-1/8" thick particleboard with Kraft backer bottom and high-pressure laminate (HPL) top cover.
- Top dimensions—47" x 23-7/8" (W-D)
- Top end caps: solid hardwood

End Panels:

- 1-1/8" thick particleboard with melamine surface back, and high-pressure laminate (HPL) surface top cover and .8 mm edge trim on the bottom.
- End panel dimensions —23-7/8" x 28-1/8" (W-H)

Full Height Skirt:

- 3/4" particleboard with melamine both front and back.
- Skirt dimensions- 48-3/32" x 28-7/32" (W-H)

Inside Panel:

- 3/4" particleboard with melamine both front and back.

Box Drawer Material:

- **FRONTS**-3/4" thick particleboard with melamine both front and back .5mm PVC edgebanding on both sides and top.
- **SIDES**-7/16" thick fiberboard, 3-5/8" high.
- **BACK** 7/16" thick fiberboard, 2-1/16" high.
- **BOTTOM**-3/16" thick printed hardboard.
- **SUBFRONT**-7/16" thick fiberboard, 3-5/8" high.
- **CONSTRUCTION**-Sides mortise/tenon into drawer front, stapled to back and subfront at corners. Bottom fits into slots on sides.

File Drawer Material:

- **FRONTS**-3/4" thick particleboard with melamine both front and back .5mm edgebanding on both sides and top.
- **SIDES**-7/16" thick fiberboard, 9-1/2" high.
- **BACK**-7/16" thick fiberboard, 9-1/2" high.
- **BOTTOM**-3/16" thick printed hardboard.
- **SUBFRONT**-7/16" thick fiberboard, 9-1/2" high.
- **CONSTRUCTION**-Sides mortise/tenon into drawer front, stapled to back and subfront at corners. Bottom fits into slots on sides.

Grommet:

- There is one grommet that is located in the back right-hand corner of the desk. It is rectangle in shape. And is 1-7/8" from the right-side of the desk and 16-7/8" from the front edge of the desk.
- Size: 3-1/4" x 1-7/8" (W-H)

Hardware:

Frame Pack-242-6772

Divider Pack-262-4002

Hangrail Pack-262-4100

Product Pack- 262-3147

Hardware Pack- 251-4400

MODEL FEATURES

- .625 Radius edge on 107 tops
- 3/4" Adjustable Glides
- Full Extension Ball Bearing File Drawer Slides.
- File drawers: Letter and legal width side-to-side and front to back filing. Hangrails are provided for all of the drawers. Use hanging folders with a maximum height of 9-3/8"



10700 Series H10716L Technical Specifications

- *** Return is for use with single pedestal desks or corner unit only. Not to be used freestanding
- **10700** Series wood produce meets or exceeds **ISTA** shipping and **ANSI/BIFMA X5.5** (latest Rev.) testing requirements for office furniture.
***Classical contemporary styling with hardwood accents.

PARTICLEBOARD: All particleboard is ANSI grade IM3 or better.

CARTONING INFORMATION

Carton-Outside Dimensions: 51-7/8" x 26-3/8" x 32" (W-D-H)

Cubes: 25.3

Carton #: 242-3050

Weight: 147lb

REVISIONS

1.1-Corrected carton size and cube. (1-19-04)