



KEY DIMENSIONS

- Heights:**
 - 2 drawer – 29"
 - 4 drawer – 52"
 - 5 drawer – 60"
- Width:**
 - Letter – 15"
 - Legal – 18-1/4"
- Depth:** 26-1/2"

Filing Capacity:
25" per drawer front to back filing

Features:

310 Series Vertical Files are available in a 2, 4 or 5 drawer configuration, in letter or legal width, and these cabinets are 26-1/2" deep. The five drawer unit uses slightly shorter drawer fronts, horizontal crossbars and kickplate to accommodate access to the top drawer.

Construction:

The case top has welded seams on the front corners and is welded to the back and sides. Vertical reinforcing channels are formed to add strength and welded to sides, two at the front and two at the rear. Formed horizontal crossbar dividers are welded in place to each side, between drawers. The single piece kickplate/corner gusset is secured to sides by welds and structural adhesive. A bottom rear reinforcing channel is welded to the back and to the sides. Both the kickplate and rear reinforcing channel wrap under the case for a sturdy construction.

QUICK REFERENCE TABLE - Actual Dimensions

Models	H312	H312C	H314	H314C	H315	H315C
Case Height	29"	29"	52"	52"	60"	60"
Case Width	14.9"	18.2"	14.9"	18.2"	14.9"	18.2"
Case Depth	26.6"	26.6"	26.6"	26.6"	26.6"	26.6"
Top Height	1.25"	1.25"	1.25"	1.25"	1.25"	1.25"
Drawer Front Height	11.4"	11.4"	11.4"	11.4"	11"	11"
Drawer Front Width	13.3"	16.6"	13.3"	16.6"	13.3"	16.6"
Drawer Divider Height	.5"	.5"	.5"	.5"	.25"	.25"
Kickplate Height	4.1"	4.1"	3.3"	3.3"	2.5"	2.5"
INSIDE DRAWER						
Height	10.7"	10.7"	10.7"	10.7"	10.3"	10.3"
Depth	25.5"	25.5"	25.5"	25.5"	25.5"	25.5"
Width	11.9"	14.9"	11.9"	14.9"	11.9"	14.9"
Load Capacity/drawer	57 lbs	71 lbs	57 lbs	71 lbs	57 lbs	71 lbs

Drawers feature a welded construction with high drawer sides, which accept hanging file folders without the need for hangrails. Sides are welded to drawer front, the bottom and the back. Drawer front includes a polypropylene plastic filler enclosing the thumb latch mechanism.

Drawer Function:

Drawers operate on three-part telescoping ball bearing slides with 100% drawer extension.

Hardware:

Includes a bright aluminum drawer pull, thumb latch button and label holder on each drawer front. Drawer pull is 1-1/8" deep x 4-1/4" wide, attached at a 4" span. The thumb latch is spring operated, and prevents drawers from opening without activating the mechanism to release the drawer. Label holder measures 3-7/16" W x 2" H overall, with a viewable area of 2-3/4" W x 1-1/4" H.

Locking:

The included core removable lock is located in the right front corner of the top. The lock utilizes a lock link which activates a one piece lock bar, engaging all drawers on the right side. HON "One Key" interchangeable cores may be ordered separately to key units alike.

Follower Block:

Positive locking follower with a spring loaded release latch, adjustable in 5/8" increments. Block is constructed of steel with two vertical ribs and a horizontal channel for added strength. Side arm guides are constructed of steel. Follower is either color matched to case, or is constructed of a pre-painted steel in the color of gray.



310 Vertical Files Technical Specifications

Finish:

Steel parts are finished with a baked enamel over a rust-inhibiting phosphate pre-treatment.

Shipping Information:

Files ship fully assembled in a full corrugated carton with inner-pack for protection.

Compliance:

Meets or exceeds applicable ANSI/BIFMA and ISTA Performance Standards.

Certified SCS Indoor Advantage™ Gold

Conforms to the BIFMA e3 Furniture Sustainability Standard level 2.

Models:	Description:
H312	2 Draw er, Letter Width
H312C	2 Draw er, Legal Width
H314	4 Draw er, Letter Width
H314C	4 Draw er, Legal Width
H315	5 Draw er, Letter Width
H315C	5 Draw er, Legal Width

The HON Company
200 Oak Street
Muscatine, IA 52761
800-833-3964
hon.com