

NEW



M18 FUEL™

DRIVEN TO OUTPERFORM.™



UP TO
700 FT-LBS
MAX FASTENING
TORQUE

UP TO
1100 FT-LBS
NUT-BUSTING
TORQUE

UP TO
2X
MORE
RUN-TIME

**1/2" High Torque Impact
Wrench with Friction Ring**

22UT67

**REDLITHIUM™
XC4.0**

1/2" HIGH TORQUE IMPACT WRENCH WITH FRICTION RING

M18 FUEL™

UP TO
700 FT-LBS
MAX FASTENING
TORQUE

UP TO
1100 FT-LBS
NUT-BUSTING
TORQUE

UP TO
2X
MORE
RUN-TIME



M18 FUEL™ 22UT67 vs COMPETITORS

Milwaukee® Milwaukee® Competitor 1 Competitor 2 Competitor 3 Competitor 4



22UT67



4LET4



Motor	POWERSTATE™ Brushless	4-Pole Neo	Air	Can	Can	Can
Impacts Per Minute	0 – 2,300	0 – 2,200	0 – 1,250	0 – 2,300	0 – 2,100	0 – 2,100
Max Fastening Torque	700 ft.-lbs.	450 ft.-lbs.	550 ft.-lbs.	650 ft.-lbs.	450 ft.-lbs.	500 ft.-lbs.
Nut-Busting Torque	1,100 ft.-lbs.	700 ft.-lbs.	1,100 ft.-lbs.	1,100 ft.-lbs.	700 ft.-lbs.	500 ft.-lbs.
Length	9"	8-7/8"	8-3/8"	9-1/2"	9-1/4"	9-1/4"
Drive-Control™	Yes	No	No	No	No	No
Variable Speed	Yes	Yes	Yes	Yes	Yes	Yes
LED Light	Yes	No	No	No	Yes	Yes
Powered By	REDLITHIUM™ XC4.0	REDLITHIUM™	Compressor	Li-ion	Li-ion	Li-ion

PROPRIETARY 2-MODE DRIVE CONTROL™

22UT67	MODE 1	MODE 2
No Load Speed (RPM / IPM)	0 – 325 / 0 – 450	0 – 1,700 / 0 – 2,300
Max Fastening Torque	100 ft.-lbs.	700 ft.-lbs.



M18 FUEL™ 1/2" High Torque Impact Wrench w/ Friction Ring (Tool-Only) 22UT66

Includes: 2763-20 M18 FUEL™ 1/2" High Torque Impact Wrench w/ Friction Ring



M18 FUEL™ 1/2" High Torque Impact Wrench w/ Friction Ring (Kit - 2 Batteries) 22UT67

Includes: 2763-20 M18 FUEL™ 1/2" High Torque Impact Wrench w/ Friction Ring, (2) M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Packs, M12™ & M18™ Multi-Voltage Charger, and Carrying Case

