


BREEZE HEADSET

Recommended for public safety markets, manufacturing,
all users in high noise environments.



Designed for less rigorous applications where an adjustable headband would not be necessary, the **Breeze** delivers comfortable, discreet two-way radio communications.

Mechanical Specifications:

- Temple pad axial pull off force: 20 lbs
- Cable pull from ear cup and PTT, axial: 20 lbs
- Cable pull from plug, axial: 40 lbs
- Cable flex from T module: 6,000 cycles
- Cable flex at plug: 25,000 cycles
- Microphone boom flex life @ +/- 60° bend: 4,500 cycles
- 24 month manufacturer's warranty

Electrical Specifications:

- Microphone sensitivity at 94dB SPL: -40 typical

Environmental Specifications:

- Operating temperature: -20° C to +60° C
- Storage temperature: -40° C to +80° C

Grainger Item #6XUA4/Mfr. Model #V4-BA2CS5
Grainger Item #6XTU0/Mfr. Model #V4-BA2MM5
Grainger Item #6XUD6/ Mfr. Model #V4-10374
Grainger Item #6XTP1/Mfr. Model #V4-BA2KB1
Grainger Item #6XTU9/Mfr. Model #V4-BA2MJ5
Grainger Item #6XTX0/Mfr. Model #V4-BA2MA1
Grainger Item #6XTZ3/Mfr. Model #V4-BA2VJ5
Grainger Item #6XTT4/Mfr. Model #V4-BA2MG5
Grainger Item #6XUC4/Mfr. Model #V4-BA2CM1