



SPECIFICATION SHEET

56-530



HI-PERFORMANCE NITRILE BY ATG®

- MaxiDry Plus by ATG®, ultra lightweight nitrile on fine gauge seamless knit nylon liner, palm & finger coated, gauntlet cuff, non-slip grip, 12-inch length.
- EN certified 100% low level chemical and oil repellent – EN 374-2
- Ultra thin design provides excellent comfort and flexibility along with maximum finger tip tactile sensitivity
- Exclusive GripTech® coating offers non-slip capabilities
- Unique wrist shape eliminates slippage in wrist area
- LiquiTech® Barrier Technology provides resistant to oils & liquids
- Silicone free

APPLICATIONS

- Offshore petroleum
- Engine and transmission assembly
- Handling small castings and other abrasive edged parts
- Light stamping in oily conditions

CARE INSTRUCTIONS

Use commercial laundry soap or detergent (do NOT use dry cleaning solutions) Wash in warm to medium hot water, do not exceed 104°F (40° C). Wash for 10 minutes and rinse in cold water. Repeat wash and rinse if soiling is especially heavy. Tumble dry - maximum temperature 140°F (60° C)

TECHNICAL DATA

MATERIAL	Nitrile, nylon, Lycra®				
COLOR	Shell: ■ Blue / Grip: ■ Black				
CUFF STYLE	Gauntlet cuff				
SIZES	S - XXL				
PACKAGING	12 pairs per dozen, 6 dozen per case				
CASE	20.0" x 11.8" x 10.8" / 50.8cm x 30.0cm x 27.4cm				
CASE WEIGHT (S-XXL)	S	M	L	XL	XXL
	15.4 lbs 7.0 kg	16.5 lbs 7.5 kg	17.6 lbs 8.0 kg	18.7 lbs 8.5 kg	19.8 lbs 9.0 kg
COO	Sri Lanka				
HARM CODE	6116.10.6500				

PERFORMANCE PROPERTIES

EN388: 4121	EN74-3:	40% Sodium Hydroxide - Level 6 / Methanol - Level 2 / 96% Sulphuric Acid - Level 1				
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

BARCODES

ITEM	BAG	DOZEN	CASE
■ 56-425/S	---	01616314079671	02616314079670
■ 56-425/M	---	01616314079664	02616314079663
■ 56-425/L	---	01616314079657	02616314079656
■ 56-425/XL	---	01616314079640	02616314079649
■ 56-425/XXL	---	01616314079633	02616314079632



DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	12.0 / 30.5	12.0 / 30.5	12.0 / 30.5	12.0 / 30.5	12.0 / 30.5
B	4.1 / 10.4	4.3 / 10.8	4.4 / 11.2	4.6 / 11.6	4.7 / 12.0

Thickness: 1.0mm/39.37 mil

