

# SSB-1900/NB

Drop Ceiling Adjustable Load Support,  
without 1900 Box




## GENERAL DESCRIPTION

The SSB-1900/NB is a rust resistant steel, adjustable, load bearing support without an electrical junction box.

## INTENDED USE - Indoor or Protected Outdoor Environment

<b>Installation</b>	Parallel to floor plane in a suspended ceiling structure; maximum span of 24" in one dimension.
---------------------	---




## JUNCTION BOX ACCESS

<b>All 4 Vertical Sides</b>	2x 1/2" k/o conduit 1x 1/2" / 3/4" eccentric k/o conduit
<b>Top Horizontal Surface</b>	3 x 1/2" k/o conduit 2x 1/2" / 3/4" eccentric k/o conduit

## MECHANICAL ATTACHMENT

<b>Bottom Horizontal</b>	2x 8-32 formed threads to attach 2-gang Surface adapter plate if required
<b>Tie-Offs</b>	4x Total, 1 each at end of bridge rail 2x Terminal plate



<p>Recommended construction sequences, installation instructions, and A&amp;E Specifications are available in various formats in the QUAM Architects' and Engineers' Resources section on the web at: <a href="http://www.QuamSpeakers.com">www.QuamSpeakers.com</a></p>			<p>QUAM-NICHOLS COMPANY, INC. 234 East Marquette Rd. Chicago, IL. 60637 Tel: 1-800-NEED-NOW (800-633-3669) Fax: 1-888-NEED-NOW (888-633-3669) e-mail: NeedNow@QNC.com <a href="http://www.QuamSpeakers.com">www.QuamSpeakers.com</a></p>
<p>© 2013 Quam-Nichols Company reserves the right to make changes and/or improvements to its products at any time and without notice.</p>			