



Quam

QH16T

PAGING HORN

Compression Type, Double Re-Entrant Horn Loudspeaker,
16W-25/70V Rotary Select Transformer

GENERAL DESCRIPTION

The QH16T is a compression type, double re-entrant horn loudspeaker with an integrated 16W-25/70V rotary select transformer and an adjustable mounting base. Tan, enamel finish.

INTENDED USE - Indoor or Protected Outdoor Environment

Program Material	Signal Tones, and Voice
Installation	Horizontal or Vertical Alignment


AUDIO SPECIFICATIONS

Speaker Type	Compression, Double Re-Entrant Horn
Average Sensitivity	110 dB SPL, 1W/ 1M
Loudspeaker Power Rating	16W RMS, EIA 426A Standard
Calculated Output	121 dB SPL, 16W/ 1M
Frequency Response	450 Hz - 15 kHz EIA 426A Standard
Nominal Coverage Angle	110° Included Angle, -6 dB / 2 kHz, Half space
Audio Connection	Screw Terminals
Transformer	25/70V 16W-5 Tap, Rotary Select (16W, 8W, 4W, 2W, 1W)



RECOMMENDED QUAM COMPONENTS

KIT# 104	Three (3) Conduit Entry Plates
-----------------	--------------------------------



<p>Recommended construction sequences, installation instructions, and A&E Specifications are available in various formats in the QUAM Architects' and Engineers' Resources section on the web at: www.QuamSpeakers.com</p>			<p>QUAM-NICHOLS COMPANY, INC. 234 East Marquette Rd. Chicago, IL. 60637 Tel: 1-800-NEED-NOW (800-633-3669) Fax: 1-888-NEED-NOW (888-633-3669) e-mail: NeedNow@QNC.com www.QuamSpeakers.com</p>
<p>© 2013 Quam-Nichols Company reserves the right to make changes and/or improvements to its products at any time and without notice.</p>			