

### SA270



- .27 Caliber Strip Tool
- Semi-Automatic
- Power Adjust
- .27 caliber 10-shot strip loads: 3 (Green), 4 (Yellow), 5 (Red)
- Weight: 5.45 lbs.
- Length: 15.3"
- Muzzle Bushing O.D.: 5/8"
- Maximum Pin Length: 3" straight pin
- 3 Year Warranty

#### ADVANTAGES

- Very Powerful
- Excellent balance—easy to use all day long
- Rubber grip on front barrel—eliminates pinched fingers and hands
- Twist lock front end—easy to clean
- Rugged polyamide housing—reduces heat transfer and maximizes operator comfort
- Soft, recoil-absorbing handle—for increased operator comfort

#### MOST COMMON FASTENERS

PIN #	SHANK LENGTH		MOST COMMON APPLICATION
	IN.	(MM)	
1516SDC (washed)	2-1/2	63.5	2" x 4" to concrete
1524SDP(washed)	3	76.2	2" x 4" to concrete
SP58TH	5/8	15.9	Track to steel

Fasteners start on page 34.

#### COMMON REPLACEMENT PARTS

- 27833 Piston with Ring

### COBRA



- .27 Caliber Strip Tool
- Semi-Automatic
- Economical
- .27 caliber 10-shot strip loads: 3 (Green), 4 (Yellow), 5 (Red)
- Weight: 4.5 lbs.
- Length: 13-1/4"
- Muzzle Bushing O.D.: 9/16"
- Maximum Pin Length: 2-1/2" (3" w/washer)

#### ADVANTAGES

- Semi-automatic .27-caliber tool — uses strip loads
- Padded recoil-absorbing handle—for greater operator comfort
- Fastens up to 3" standard Ramset drive pins and threaded studs—ideal for general construction applications
- Full one-year warranty

#### MOST COMMON FASTENERS

PIN #	SHANK LENGTH		MOST COMMON APPLICATION
	IN.	(MM)	
1524SDP (washed)	3	76.2	2" x 4" concrete
1524SDC (washed)	2-1/2	63.5	2" x 4" concrete
1506B	3/4	19.1	Drywall track to concrete

Fasteners start on page 34.

#### COMMON REPLACEMENT PARTS

- SC301200A Piston and Ring
- SC301012 Pawl (stop)