

2-DRAWER LETTER VERTICAL FIRE FILE - 25" DEEP

2T2500B/2T2500P/2T2500L

Schwab reference #: 2LFD-2500

P - Putty B - Black L - Light Gray



PROTECTION FEATURES:

- UL Classified Fire Endurance (1 hour at 1700° F)
 - Protects documents, records and valuables against catastrophic loss
- UL Classified Explosion Hazard Resistance
 - Design integrity protects contents against explosions in case of sudden exposure to intense heat

SECURITY FEATURES:

- Plunger key lock secures all drawers
- Drawer-specific "lock/unlock" provision
 - Provides additional security by isolating access to specific drawers

INTERIOR FEATURES:

- Lined interior conceals cabinet insulation and protects contents from unwanted dust
- Rugged suspension system design
 - Ensures smooth and easy drawer movement – even when fully loaded
- Drawer layout flexibility accommodates letter size hanging file folders



EXTERIOR FEATURES:

- Seamless design provides a sleek, attractive high-end appearance
- Easy-to-use recessed handles with label holders

Dimensions (H x W x D)	Interior Capacity	Ship. Weight
Exterior 27.6" x 16.6" x 25" 70.1 cm x 42.2 cm x 63.5 cm	2.9 cu. ft. 82 liters	220 lbs. 100 kg
Drawer Interior 10.3" x 12.1" x 20" 26.2 cm x 30.7 cm x 50.8 cm		

USA MADE UNSURPASSED PROTECTIVE STORAGE SINCE 1930

DIMENSIONAL ILLUSTRATIONS



SIDE VIEW