



SITOP PSU300M 48V/10A STABILIZED POWER SUPPLY
 INPUT: 400-500 V 3 AC OUTPUT: 48 V/10 A DC

Technical specifications	
Product	SITOP PSU300M
Power supply, type	48 V/10 A
Input	
Input	3-phase AC
Rated voltage value V_{in} rated	400 ... 500 V
Voltage range	320 ... 575 V
Wide-range input	Yes
Oversoltage resistance	$2.3 \times V_{in}$ rated, 1.3 ms
Mains buffering at I_{out} rated, min.	15 ms
Mains buffering	at $V_{in} = 400$ V
Rated line frequency	50 / 60 Hz
Rated line range	47 ... 63 Hz
Input current / at nominal level of the input voltage 400 V	1.2 A
Input current / at nominal level of the input voltage 500 V	1 A
Switch-on current limiting (+25 °C), max.	18 A
I^2t , max.	0.8 A ² ·s
Built-in incoming fuse	none
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 6 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)

Output	
Output	Controlled, isolated DC voltage
Rated voltage V_{out} DC	48 V
Total tolerance, static \pm	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	0.2 %
Residual ripple peak-peak, max.	100 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV
Adjustment range	42 ... 56 V
Product feature / output voltage adjustable	Yes
Output voltage setting	via potentiometer
• Note	max. 480 W
Status display	Green LED for 48 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 48 V OK
On/off behavior	No overshoot of V_{out} (soft start)
Startup delay, max.	2.5 s
Voltage rise, typ.	150 ms
Voltage increase time / of the output voltage / maximum	500 ms
Rated current value I_{out} rated	10 A
Current range	0 ... 10 A
• Note	7 A up to +70 °C
delivered active power / typ.	480 W
constant overload current / at short-circuit during run-up / typical	11 A
short-term overload current / at short-circuit during operation / typical	23 A
Duration of overloading ability for excess current / on short-circuiting during the operational phase	25 ms
Parallel switching for enhanced performance	Yes
• Note	switchable characteristic
Numbers of parallel switchable units for enhanced performance	2
Efficiency	
Efficiency at V_{out} rated, I_{out} rated, approx.	93 %
Power loss at V_{out} rated, I_{out} rated, approx.	36 W
Closed-loop control	
Dynamic mains compensation (V_{in} rated ± 15 %), max.	1 %
Dynamic load smoothing (I_{out} : 50/100/50 %), $U_{out} \pm$ typ.	2 %
Load step setting time 50 to 100%, typ.	2 ms
Load step setting time 100 to 50%, typ.	2 ms
Setting time / maximum	10 ms
Protection and monitoring	

Output overvoltage protection	Yes, according to EN 60950
Current limitation, typ.	11 A
Characteristic feature of the output / short-circuit protected	Yes
Short-circuit protection	Alternatively, constant current characteristic approx. 11 A or latching shutdown
Enduring short circuit current / Effective level / typical	11 A
• Note	overload capability 150 % I _{out} rated up to 5 s/min
Overload/short-circuit indicator	LED yellow for "overload", LED red for "latching shutdown"
Safety	
Primary/secondary isolation	Yes
Potential separation	Safety extra-low output voltage U _{out} acc. to EN 60950-1 and EN 50178
Protection class	Class I
stray current / maximum	3.5 mA
CE mark	Yes
UL/CSA approval	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
Explosion protection	ATEX (EX) II 3G Ex nA nC IIC T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01)
FM approval	-
CB approval	No
Marine approval	GL, ABS
Degree of protection (EN 60529)	IP20
EMC	
Emitted interference	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2
Noise immunity	EN 61000-6-2
Operating data	
Ambient temperature / in operation	-10 ... +70 °C
• Note	with natural convection
Ambient temperature / on transport	-40 ... +85 °C
Ambient temperature / in storage	-40 ... +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation
Mechanics	
Connection technology	screw-type terminals
Connections / Supply input	L1, L2, L3, PE: 1 screw terminal each for 0.5 ... 2.5 mm ² single-core/finely stranded
Connections / Output	+, -: 2 screw terminals each for 0.2 ... 4 mm ²
Connections / Auxiliary	13, 14 (alarm signal): 1 screw terminal each for 0.14 ... 1.5 mm ²
Width / of the housing	70 mm
Height / of the housing	125 mm

Depth / of the housing	125 mm
Installation width	70 mm
Mounting height	225 mm
Weight, approx.	1.2 kg
Product feature / of the housing / housing for side-by-side mounting	Yes
Type of mounting / wall mounting	No
Type of fixing / cap rail mounting	Yes
Type of mounting / S7-300 rail mounting	No
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
Mechanical accessories	Device identification label 20 mm x 7 mm, pastel-turquoise 3RT1900-1SB20
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

letzte Änderung:

Mar 22, 2013