

PRODUCT SPECIFICATION

Printed: 2/10/2014

Page 1 of 1

Catalog : S1295

Sodium Hydroxide, Low Chloride, Pellets, Reagent, ACS

CAS# : 1310-73-2

Formula : NaOH

Formula Weight : 40.00

Test	Limit	
	Min.	Max.
ASSAY (NaOH)	97.0 %	--
SODIUM CARBONATE (Na ₂ CO ₃)	--	1.0 %
CHLORIDE (Cl)	--	0.005 %
NITROGEN COMPOUNDS (as N)	--	0.001 %
PHOSPHATE (PO ₄)	--	0.001 %
SULFATE	--	0.003 %
HEAVY METALS (as Ag)	--	0.002 %
IRON (Fe)	--	0.001 %
MERCURY	--	0.1 PPM
NICKEL (Ni)	--	0.001 %
CALCIUM (Ca)	--	0.005 %
MAGNESIUM (Mg)	--	0.002 %
POTASSIUM (K)	--	0.02 %
IDENTIFICATION	TO PASS TEST	
RETEST DATE		