

PRODUCT SPECIFICATION

Printed: 2/10/2014

Catalog : S1349

Sodium Ascorbate, Powder, USP

CAS# : 134-03-2

Formula : C₆H₇NaO₆

Formula Weight : 198.11

Test

**Limit
Min. Max.**

	Limit Min. Max.
ASSAY (DRIED BASIS)	99.0 - 101.0%
pH OF A 10% SOLUTION	7.0 - 8.0
SPECIFIC ROTATION [α] _D	+103° TO +108°
LOSS ON DRYING	-- 0.25%
HEAVY METALS (as Pb)	-- 0.002%
IDENTIFICATION	-- TO PASS TEST
EXPIRATION DATE	
RESIDUAL SOLVENTS	TO PASS TEST