







Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
 	Toxic compound, do not ingest or inhale. Avoid all contact with this material. Stench -- do not inhale, use under a fume hood.	   

Section I. Chemical Product and Company Identification

Chemical Name	Diphenyl Diselenide		
Catalog Number	D2186	Supplier	TCI America 9211 N. Harborsgate St. Portland OR 1-800-423-8616
Synonym	Bis(phenylselenide)	<div style="border: 2px solid black; padding: 5px;"> In case of Emergency Call Chemtrec® (800) 424-9300 (U.S.) (703) 527-3887 (International) </div>	
Chemical Formula	C ₁₂ H ₁₀ Se ₂		
CAS Number	1666-13-3		

Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
Diphenyl Diselenide	1666-13-3	Min. 96.0 (GC)	Not available.	Mouse LD ₅₀ (intravenous) 28mg/kg

Section III. Hazards Identification

Acute Health Effects	<p>Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death.</p> <p>This material produces an irritating stench. Do not inhale and always use under a fume hood. Inhalation can result in inflammation of the respiratory system, headaches, nausea, and vomiting. Always cover all exposed skin with an impermeable layer and use proper eye protection. A OSHA/MSHA approved dust and vapor respirator is required when working with this material.</p> <p>Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.</p>
Chronic Health Effects	<p>CARCINOGENIC EFFECTS : Not available.</p> <p>MUTAGENIC EFFECTS : Not available.</p> <p>TERATOGENIC EFFECTS : Not available.</p> <p>DEVELOPMENTAL TOXICITY : Not available.</p> <p>Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.</p>

Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Skin Contact	In case of contact, immediately flush skin with plenty of water for at least 15 minutes while removing contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention immediately.
Inhalation	If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material has ingested; the absence of such signs, however, is not conclusive. SEEK IMMEDIATE MEDICAL ATTENTION in case of ingestion of a radioactive material.

Section V. Fire and Explosion Data

Flammability	May be combustible at high temperature.	Auto-Ignition	Not available.
Flash Points	Not available.	Flammable Limits	Not available.
Combustion Products	These products are toxic carbon oxides (CO, CO ₂), metallic oxides.		
Fire Hazards	Not available.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available.		
Fire Fighting Media and Instructions	SMALL FIRE: Use DRY chemical powder. LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet. Consult with local fire authorities before attempting large scale fire-fighting operations.		

Continued on Next Page

Emergency phone number (800) 424-9300

Section VI. Accidental Release Measures**Spill Cleanup Instructions**

Toxic material. Stench material.

Stop leak if without risk. DO NOT get water inside container. DO NOT touch spilled material. Use water spray to reduce vapors. Prevent entry into sewers, basements or confined areas; dike if needed. Eliminate all sources of ignition. Consult federal, state, and/or local authorities for assistance on disposal.

Section VII. Handling and Storage**Handling and Storage Information**

TOXIC. STENCH. Keep locked up.. Keep away from heat. Mechanical exhaust required. When not in use, tightly seal the container and store in a dry, cool place. Avoid excessive heat and light. DO NOT ingest. Do not breathe dust. Wear suitable protective clothing. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively.

Always store away from incompatible compounds such as oxidizing agents.

Section VIII. Exposure Controls/Personal Protection**Engineering Controls**

Use process enclosures, local exhaust ventilation, or other engineering controls to keep airborne levels below recommended exposure limits. If user operations generate dust, fume or mist, use ventilation to keep exposure to airborne contaminants below the exposure limit.

Personal Protection

Splash goggles. Lab coat. Dust respirator. Boots. Gloves. A MSHA/NIOSH approved respirator must be used to avoid inhalation of the product. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product.

**Exposure Limits**

Not available.

Section IX. Physical and Chemical Properties**Physical state @ 20°C**

Solid.

Solubility

Not available.

Specific Gravity

Not available.

Molecular Weight

312.13

Partition Coefficient

Not available.

Boiling Point

Not available.

Vapor Pressure

Not applicable.

Melting Point

61°C (141.8°F)

Vapor Density

Not available.

Refractive Index

Not available.

Volatility

Not available.

Critical Temperature

Not available.

Odor

Not available.

Viscosity

Not available.

Taste

Not available.

Section X. Stability and Reactivity Data**Stability**

This material is stable if stored under proper conditions. (See Section VII for instructions)

Conditions of Instability

Avoid excessive heat and light.

Incompatibilities

Reactive with oxidizing agents.

Section XI. Toxicological Information**RTECS Number**

JM9152500

Routes of Exposure

Eye Contact. Ingestion. Inhalation.

Toxicity Data

Mouse LD₅₀ (intravenous) 28mg/kg

Chronic Toxic Effects

CARCINOGENIC EFFECTS : Not available.

MUTAGENIC EFFECTS : Not available.

TERATOGENIC EFFECTS : Not available.

DEVELOPMENTAL TOXICITY : Not available.

Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.

Acute Toxic Effects

Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death.

This material produces an irritating stench. Do not inhale and always use under a fume hood. Inhalation can result in inflammation of the respiratory system, headaches, nausea, and vomiting. Always cover all exposed skin with an impermeable layer and use proper eye protection. A OSHA/MSHA approved dust and vapor respirator is required when working with this material.

Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

Section XII. Ecological Information

Ecotoxicity Not available.

Environmental Fate Not available.

Section XIII. Disposal Considerations

Waste Disposal Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.

Section XIV. Transport Information

DOT Classification CLASS 6.1: Toxic material.

PIN Number UN3283

Proper Shipping Name Selenium compound, n.o.s.

Packing Group (PG) III

DOT Pictograms

**Section XV. Other Regulatory Information and Pictograms**

TSCA Chemical Inventory (EPA) This compound is **ON** the EPA Toxic Substances Control Act (TSCA) inventory list.

WHMIS Classification (Canada) CLASS D-1B: Material causing immediate and serious toxic effects (TOXIC).
On NDSL.

EINECS Number (EEC) 216-780-2

EEC Risk Statements R23/24/25- Toxic by inhalation, in contact with skin and if swallowed.

Japanese Regulatory Data Not available.

Section XVI. Other Information**Version 1.0****Validated on 11/26/2001.****Printed 2/12/2005.****Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.

Printed 2/12/2005.