


CURRENT SETTING RANGE AMPS	TERMINAL TORQUE (LB. IN.)	CLASS 10 TRIP CODE (1)	CLASS 20 TRIP CODE (1)
90-150	-	369	569

NOTE: ALL LR9D SOLID STATE OVERLOAD RELAYS ARE RATED FOR 1,000 VOLTS.

(1) = SELECT DESIRED SUFFIX FOR COMPLETE CATALOG NUMBER

LUG PART NUMBERS		MAXIMUM CABLE SIZE	SUITABLE FOR OVERLOAD RELAY LR9-D5(1)
SINGLE LUG	SET OF SIX LUGS		
DZ2FG1	DZ2FG6	3/0	369, 569

NOTE: ALL OVERLOAD RELAYS DEPICTED DIRECTLY MOUNT TO CONTACTORS LC1-D115 THROUGH LC1-D150.



Catalog Number: LR9-D5(1)  
 Ratings: SEE CHART  
 UL File/CCN:  
 CSA File/Class:  
 Meets Standards: IEC 947-1, 255-8, 255-17 AND VDE 0060 EN 60947-1, 60947-4-1  
 Weight:  
 Wire Size: SEE CHART  
 Terminal torque: SEE CHART  
 Mounting Hwd: 35mm DIN rail, #10 screws

"THE SQUARE D COMPANY HAS PROPRIETARY RIGHTS TO THE INFORMATION CONTAINED HEREON. THIS INFORMATION REMAINS THE PROPERTY OF SQUARE D COMPANY AND MAY BE USED ONLY IN CONFORMANCE WITH INSTRUCTIONS ISSUED BY SQUARE D COMPANY. USER SHOULD VERIFY DRAWINGS ARE TO THE LATEST/CURRENT REVISION PRIOR TO INCORPORATING IN A DESIGN FILE."

**DO NOT SCALE DRAWING**  
 UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES

THIRD ANGLE PROJECTION  
 TOLERANCES UNLESS OTHERWISE SPECIFIED 2 PLACE DECIMALS ± .01

IEC OVERLOAD RELAY (F-LINE)  
 LR9-D5(1)

**SQUARE D COMPANY**

DWG# E0203901-01  
 NO.