



# Material Safety Data Sheet

| HAZARD WARNINGS   | RISK PHRASES                           | PROTECTIVE CLOTHING   |
|---|--|---|
|  | Highly toxic; do not ingest or inhale. |  |

## Section I. Chemical Product and Company Identification

|                  |   |                                 |   |
|------------------|---|---------------------------------|---|
| Chemical Name    | <b>Diclofenac Sodium Salt</b>                                     |                                 |   |
| Catalog Number   | D2508   | Supplier                        | TCI America<br>9211 N. Harborgate St.<br>Portland OR<br>1-800-423-8616                    |
| Synonym          | Orthophen; Sodium 2-(2,6-dichloroanilino)phenylacetate            |                                 |   |
| Chemical Formula | C <sub>14</sub> H <sub>10</sub> Cl <sub>2</sub> NNaO <sub>2</sub> |                                 |   |
| CAS Number       | 15307-79-6  | In case of<br>Emergency<br>Call | <b>Chemtrec®</b><br><b>(800) 424-9300 (U.S.)</b><br><b>(703) 527-3887 (International)</b> |

## Section II. Composition and Information on Ingredients

| Chemical Name          | CAS Number | Percent (%)            | TLV/PEL        | Toxicology Data  |
|------------------------|------------|------------------------|----------------|--|
| Diclofenac Sodium Salt | 15307-79-6 | Min. 98.0<br>(HPLC, N) | Not available. | Rat LD <sub>50</sub> (oral) 53mg/kg<br>Mouse LD <sub>50</sub> (oral) 95mg/kg<br>Woman TD <sub>Lo</sub> (oral) 270mg/kg |

## Section III. Hazards Identification

|                        |  |
|------------------------|--|
| Acute Health Effects   | Highly toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.  |
| Chronic Health Effects | <p><b>CARCINOGENIC EFFECTS</b> : Not available.</p> <p><b>MUTAGENIC EFFECTS</b> : Not available.</p> <p><b>TERATOGENIC EFFECTS</b> : Not available.</p> <p><b>DEVELOPMENTAL TOXICITY</b>: Reproductive: rat (oral) 1mg/kg. Duration: female 21 days of pregnancy. Specific developmental abnormalities- Cardio vascular (ciculatory) system.<br/>rat (oral) 6mg/kg. Duration: female 9-14 days of pregnancy.<br/>Effects on embryo or fetus- Fetotoxicity.<br/>Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.</p> |

## Section IV. First Aid Measures

|              |   |
|--------------|---|
| Eye Contact  | Check for and remove any contact lenses. IMMEDIATELY flush eyes with running water for at least 15 minutes. Keeping eyelids open. COLD water may be used. DO NOT use an eye ointment. Flush eyes with running water for a minimum of 15 minutes, occasionally lifting the upper eyelids. Seek medical attention. Treat symptomatically and supportively.  |
| Skin Contact | After contact with skin, wash immediately with plenty of water. Gently and thorough wash the contaminated skin with running water and non-abrasive soap. Be particularly careful to clean folds, crevices, creases and groin. COLD water may be used. Cover the irritated skin with an emollient. Seek medical attention. Treat symptomatically and supportively. Wash any contaminated clothing before reusing.  |
| Inhalation   | Evacuate the victim to a safe area as soon as possible. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, administer oxygen. If the victim is not breathing, perform artificial respiration. WARNING: It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation when the inhaled material is toxic, infectious or corrosive. Seek immediate medical attention and, if possible, show the chemical label. Treat symptomatically and supportively.  |
| Ingestion    | INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt, or waistband. If the victim is not breathing, administer artificial respiration. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive. Seek immediate medical attention and, if possible, show the chemical label. Treat symptomatically and supportively. |

## Section V. Fire and Explosion Data

|                     |   |                  |                |
|---------------------|---|------------------|----------------|
| Flammability        | May be combustible at high temperature.   | Auto-Ignition    | Not available. |
| Flash Points        | Not available.  | Flammable Limits | Not available. |
| Combustion Products | These products are toxic carbon oxides (CO, CO <sub>2</sub> ), nitrogen oxides (NO, NO <sub>2</sub> ), halogenated compounds, Some metallic oxides.<br>WARNING: Highly toxic HCl gas is produced during combustion.                                 |                  |                |
| Fire Hazards        | No specific information is available regarding the flammability of this compound in the presence of various materials.  |                  |                |
| Explosion Hazards   | Risks of explosion of the product in presence of mechanical impact: Not available.<br>Risks of explosion of the product in presence of static discharge: Not available.<br>No additional information is available regarding the risks of explosion. |                  |                |

Continued on Next Page

Emergency phone number (800) 424-9300

Fire Fighting Media  
and Instructions

SMALL FIRE: Use DRY chemicals, CO<sub>2</sub>, water spray or foam.  
LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet.

**Section VI. Accidental Release Measures**Spill Cleanup  
Instructions

Toxic material.  
In case of a spill and/or a leak, always shut off any sources of ignition, ventilate the area, and exercise caution. Use a shovel to put the material into a convenient waste disposal container. Consult federal, state, and/or local authorities for assistance on disposal.

**Section VII. Handling and Storage**Handling and Storage  
Information

TOXIC. Handle with caution and minimize exposure. Keep away from heat and sources of ignition. Mechanical exhaust required. When not in use, tightly seal the container and store in a dry, cool place. Avoid excessive heat and light. DO NOT ingest. DO NOT breathe dust. Wear suitable protective clothing. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively.  
Always store away from incompatible compounds such as oxidizing agents.

**Section VIII. Exposure Controls/Personal Protection**

## Engineering Controls

Use process enclosures, local exhaust ventilation, or other engineering controls to keep airborne levels below recommended exposure limits. If user operations generate dust, fume or mist, use ventilation to keep exposure to airborne contaminants below the exposure limit.

## Personal Protection

Splash goggles. Lab coat. Dust respirator. Boots. Gloves. Be sure to use a MSHA/NIOSH approved respirator or equivalent. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product.



## Exposure Limits

Not available.

**Section IX. Physical and Chemical Properties**

## Physical state @ 20°C

Solid.

## Solubility

Not available.

## Specific Gravity

Not available.

## Molecular Weight

318.13

## Partition Coefficient

Not available.

## Boiling Point

Not available.

## Vapor Pressure

Not available.

## Melting Point

283 to 285 °C (541.4 to 545 °F)

## Vapor Density

Not available.

## Refractive Index

Not available.

## Volatility

Not available.

## Critical Temperature

Not available.

## Odor

Not available.

## Viscosity

Not available.

## Taste

Not available.

**Section X. Stability and Reactivity Data**

## Stability

This material is stable if stored under proper conditions. (See Section VII for instructions)

## Conditions of Instability

Avoid excessive heat and light.

## Incompatibilities

Reactive with oxidizing agents.

**Section XI. Toxicological Information**

## RTECS Number

AG6330000

## Routes of Exposure

Eye contact. Ingestion. Inhalation.

## Toxicity Data

Rat LD<sub>50</sub> (oral) 53mg/kg  
Mouse LD<sub>50</sub> (oral) 95mg/kg  
Woman TD<sub>Lo</sub> (oral) 270mg/kg

## Chronic Toxic Effects

**CARCINOGENIC EFFECTS** : Not available.  
**MUTAGENIC EFFECTS** : Not available.  
**TERATOGENIC EFFECTS** : Not available.  
**DEVELOPMENTAL TOXICITY**: Reproductive: rat (oral) 1mg/kg. Duration: female 21 days of pregnancy.  
Specific developmental abnormalities- Cardio vascular (ciculatory) system.  
rat (oral) 6mg/kg. Duration: female 9-14 days of pregnancy.  
Effects on embryo or fetus- Fetotoxicity.  
Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.

## Acute Toxic Effects

Highly toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

**Section XII. Ecological Information**

|                    |                |
|--------------------|----------------|
| Ecotoxicity        | Not available. |
| Environmental Fate | Not available. |

**Section XIII. Disposal Considerations**

|                |   |
|----------------|---|
| Waste Disposal | Recycle to process, if possible. Consult your local or regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state, and local regulations when disposing of the substance. |
|----------------|---|

**Section XIV. Transport Information**

|                      |                                |
|----------------------|--------------------------------|
| DOT Classification   | DOT CLASS 6.1: Toxic material. |
| PIN Number           | UN2811                         |
| Proper Shipping Name | Toxic solid, organic, n.o.s.   |
| Packing Group (PG)   | III                            |
| DOT Pictograms       |                                |

**Section XV. Other Regulatory Information and Pictograms**

|                               |  |
|-------------------------------|--|
| TSCA Chemical Inventory (EPA) | This product is <b>NOT</b> on the EPA Toxic Substances Control Act (TSCA) inventory. The following notices are required by 40 CFR 720.36 (C) for those products not on the inventory list:<br>(i) These products are supplied solely for use in research and development by or under the supervision of a technically qualified individual as defined in 40 CFR 720.0 et sec.<br>(ii) The health risks of these products have not been fully determined. Any information that is or becomes available will be supplied on an MSDS sheet. |
| WHMIS Classification (Canada) | Not available.   |
| EINECS Number (EEC)           | 239-346-4  |
| EEC Risk Statements           | R23/24/25- Toxic by inhalation, in contact with skin and if swallowed.   |
| Japanese Regulatory Data      | Not available.   |

**Section XVI. Other Information**

**Version 1.0**  
**Validated on 4/8/1999.**  
**Printed 12/28/2011.**

**Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.