

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
  	<p>Toxic compound, do not ingest or inhale. Avoid all contact with this material.</p> <p>Irritating to skin, eyes, and the respiratory system.</p> <p>CARCINOGEN. MINIMIZE EXPOSURE.</p> <p>This compound is a skin sensitizer. Light sensitive.</p>	   

Section I. Chemical Product and Company Identification

Chemical Name	Acrylamide Monomer (for Electrophoresis)		
Catalog Number	A1132	Supplier	TCI America 9211 N. Harborside St. Portland OR 1-800-423-8616
Synonym	2-Propenamide (9 CI)		
Chemical Formula	CH ₂ :CHCONH ₂		
CAS Number	79-06-1	In case of Emergency Call	Chemtrec® (800) 424-9300 (U.S.) (703) 527-3887 (International)

Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
Acrylamide <small>Monomer (for Electrophoresis)</small>	79-06-1	Min. 98.0 (T)	This chemical is classified as a carcinogen. There is no acceptable exposure limit for a carcinogen.	Rat LD ₅₀ (oral) 124mg/kg Rat LD ₅₀ (dermal) 400mg/kg Rabbit LD ₅₀ (dermal) 1680µL/kg

Section III. Hazards Identification

Acute Health Effects	<p>Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death.</p> <p>Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering.</p> <p>Skin contact may result in sensitization. Always cover all exposed skin with an impermeable layer and use proper eye protection. A OSHA/MSHA approved dust and vapor respirator is required when working with this material.</p> <p>Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.</p>
Chronic Health Effects	<p>CARCINOGENIC EFFECTS : Not available.</p> <p>MUTAGENIC EFFECTS : Not available.</p> <p>TERATOGENIC EFFECTS : Tumorigenic Effects: Rat TD (oral) 1460 mg/kg 2 years continuous. Toxic Effects: Tumorigenic - Carcinogenic by RTECS criteria. Brain and Coverings - Tumors. Skin and Appendages - Tumors. Rat TDLo (oral) 1456 mg/kg/2 years continuous. Toxic Effects: Tumorigenic - Carcinogenic by RTECS criteria. Tumorigenic Effects - Testicular tumors. Mouse TDLo (intraperitoneal) 24mg/kg 8 weeks, intermittent. Toxic Effects: Tumorigenic - Neoplastic by RTECS criteria. Lung, Thorax, or Respiration - Tumors.</p> <p>DEVELOPMENTAL TOXICITY Reproductive Effects. Rat TDLo (intraperitoneal) 400mg/kg, male 8 days prior to mating. Toxic Effects: Effects on Embryo or Fetus - Fetotoxicity. Effects on Newborn - Behavioral. Rat TDLo (oral) 560 mg/kg, female 6-21 days of pregnancy and 10 days after birth. Toxic Effects: Maternal Effects - Parturition. Effects on Newborn - Stillbirth. Effects on Newborn - Viability index. Mouse TDLo (oral) 95 gm/kg, male 4 weeks prior to mating. Toxic Effects: Paternal Effects - Spermatogenesis. Effects on Fertility - Male fertility index. Effects on Fertility - post-implantation mortality. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.</p>

Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Skin Contact	In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention.
Inhalation	If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive. SEEK IMMEDIATE MEDICAL ATTENTION in case of ingestion of a radioactive material.

Section V. Fire and Explosion Data

Flammability	May be combustible at high temperature.	Auto-Ignition	Not available.
Flash Points	Not available.	Flammable Limits	Not available.
Combustion Products	These products are toxic carbon oxides (CO, CO ₂), nitrogen oxides (NO, NO ₂), ammonia.		
Fire Hazards	Not available.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available.		
Fire Fighting Media and Instructions	SMALL FIRE: Use DRY chemical powder. LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet. Consult with local fire authorities before attempting large scale fire-fighting operations.		

Section VI. Accidental Release Measures

Spill Cleanup Instructions	Toxic material. Irritating material. Carcinogenic material. Light-sensitive material. Sensitizing material. Stop leak if without risk. DO NOT get water inside container. DO NOT touch spilled material. Use water spray to reduce vapors. Prevent entry into sewers, basements or confined areas; dike if needed. Eliminate all sources of ignition. Consult federal, state, and/or local authorities for assistance on disposal.
----------------------------	--

Section VII. Handling and Storage

Handling and Storage Information	TOXIC. IRRITANT. LIGHT-SENSITIVE. CARCINOGEN. SENSITIZER. Keep locked up.. Keep away from heat. Mechanical exhaust required. When not in use, tightly seal the container and store in a dry, cool place. Avoid excessive heat and light. DO NOT ingest. Do not breathe dust. Wear suitable protective clothing. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively. Always store away from incompatible compounds such as oxidizing agents, reducing agents, acids, alkalis (bases).
----------------------------------	---

Section VIII. Exposure Controls/Personal Protection

Engineering Controls	Use process enclosures, local exhaust ventilation, or other engineering controls to keep airborne levels below recommended exposure limits. If user operations generate dust, fume or mist, use ventilation to keep exposure to airborne contaminants below the exposure limit.
Personal Protection	Splash goggles. Lab coat. Dust respirator. Boots. Gloves. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product. Be sure to use a MSHA/NIOSH approved respirator or equivalent.
	
Exposure Limits	This chemical is classified as a carcinogen. There is no acceptable exposure limit for a carcinogen.

Section IX. Physical and Chemical Properties

Physical state @ 20°C	Solid. (White crystalline chunks)	Solubility	Soluble in ether. 215.5 g/100 ml water, 155 g/100 ml methanol, 63.1 g/100 ml acetone, 12.6 g/100 ml ethyl acetate, 2.66 g/100 ml chloroform, 0.346 g/100 ml benzene, 0.0068 g/100 ml heptane, 86.2 g/100 ml ethanol; at 30°C.
Specific Gravity	1.122 @ 30°C (water=1)	Partition Coefficient	Not available.
Molecular Weight	71.08	Vapor Pressure	1.6 mm Hg @ 84.5°C
Boiling Point	125°C (257°F) @ 25 mm Hg	Vapor Density	2.45 (Air = 1)
Melting Point	84 to 86°C (183.2 to 186.8°F)	Volatility	Not available.
Refractive Index	Not available.	Odor	Odorless.
Critical Temperature	Not available.	Taste	Not available.
Viscosity	Not available.		

Continued on Next Page

Emergency phone number (800) 424-9300

Section X. Stability and Reactivity Data

Stability	This material is stable if stored under proper conditions. (See Section VII for instructions)
Conditions of Instability	Avoid excessive heat and light. Do not heat over 50°C. May polymerize on exposure to light.
Incompatibilities	Reactive with oxidizing agents, reducing agents, acids, alkalis (bases), iron, iron salts, copper, aluminum, brass, free radical initiators, air.

Section XI. Toxicological Information

RTECS Number	AS3325000
Routes of Exposure	Eye Contact. Ingestion. inhalation. Skin contact.
Toxicity Data	Rat LD ₅₀ (oral) 124mg/kg Rat LD ₅₀ (dermal) 400mg/kg Rabbit LD ₅₀ (dermal) 1680µL/kg
Chronic Toxic Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Tumorigenic Effects: Rat TD (oral) 1460 mg/kg 2 years continuous. Toxic Effects: Tumorigenic - Carcinogenic by RTECS criteria. Brain and Coverings - Tumors. Skin and Appendages - Tumors. Rat TDLo (oral) 1456 mg/kg/2 years continuous. Toxic Effects: Tumorigenic - Carcinogenic by RTECS criteria. Tumorigenic Effects - Testicular tumors. Mouse TDLo (intraperitoneal) 24mg/kg 8 weeks, intermittent. Toxic Effects: Tumorigenic - Neoplastic by RTECS criteria. Lung, Thorax, or Respiration - Tumors. DEVELOPMENTAL TOXICITY Reproductive Effects. Rat TDLo (intraperitoneal) 400mg/kg, male 8 days prior to mating. Toxic Effects: Effects on Embryo or Fetus - Fetotoxicity. Effects on Newborn - Behavioral. Rat TDLo (oral) 560 mg/kg, female 6-21 days of pregnancy and 10 days after birth. Toxic Effects: Maternal Effects - Paturition. Effects on Newborn - Stillbirth. Effects on Newborn - Viability index. Mouse TDLo (oral) 95 gm/kg, male 4 weeks prior to mating. Toxic Effects: Paternal Effects - Spermatogenesis. Effects on Fertility - Male fertility index. Effects on Fertility - post-implantation mortality. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.
Acute Toxic Effects	Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Skin contact may result in sensitization. Always cover all exposed skin with an impermeable layer and use proper eye protection. A OSHA/MSHA approved dust and vapor respirator is required when working with this material. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

Section XII. Ecological Information

Ecotoxicity	Not available.
Environmental Fate	Acrylamide may be released into the environment primarily in wastewater during its production and use in the manufacture of polyacrylamides and other polymers. Other releases may result from the disposal of the solid monomer on land or from leaching of residual monomer from polyacrylamides. If released on land, acrylamide would be expected to leach readily into the ground and biodegrade within a few weeks based on experimental data. If released into water, it should biodegrade in approximately 8 to 12 days. Bioconcentration in fish and adsorption to sediment should not be significant. In the atmosphere, the vapor phase chemical should react with photochemically produced hydroxyl radicals (half-life 6.6 hr) and be washed out by rain. Human exposure will be primarily occupational via dermal contact and inhalation, although exposure to the general public has resulted from the leaching of the acrylamide monomer from polyacrylamide flocculants used in water treatment.

Section XIII. Disposal Considerations

Waste Disposal	Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.
----------------	---

Section XIV. Transport Information

DOT Classification	CLASS 6.1: Poisonous material.
PIN Number	UN2074
Proper Shipping Name	Acrylamide
Packing Group (PG)	III
DOT Pictograms	

**Section XV. Other Regulatory Information and Pictograms**

TSCA Chemical Inventory (EPA)	This compound is ON the EPA Toxic Substances Control Act (TSCA) inventory list.
WHMIS Classification (Canada)	CLASS D-1B: Material causing immediate and serious toxic effects (TOXIC).
EINECS Number (EEC)	201-173-7
EEC Risk Statements	R23/24/25- Toxic by inhalation, in contact with skin and if swallowed. R36/37/38- Irritating to eyes, respiratory system and skin. R42/43- May cause sensitization by inhalation and skin contact. R45- May cause cancer.
Japanese Regulatory Data	Not available.

Section XVI. Other Information

Version 1.0
Validated on 12/13/2001.
Printed 1/17/2005.

Notice to Reader

TCl laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, household, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.