

Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
 	Flammable material; avoid heat and sources of ignition. Harmful compound, minimize exposure. Irritating to skin, eyes, and the respiratory system. Readily absorbed through skin.	   

Section I. Chemical Product and Company Identification

Chemical Name	2-Hexanone		
Catalog Number	H0114	Supplier	TGI America 9211 N. Harbortgate St. Portland OR 1-800-423-8616
Synonym	Methyl n-Butyl Ketone		
Chemical Formula	CH ₃ (CH ₂) ₃ COCH ₃		
CAS Number	591-78-6	In case of Emergency Call	Chemtrec® (800) 424-9300 (U.S.) (703) 527-3887 (International)

Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
2-Hexanone	591-78-6	Min. 98.0 (GC)	Not available.	Rat LD ₅₀ (oral) 2590 mg/kg Rabbit LD ₅₀ (dermal) 4800 mg/kg Rat LC ₅₀ (inhalation) 8000 ppm/4H

Section III. Hazards Identification

Acute Health Effects	Harmful if ingested or inhaled. Minimize exposure to this material. Severe overexposure can result in injury or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Readily absorbed through skin. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.
Chronic Health Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Not available. DEVELOPMENTAL TOXICITY : Reproductive Effects. Rat TCLo Inhalation 1000 ppm/6H, female 1-21 days of pregnancy TOXIC Effects: Specific Developmental Abnormalities - Gastrointestinal system Specific Developmental Abnormalities - Urogenital system Rat TCLo Inhalation 2000 ppm/6H, female 1-21 days of pregnancy TOXIC Effects: Effects on Newborn - Live birth index Effects on Newborn - Growth statistics Effects on Newborn - Behavioral Rat TCLo Inhalation 2045 mg/m ³ , female 1-22 days of pregnancy TOXIC Effects: Effects on Fertility - Litter size Effects on Newborn - Growth statistics Effects on Newborn - Behavioral

Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Skin Contact	In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention.
Inhalation	If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive.

Section V. Fire and Explosion Data			
Flammability	Flammable.	Auto-Ignition	423 °C (793.4 °F)
Flash Points	25 °C (77 °F).	Flammable Limits	LOWER: 1.2% UPPER: 8%
Combustion Products	These products are toxic carbon oxides (CO, CO ₂).		
Fire Hazards	Not available.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available.		
Fire Fighting Media and Instructions	Flammable liquid. SMALL FIRE: Use DRY chemical powder. LARGE FIRE: Use alcohol foam, water spray or fog. Cool containing vessels with water jet in order to prevent pressure build-up, autoignition or explosion. Consult with local fire authorities before attempting large scale fire-fighting operations.		

Section VI. Accidental Release Measures	
Spill Cleanup Instructions	Flammable liquid. Harmful material. Irritating material. Readily absorbed through skin. Keep away from heat. Mechanical exhaust required. Stop leak if without risk. Absorb with DRY earth, sand or other non-combustible material. DO NOT touch spilled material. Prevent entry into sewers, basements or confined areas; dike if needed. Consult federal, state, and/or local authorities for assistance on disposal.

Section VII. Handling and Storage	
Handling and Storage Information	FLAMMABLE. HARMFUL. IRRITANT. READILY ABSORBED THROUGH SKIN. Keep away from heat. Mechanical exhaust required. Avoid excessive heat and light. Do not breathe gas/fumes/ vapor/spray. Always store away from incompatible compounds such as oxidizing agents, alkalis (bases).

Section VIII. Exposure Controls/Personal Protection	
Engineering Controls	Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value. Ensure that eyewash station and safety shower is proximal to the work-station location.
Personal Protection	Splash goggles. Lab coat. Vapor respirator. Boots. Gloves. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product. Be sure to use a MSHA/NIOSH approved respirator or equivalent.
	
Exposure Limits	Not available.

Section IX. Physical and Chemical Properties			
Physical state @ 20 °C	Liquid. (Clear, Colorless-Light Yellow.)	Solubility	Soluble in Alcohol, Ether, Acetone. Slightly soluble in Water.
Specific Gravity	0.81(water=1)		
Molecular Weight	100.16	Partition Coefficient	Not available.
Boiling Point	126 to 128 °C (258.8 to 262.4 °F)	Vapor Pressure	0.36 kPa (@ 20 °C)
Melting Point	-57 °C (-70.6 °F)	Vapor Density	3.5 (Air = 1)
Refractive Index	1.399 - 1.403	Volatility	Not available.
Critical Temperature	Not available.	Odor	Characteristic.
Viscosity	Not available.	Taste	Not available.

Section X. Stability and Reactivity Data	
Stability	This material is stable if stored under proper conditions. (See Section VII for instructions)
Conditions of Instability	Avoid excessive heat and light.
Incompatibilities	Reactive with oxidizing agents, strong alkalis (bases).

Section XI. Toxicological Information

RTECS Number	MP1400000
Routes of Exposure	Eye Contact. Ingestion. Inhalation.
Toxicity Data	Rat LD ₅₀ (oral) 2590 mg/kg Rabbit LD ₅₀ (dermal) 4800 mg/kg Rat LC ₅₀ (inhalation) 8000 ppm/4H
Chronic Toxic Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Not available. DEVELOPMENTAL TOXICITY : Reproductive Effects. Rat TCLo Inhalation 1000 ppm/6H, female 1-21 days of pregnancy TOXIC Effects: Specific Developmental Abnormalities - Gastrointestinal system Specific Developmental Abnormalities - Urogenital system Rat TCLo Inhalation 2000 ppm/6H, female 1-21 days of pregnancy TOXIC Effects: Effects on Newborn - Live birth index Effects on Newborn - Growth statistics Effects on Newborn - Behavioral Rat TCLo Inhalation 2045 mg/m ³ , female 1-22 days of pregnancy TOXIC Effects: Effects on Fertility - Litter size Effects on Newborn - Growth statistics Effects on Newborn - Behavioral
Acute Toxic Effects	Harmful if ingested or inhaled. Minimize exposure to this material. Severe overexposure can result in injury or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Readily absorbed through skin. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

Section XII. Ecological Information

Ecotoxicity	Not available.
Environmental Fate	2-Hexanone's production and use as a solvent for a wide variety of materials including lacquers, resins, oils, nitrocellulose, acrylates, vinyl, and alkyd coatings will result in its release to the environment through various waste streams. Based on an experimental vapor pressure of 11.6 mm Hg at 25 deg C, 2-hexanone is expected to exist solely as a vapor in the ambient atmosphere. Vapor-phase 2-hexanone is degraded in the atmosphere by reaction with photochemically-produced hydroxyl radicals with an estimated atmospheric half-life of about 2 days. 2-Hexanone is expected to have high mobility in soils based upon an estimated Koc value of 134. Volatilization from dry soil surfaces is expected based upon the vapor pressure of this compound. Volatilization from moist soil surfaces is also expected based upon an estimated Henry's Law constant of 9.3X10 ⁻⁵ atm-cu m/mol. This compound is expected to biodegrade under both aerobic and anaerobic conditions. In water, 2-hexanone is not expected to adsorb to suspended solids or sediment based upon its estimated Koc value. This compound is expected to volatilize from water surfaces given its estimated Henry's Law constant. Estimated half-lives for a model river and model lake are 12 and 164 hours, respectively. Bioconcentration in aquatic organisms is considered low based upon the estimated BCF value of 7. Occupational exposure may be through inhalation and dermal contact with this compound at workplaces where 2-hexanone is produced or used. The general population may be exposed to 2-hexanone via inhalation of ambient air and the ingestion of food and drinking water, containing 2-hexanone.

Section XIII. Disposal Considerations

Waste Disposal	Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.
----------------	---

Section XIV. Transport Information

DOT Classification	DOT CLASS 3: Flammable liquid
PIN Number	UN1224
Proper Shipping Name	Ketones, liquid, n.o.s.
Packing Group (PG)	III
DOT Pictograms	

Section XV. Other Regulatory Information and Pictograms

TSCA Chemical Inventory (EPA)	This compound is ON the EPA Toxic Substances Control Act (TSCA) inventory list.
WHMIS Classification (Canada)	On DSL
EINECS Number (EEC)	209-731-1
EEC Risk Statements	R10- Flammable. R18- In use, may form flammable/explosive vapor-air mixture. R20/21/22- Harmful by inhalation, in contact with skin and if swallowed. R36/37/38- Irritating to eyes, respiratory system and skin.
Japanese Regulatory Data	ENCS No. 2-542

Section XVI. Other Information

Version 1.0
Validated on 4/4/2006.
Printed 4/4/2006.

Notice to Reader

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.