

# Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
 	<b>Toxic compound, do not ingest or inhale. Avoid all contact with this material.</b> Irritating to skin, eyes, and the respiratory system.	   

## Section I. Chemical Product and Company Identification

Chemical Name	<b>Tetraethylthiuram Disulfide</b>		
Catalog Number	B0479	Supplier	TCl America 9211 N. Harborgate St. Portland OR 1-800-423-8616
Synonym	Bis(diethylthiocarbamyl)Disulfide; Disulfiram		
Chemical Formula	[(C <sub>2</sub> H <sub>5</sub> ) <sub>2</sub> NCSS] <sub>2</sub>		
CAS Number	97-77-8	In case of Emergency Call	<b>Chemtrec®</b> <b>(800) 424-9300 (U.S.)</b> <b>(703) 527-3887 (International)</b>

## Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
Tetraethylthiuram Disulfide	97-77-8	Min. 97.0 (T)	Not available.	Rat LD <sub>50</sub> (oral) 500mg/kg Rabbit LD <sub>50</sub> (oral) 1800mg/kg Mouse LD <sub>50</sub> (intraperitoneal) 75mg/kg

## Section III. Hazards Identification

Acute Health Effects	Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.
Chronic Health Effects	<b>CARCINOGENIC EFFECTS</b> : Not available. <b>MUTAGENIC EFFECTS</b> : Not available. <b>TERATOGENIC EFFECTS</b> : Tumorigenic: mouse (oral) 35000mg/kg/ 78 weeks intermittent. Tumorigenic- Neoplastic by RTECS criteria. mouse (subcutaneous) 1000mg/kg. Tumorigenic- Neoplastic by RTECS criteria. <b>DEVELOPMENTAL TOXICITY</b> Reproductive: rat (oral) 310mg/kg. Duration: male 31 days prior to mating. Paternal effects- Testes, epididymis, sperm duct. rat (oral) 5000mg/kg. Duration: female 3-12 days of pregnancy. Effects on fertility- Post-implantation mortality. Effects on embryo or fetus- Fetotoxicity. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.

## Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. IMMEDIATELY flush eyes with running water for at least 15 minutes. Keeping eyelids open. COLD water may be used. DO NOT use an eye ointment. Flush eyes with running water for a minimum of 15 minutes, occasionally lifting the upper eyelids. Seek medical attention. Treat symptomatically and supportively.
Skin Contact	After contact with skin, wash immediately with plenty of water. Gently and thorough wash the contaminated skin with running water and non-abrasive soap. Be particularly careful to clean folds, crevices, creases and groin. COLD water may be used. Cover the irritated skin with an emollient. Seek medical attention. Treat symptomatically and supportively. Wash any contaminated clothing before reusing.
Inhalation	Evacuate the victim to a safe area as soon as possible. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, administer oxygen. If the victim is not breathing, perform artificial respiration. WARNING: It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation when the inhaled material is toxic, infectious or corrosive. Seek immediate medical attention and, if possible, show the chemical label. Treat symptomatically and supportively.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt, or waistband. If the victim is not breathing, administer artificial respiration. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive. Seek immediate medical attention and, if possible, show the chemical label. Treat symptomatically and supportively.

**Section V. Fire and Explosion Data**

Flammability	May be combustible at high temperature.	Auto-Ignition	Not available.
Flash Points	Not available.	Flammable Limits	Not available.
Combustion Products	These products are toxic carbon oxides (CO, CO <sub>2</sub> ), nitrogen oxides (NO, NO <sub>2</sub> ), sulfur oxides (SO <sub>2</sub> , SO <sub>3</sub> ...).		
Fire Hazards	No specific information is available regarding the flammability of this compound in the presence of various materials.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available. No additional information is available regarding the risks of explosion.		
Fire Fighting Media and Instructions	SMALL FIRE: Use DRY chemicals, CO <sub>2</sub> , water spray or foam. LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet.		

**Section VI. Accidental Release Measures**

Spill Cleanup Instructions	Toxic material. Irritating material. In case of a spill and/or a leak, always shut off any sources of ignition, ventilate the area, and exercise caution. Use a shovel to put the material into a convenient waste disposal container. Consult federal, state, and/or local authorities for assistance on disposal.
----------------------------	--

**Section VII. Handling and Storage**

Handling and Storage Information	TOXIC. IRRITANT. Handle with caution and minimize exposure. Keep away from heat and sources of ignition. Mechanical exhaust required. When not in use, tightly seal the container and store in a dry, cool place. Avoid excessive heat and light. DO NOT ingest. DO NOT breathe dust. Wear suitable protective clothing. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively. Always store away from incompatible compounds such as oxidizing agents.
----------------------------------	--

**Section VIII. Exposure Controls/Personal Protection**

Engineering Controls	Use process enclosures, local exhaust ventilation, or other engineering controls to keep airborne levels below recommended exposure limits. If user operations generate dust, fume or mist, use ventilation to keep exposure to airborne contaminants below the exposure limit.
Personal Protection	Splash goggles. Lab coat. Dust respirator. Boots. Gloves. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product. Be sure to use a MSHA/NIOSH approved respirator or equivalent.
	
Exposure Limits	Not available.

**Section IX. Physical and Chemical Properties**

Physical state @ 20°C	Powder.	Solubility	Practically insoluble in water. Soluble in alcohol, acetone, carbon disulfide. Slightly soluble in light petroleum.
Specific Gravity	1.30	Partition Coefficient	Not available.
Molecular Weight	296.52	Vapor Pressure	Not available.
Boiling Point	Not available.	Vapor Density	Not available.
Melting Point	70°C (158°F)	Volatility	Not available.
Refractive Index	Not available.	Odor	Slight odor.
Critical Temperature	Not available.	Taste	Slightly bitter taste.
Viscosity	Not available.		

**Section X. Stability and Reactivity Data**

Stability	This material is stable if stored under proper conditions. (See Section VII for instructions)
Conditions of Instability	Avoid excessive heat and light.
Incompatibilities	Reactive with oxidizing agents.

**Section XI. Toxicological Information**

RTECS Number	JO1225000
Routes of Exposure	Eye contact. Ingestion. Inhalation. Skin contact.
Toxicity Data	Rat LD <sub>50</sub> (oral) 500mg/kg Rabbit LD <sub>50</sub> (oral) 1800mg/kg Mouse LD <sub>50</sub> (intraperitoneal) 75mg/kg
Chronic Toxic Effects	<b>CARCINOGENIC EFFECTS</b> : Not available. <b>MUTAGENIC EFFECTS</b> : Not available. <b>TERATOGENIC EFFECTS</b> : Tumorigenic: mouse (oral) 35000mg/kg/ 78 weeks intermittent. Tumorigenic- Neoplastic by RTECS criteria. mouse (subcutaneous) 1000mg/kg. Tumorigenic- Neoplastic by RTECS criteria. <b>DEVELOPMENTAL TOXICITY</b> Reproductive: rat (oral) 310mg/kg. Duration: male 31 days prior to mating. Paternal effects- Testes, epididymis, sperm duct. rat (oral) 5000mg/kg. Duration: female 3-12 days of pregnancy. Effects on fertility- Post-implantation mortality. Effects on embryo or fetus- Fetotoxicity. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.
Acute Toxic Effects	Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

**Section XII. Ecological Information**

Ecotoxicity	Not available.
Environmental Fate	Disulfiram may be released to the environment as a result of its manufacture and use as a rubber accelerator and as a drug for chronic alcoholism. It will hydrolyze in water and moist soil and hydrolysis will increase with pH. Based on data for disulfiram's methyl analog, thiram, its half-life in water should be approximately 5 days at pH 7. It should also photodegrade in air, surface water, or on the soil surface. It is expected to adsorb strongly to soil and sediment. Disulfiram's biodegradability is unknown. Bioconcentration in aquatic organisms should be low to moderate. Volatilization will not be significant and it will not partition to the atmosphere. If released in the atmosphere as an aerosol or attached to particulate matter, it will be removed by gravitational settling. Vapor-phase disulfiram would react with photochemically-produced hydroxyl radicals (half-life 0.045 days). Exposure to disulfiram will be primarily occupational via dermal contact and possibly inhalation of aerosols.

**Section XIII. Disposal Considerations**

Waste Disposal	Recycle to process, if possible. Consult your local or regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state, and local regulations when disposing of the substance.
----------------	---

**Section XIV. Transport Information**

DOT Classification	Not a DOT controlled material (United States).
PIN Number	Not applicable.
Proper Shipping Name	Not applicable.
Packing Group (PG)	Not applicable.
DOT Pictograms	

**Section XV. Other Regulatory Information and Pictograms**

TSCA Chemical Inventory (EPA)	This compound is <b>ON</b> the EPA Toxic Substances Control Act (TSCA) inventory list.
WHMIS Classification (Canada)	Not available.
EINECS Number (EEC)	Not available.
EEC Risk Statements	R23/24/25- Toxic by inhalation, in contact with skin and if swallowed. R36/37/38- Irritating to eyes, respiratory system and skin.
Japanese Regulatory Data	Not available.

**Section XVI. Other Information****Version 1.0****Validated on 6/22/1999.****Printed 1/21/2005.****Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, household, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.

Printed 1/21/2005.