

Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
	Combustible material; avoid heat and sources of ignition.	   

Section I. Chemical Product and Company Identification

Chemical Name	4-Methylcyclohexanol (cis- and trans- mixture)		
Catalog Number	M0196	Supplier	TCI America 9211 N. Harbortgate St. Portland OR 1-800-423-8616
Synonym	4-Methylhexalin		
Chemical Formula	CH ₃ C ₆ H ₁₀ OH		
CAS Number	589-91-3	In case of Emergency Call	Chemtrec® (800) 424-9300 (U.S.) (703) 527-3887 (International)

Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
4-Methylcyclohexanol (cis- and trans- mixture)	589-91-3	Min. 98.0 (GC)	Not available.	Not available.

Section III. Hazards Identification

Acute Health Effects	No specific information is available in our data base regarding the toxic effects of this material for humans. However, exposure to any chemical should be kept to a minimum. Skin and eye contact may result in irritation. May be harmful if inhaled or ingested. Always follow safe industrial hygiene practices and wear proper protective equipment when handling this compound. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.
Chronic Health Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Not available. DEVELOPMENTAL TOXICITY : Not available. Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.

Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Skin Contact	In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention.
Inhalation	If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive.

Section V. Fire and Explosion Data

Flammability	Combustible.	Auto-Ignition	295°C (563°F)
Flash Points	68°C (154.4°F).	Flammable Limits	LOWER: 1%
Combustion Products	These products are toxic carbon oxides (CO, CO ₂).		
Fire Hazards	Not available.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available.		
Fire Fighting Media and Instructions	Combustible liquid. SMALL FIRE: Use DRY chemical powder. LARGE FIRE: Use water spray, fog or foam. DO NOT use water jet. Consult with local fire authorities before attempting large scale fire-fighting operations.		

Section VI. Accidental Release MeasuresSpill Cleanup
Instructions

Combustible material.
Keep away from heat. Mechanical exhaust required. Stop leak if without risk. Finish cleaning the spill by rinsing any contaminated surfaces with copious amounts of water. Consult federal, state, and/or local authorities for assistance on disposal.

Section VII. Handling and StorageHandling and Storage
Information

COMBUSTIBLE. Keep away from heat. Mechanical exhaust required. Avoid excessive heat and light. Do not breathe gas/fumes/ vapor/spray.

Section VIII. Exposure Controls/Personal Protection

Engineering Controls

Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value. Ensure that eyewash station and safety shower is proximal to the work-station location.

Personal Protection

Splash goggles. Lab coat. Vapor respirator. Boots. Gloves. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product. Be sure to use a MSHA/NIOSH approved respirator or equivalent.



Exposure Limits

Not available.

Section IX. Physical and Chemical Properties

Physical state @ 20°C

Liquid. (Clear, colorless.)

Solubility

Very slightly soluble in water.
Soluble in Ether, Alcohol.

Specific Gravity

0.92 (water=1)

Molecular Weight

114.19

Partition Coefficient

Not available.

Boiling Point

170 to 175°C (338 to 347°F)

Vapor Pressure

1.5 mmHg (@ 20°C)

Melting Point

-41°C (-41.8°F)

Vapor Density

3.94 (Air = 1)

Refractive Index

1.4550 - 1.4600

Volatility

Not available.

Critical Temperature

Not available.

Odor

Not available.

Viscosity

Not available.

Taste

Not available.

Section X. Stability and Reactivity Data

Stability

This material is stable if stored under proper conditions. (See Section VII for instructions)

Conditions of Instability

Avoid excessive heat and light.

Incompatibilities

Reactive with strong oxidizing agents, acid chlorides, and acid anhydrides.

Section XI. Toxicological Information

RTECS Number

Not available.

Routes of Exposure

Eye Contact. Ingestion. Inhalation.

Toxicity Data

Not available.

Chronic Toxic Effects

CARCINOGENIC EFFECTS : Not available.
MUTAGENIC EFFECTS : Not available.
TERATOGENIC EFFECTS : Not available.
DEVELOPMENTAL TOXICITY : Not available.
Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.

Acute Toxic Effects

No specific information is available in our data base regarding the toxic effects of this material for humans. However, exposure to any chemical should be kept to a minimum. Skin and eye contact may result in irritation. May be harmful if inhaled or ingested. Always follow safe industrial hygiene practices and wear proper protective equipment when handling this compound.
Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

Section XII. Ecological Information

Ecotoxicity Not available.

Environmental Fate Not available.

Section XIII. Disposal Considerations

Waste Disposal Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.

Section XIV. Transport Information

DOT Classification Not a DOT controlled material (United States).

PIN Number Not available.

Proper Shipping Name Not available.

Packing Group (PG) Not available.

DOT Pictograms

**Section XV. Other Regulatory Information and Pictograms**

TSCA Chemical Inventory (EPA) This compound is **ON** the EPA Toxic Substances Control Act (TSCA) inventory list.

WHMIS Classification (Canada) CLASS B-3: Combustible liquid with a flash point between 37.8°C (100°F) and 93.3°C (200°F).
On NDSL

EINECS Number (EEC) Not available.

EEC Risk Statements Not available.

Japanese Regulatory Data ENCS No. 2-2301 ; 3-2301

Section XVI. Other Information**Version 1.0****Validated on 12/28/2007.****Printed 12/28/2007.****Notice to Reader**

TCl laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.