

Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
 	<p>Corrosive to eyes and skin on contact. Flammable material; avoid heat and sources of ignition. Hygroscopic -- keep container tightly sealed. Store under inert gas.</p>	

Section I. Chemical Product and Company Identification

Chemical Name	1-Methylpiperidine		
Catalog Number	M0403	Supplier	TCI America 9211 N. Harbortgate St. Portland OR 1-800-423-8616
Synonym	Piperidine, 1-methyl- (CA INDEX NAME)		
Chemical Formula	C ₆ H ₁₃ N		
CAS Number	626-67-5	In case of Emergency Call	Chemtrec® (800) 424-9300 (U.S.) (703) 527-3887 (International)

Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
1-Methylpiperidine	626-67-5	Min. 99.0 (GC)	Not available.	Mouse LD ₅₀ (intraperitoneal) 400 mg/kg

Section III. Hazards Identification

Acute Health Effects	Corrosive to skin, eyes, and respiratory system. Liquid or spray mist may produce tissue damage, particularly in mucous membranes of the eyes, mouth and respiratory tract. Skin contact may produce burns. Eye contact can result in corneal damage or blindness. Inhalation of the spray mist may produce severe irritation of respiratory tract, characterized by coughing, choking, or shortness of breath. Corrosive materials may cause serious injury if ingested. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.
Chronic Health Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Not available. DEVELOPMENTAL TOXICITY : Not available. Repeated or prolonged contact with spray mist may produce chronic eye irritation and severe skin irritation. Repeated or prolonged exposure to spray mist may produce respiratory tract irritation leading to frequent attacks of bronchial infection.

Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Skin Contact	In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention.
Inhalation	If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.
Ingestion	DO NOT INDUCE VOMITING. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive.

Section V. Fire and Explosion Data

Flammability	Flammable.	Auto-Ignition	205 °C (401 °F)
Flash Points	3 °C (37.4 °F).	Flammable Limits	LOWER: 0.5% UPPER: 11.5%
Combustion Products	These products are toxic carbon oxides (CO, CO ₂), nitrogen oxides (NO _x).		
Fire Hazards	Not available.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available.		
Fire Fighting Media and Instructions	Flammable liquid. SMALL FIRE: Use DRY chemical powder. LARGE FIRE: Use alcohol foam, water spray or fog. Consult with local fire authorities before attempting large scale fire-fighting operations.		

Section VI. Accidental Release Measures

Spill Cleanup Instructions	Flammable material. Corrosive material. Hygroscopic material. Keep away from heat. Mechanical exhaust required. Stop leak if without risk. Absorb with DRY earth, sand or other non-combustible material. DO NOT get water inside container. DO NOT touch spilled material. Use water spray curtain to divert vapor drift. Prevent entry into sewers, basements or confined areas; dike if needed. Consult federal, state, and/or local authorities for assistance on disposal.
----------------------------	--

Section VII. Handling and Storage

Handling and Storage Information	FLAMMABLE. CORROSIVE. HYGROSCOPIC. STORE UNDER INERT GAS. Keep container dry. Keep away from heat. Mechanical exhaust required. Avoid excessive heat and light. Do not breathe gas/fumes/ vapor/spray. Never add water to this product. Wear suitable protective clothing. If you feel unwell, seek medical attention and show the label when possible. Treat symptomatically and supportively. Always store away from incompatible compounds such as oxidizing agents, acids, moisture.
----------------------------------	---

Section VIII. Exposure Controls/Personal Protection

Engineering Controls	Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value. Ensure that eyewash station and safety shower is proximal to the work-station location.
----------------------	---

Personal Protection	Face shield. Lab coat. Vapor respirator. Gloves. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product. Be sure to use a MSHA/NIOSH approved respirator or equivalent.
---------------------	---



Exposure Limits	Not available.
-----------------	----------------

Section IX. Physical and Chemical Properties

Physical state @ 20°C	Liquid. (Clear, colorless ~ light yellow.)	Solubility	Miscible with water. Soluble in alcohol, ether.
Specific Gravity	0.82 (water=1)		
Molecular Weight	99.17	Partition Coefficient	LOG P _{ow} : 1.3
Boiling Point	107°C (224.6°F)	Vapor Pressure	2.6 kPa (@ 25°C)
Melting Point	-50°C (-58°F)	Vapor Density	Not available.
Refractive Index	1.44	Volatility	Not available.
Critical Temperature	Not available.	Odor	Characteristic.
Viscosity	Not available.	Taste	Not available.

Section X. Stability and Reactivity Data

Stability	This material is stable if stored under proper conditions. (See Section VII for instructions)
-----------	---

Conditions of Instability	Avoid excessive heat and light. Hygroscopic; keep container tightly closed. Store under inert gas.
---------------------------	--

Incompatibilities	Reactive with oxidizing agents, acids, acid chlorides, acid anhydrides, moisture, carbon monoxide.
-------------------	--

Section XI. Toxicological Information

RTECS Number	TN1225000
--------------	-----------

Routes of Exposure	Eye Contact. Ingestion. Inhalation. Skin contact.
--------------------	---

Toxicity Data	Mouse LD ₅₀ (intraperitoneal) 400 mg/kg
---------------	--

Chronic Toxic Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Not available. DEVELOPMENTAL TOXICITY : Not available. Repeated or prolonged contact with spray mist may produce chronic eye irritation and severe skin irritation. Repeated or prolonged exposure to spray mist may produce respiratory tract irritation leading to frequent attacks of bronchial infection.
-----------------------	--

Acute Toxic Effects	Corrosive to skin, eyes, and respiratory system. Liquid or spray mist may produce tissue damage, particularly in mucous membranes of the eyes, mouth and respiratory tract. Skin contact may produce burns. Eye contact can result in corneal damage or blindness. Inhalation of the spray mist may produce severe irritation of respiratory tract, characterized by coughing, choking, or shortness of breath. Corrosive materials may cause serious injury if ingested. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.
---------------------	--

Section XII. Ecological Information

Ecotoxicity	Not available.
Environmental Fate	Not available.

Section XIII. Disposal Considerations

Waste Disposal	Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.
----------------	---

Section XIV. Transport Information

DOT Classification	DOT CLASS 3: Flammable liquid. DOT CLASS 8: Corrosive material
PIN Number	UNNA: UN2399 Shipping name: 1-Methylpiperidine
Proper Shipping Name	1-Methylpiperidine
Packing Group (PG)	II
DOT Pictograms	

Section XV. Other Regulatory Information and Pictograms

TSCA Chemical Inventory (EPA)	This compound is ON the EPA Toxic Substances Control Act (TSCA) inventory list.
WHMIS Classification (Canada)	CLASS B-2: Flammable liquid with a flash point lower than 37.8°C (100°F). CLASS E: Corrosive liquid. On NDSL.
EINECS Number (EEC)	210-959-9
EEC Risk Statements	R11- Highly flammable. R18- In use, may form flammable/explosive vapor-air mixture. R34- Causes burns.
Japanese Regulatory Data	ENCS No. 5-767

Section XVI. Other Information

Version 1.0
Validated on 10/1/2009.
Printed 10/1/2009.

Notice to Reader

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.