

Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
   	<p>Flammable material; avoid heat and sources of ignition. Toxic compound, do not ingest or inhale. Avoid all contact with this material. Irritating to skin, eyes, and the respiratory system. Possible mutagen and teratogen. Refrigerate and vent pressure slowly before opening.</p>	   

Section I. Chemical Product and Company Identification

Chemical Name	Acetylacetone		
Catalog Number	P0052	Supplier	TCl America 9211 N. Harborage St. Portland OR 1-800-423-8616
Synonym	Diacetylmethane		
Chemical Formula	CH ₃ COCH ₂ COCH ₃		
CAS Number	123-54-6	In case of Emergency Call	Chemtrec® (800) 424-9300 (U.S.) (703) 527-3887 (International)

Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
Acetylacetone	123-54-6	Min. 99.0 (GC)	This compound is classified as a possible mutagen. There is no acceptable exposure limit for a mutagen.	Rat LD ₅₀ (oral) 55mg/kg Rat LC ₁₀ (inhalation) 1000ppm/4H Rabbit LD ₅₀ (dermal) 8100µl/kg

Section III. Hazards Identification

Acute Health Effects	Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.
Chronic Health Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Not available. DEVELOPMENTAL TOXICITY Reproductive: rat (inhalation) 398ppm/6H. Duration: female 6-15 days of pregnancy. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.

Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. IMMEDIATELY flush eyes with running water for at least 15 minutes. Keeping eyelids open. COLD water may be used. DO NOT use an eye ointment. Flush eyes with running water for a minimum of 15 minutes, occasionally lifting the upper eyelids. Seek medical attention. Treat symptomatically and supportively.
Skin Contact	After contact with skin, wash immediately with plenty of water. Gently and thorough wash the contaminated skin with running water and non-abrasive soap. Be particularly careful to clean folds, crevices, creases and groin. COLD water may be used. Cover the irritated skin with an emollient. Seek medical attention. Treat symptomatically and supportively. Wash any contaminated clothing before reusing.
Inhalation	Evacuate the victim to a safe area as soon as possible. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, administer oxygen. If the victim is not breathing, perform artificial respiration. WARNING: It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation when the inhaled material is toxic, infectious or corrosive. Seek immediate medical attention and, if possible, show the chemical label. Treat symptomatically and supportively.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt, or waistband. If the victim is not breathing, administer artificial respiration. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive. Seek immediate medical attention and, if possible, show the chemical label. Treat symptomatically and supportively.

Section V. Fire and Explosion Data			
Flammability	Flammable.	Auto-Ignition	349°C (660.2°F)
Flash Points	34°C (93.2°F).	Flammable Limits	Not available.
Combustion Products	These products are toxic carbon oxides (CO, CO ₂).		
Fire Hazards	No specific information is available regarding the flammability of this compound in the presence of various materials.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available. No additional information is available regarding the risks of explosion.		
Fire Fighting Media and Instructions	Flammable liquid. SMALL FIRE: Use DRY chemicals, CO ₂ , alcohol foam or water spray. LARGE FIRE: Use alcohol foam, water spray or fog.		

Section VI. Accidental Release Measures	
Spill Cleanup Instructions	Flammable liquid. Toxic material. Irritating material. Possible mutagenic and teratogenic material. Refrigerate material. Keep away from heat and sources of ignition. Mechanical exhaust required. Stop leak if without risk. Absorb with DRY earth, sand or other non-combustible material. DO NOT touch spilled material. Prevent entry into sewers, basements or confined areas; dike if needed. Eliminate all sources of ignition. Consult federal, state, and/or local authorities for assistance on disposal.

Section VII. Handling and Storage	
Handling and Storage Information	FLAMMABLE. TOXIC. POSSIBLE MUTAGEN AND TERATOGEN. REFRIGERATE. Handle with caution and minimize exposure. DO NOT ingest. Do not breathe gas, fumes, vapor or spray. Wear suitable protective clothing. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively. Always store away from incompatible compounds such as oxidizing agents, reducing agents, alkalis (bases).

Section VIII. Exposure Controls/Personal Protection	
Engineering Controls	Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value. Ensure that eyewash station and safety shower is proximal to the work-station location.
Personal Protection	Splash goggles. Lab coat. Dust respirator. Boots. Gloves. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product.
	
Exposure Limits	This compound is classified as a possible mutagen. There is no acceptable exposure limit for a mutagen.

Section IX. Physical and Chemical Properties			
Physical state @ 20°C	Liquid.	Solubility	Soluble in ether, alcohol, acetone, and chloroform.
Specific Gravity	0.975		Miscible with glacial acetic acid, and benzene.
Molecular Weight	100.12	Partition Coefficient	Not available.
Boiling Point	140°C (284°F)	Vapor Pressure	6 mm Hg @ 20°C
Melting Point	-23°C (-9.4°F)	Vapor Density	3.5
Refractive Index	1.4494 @ 20°C	Volatility	Not available.
Critical Temperature	Not available.	Odor	Pleasant odor.
Viscosity	Not available.	Taste	Not available.

Section X. Stability and Reactivity Data	
Stability	This material is stable if stored under proper conditions. (See Section VII for instructions)
Conditions of Instability	Avoid excessive heat and light.
Incompatibilities	Reactive with oxidizing agents, strong reducing agents, strong alkalis (bases), and halogens.

Section XI. Toxicological Information

RTECS Number	SA1925000
Routes of Exposure	Eye contact. Ingestion. Inhalation. Skin contact.
Toxicity Data	Rat LD ₅₀ (oral) 55mg/kg Rat LC ₅₀ (inhalation) 1000ppm/4H Rabbit LD ₅₀ (dermal) 8100µl/kg
Chronic Toxic Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Not available. DEVELOPMENTAL TOXICITY Reproductive: rat (inhalation) 398ppm/6H. Duration: female 6-15 days of pregnancy. Repeated exposure to an highly toxic material may produce general deterioration of health by an accumulation in one or many human organs.
Acute Toxic Effects	Toxic if ingested or inhaled. Avoid prolonged contact with this material. Overexposure may result in serious illness or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

Section XII. Ecological Information

Ecotoxicity	Not available.
Environmental Fate	Acetyl acetone may be released to the environment in waste streams from its production and use. If released to soil, acetyl acetone is expected to leach readily (estimated Koc range of 6 to 28) and volatilize from dry soil surfaces. One screening study suggests that biodegradation may be the predominant fate process in water. Although this study is not specific to soil media, it suggests that biodegradation in soil may be important. If released to water, hydrolysis, aquatic oxidation, adsorption to sediment and bioconcentration in aquatic organisms are not expected to be environmentally important removal processes of acetyl acetone. Volatilization half-lives of 15 and 170 days have been estimated for a model river (one meter deep) and a model environmental pond, respectively. If released to the atmosphere, acetyl acetone is expected to exist in the vapor phase. Vapor-phase acetyl acetone is expected to degrade by reaction with photochemically produced hydroxyl radicals (estimated half-life of 14 days). Based on its high water solubility, removal from air via wet deposition may occur. In occupational settings, exposure to acetyl acetone may occur through inhalation of vapors and through eye and skin contact.

Section XIII. Disposal Considerations

Waste Disposal	Recycle to process, if possible. Consult your local or regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state, and local regulations when disposing of the substance.
----------------	---

Section XIV. Transport Information

DOT Classification	CLASS 3: Flammable liquid. CLASS 6.1: Toxic material.
PIN Number	UN2310
Proper Shipping Name	Pentane-2,4-dione
Packing Group (PG)	III
DOT Pictograms	 

Section XV. Other Regulatory Information and Pictograms

TSCA Chemical Inventory (EPA)	This compound is ON the EPA Toxic Substances Control Act (TSCA) inventory list.
WHMIS Classification (Canada)	WHMIS CLASS B-2: Flammable liquid with a flash point lower than 35°C (100°F).
EINECS Number (EEC)	204-634-0
EEC Risk Statements	R10- Flammable. R18- In use, may form flammable/explosive vapor-air mixture. R23/24/25- Toxic by inhalation, in contact with skin and if swallowed. R36/37/38- Irritating to eyes, respiratory system and skin. R46- May cause heritable genetic damage.
Japanese Regulatory Data	Not available.

Section XVI. Other Information**Version 1.0****Validated on 9/15/1998.****Printed 3/17/2005.****Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.

Printed 3/17/2005.