

Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
 	Oxidizer. Irritating to skin, eyes, and the respiratory system. Heat and Shock Sensitive. Refrigerate.	   

Section I. Chemical Product and Company Identification

Chemical Name	Iodomesitylene Diacetate		
Catalog Number	I0479	Supplier	TCI America 9211 N. Harborside St. Portland OR 1-800-423-8616
Synonym	Iodine, bis(acetato-kappaO) (2,4,6-trimethylphenyl)- (9CI)		
Chemical Formula	C ₁₃ H ₁₇ IO ₄		
CAS Number	33035-41-5	In case of Emergency Call	Chemtec® (800) 424-9300 (U.S.) (703) 527-3887 (International)

Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
Iodomesitylene Diacetate	33035-41-5	Min. 98.0%(Tit.)	Not available.	Not available.

Section III. Hazards Identification

Acute Health Effects	Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.
Chronic Health Effects	CARCINOGENIC EFFECTS : Not available. MUTAGENIC EFFECTS : Not available. TERATOGENIC EFFECTS : Not available. DEVELOPMENTAL TOXICITY : Not available. Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.

Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Skin Contact	In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention.
Inhalation	If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive.

Section V. Fire and Explosion Data

Flammability	May be combustible at high temperature.	Auto-Ignition	Not available.
Flash Points	Not available.	Flammable Limits	Not available.
Combustion Products	These products are toxic carbon oxides (CO, CO ₂), halogenated compounds.		
Fire Hazards	Not available.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available.		
Fire Fighting Media and Instructions	Oxidizing material. DO NOT use water jet. Use flooding quantities of water. Avoid contact with organic materials. Consult with local fire authorities before attempting large scale fire-fighting operations.		

Section VI. Accidental Release Measures**Spill Cleanup
Instructions**

Oxidizing Material. Irritating Material. Heat and Shock Sensitive.
 Stop leak if without risk. Avoid contact with a combustible material (wood, paper, oil, clothing...). Keep substance damp using water spray. DO NOT touch spilled material. Prevent entry into sewers, basements or confined areas; dike if needed. Eliminate all sources of ignition. Consult federal, state, and/or local authorities for assistance on disposal.

Section VII. Handling and Storage**Handling and Storage
Information**

OXIDIZER. IRRITANT. HEAT AND SHOCK SENSITIVE. REFRIGERATE. Keep away from heat. Mechanical exhaust required. Keep away from combustible material.. When not in use, tightly seal the container and store in a dry, cool place. Avoid excessive heat and light. Do not breathe dust.
 Always store away from incompatible compounds such as oxidizing agents, reducing agents, acids.

Section VIII. Exposure Controls/Personal Protection**Engineering Controls**

Use process enclosures, local exhaust ventilation, or other engineering controls to keep airborne levels below recommended exposure limits. If user operations generate dust, fume or mist, use ventilation to keep exposure to airborne contaminants below the exposure limit.

Personal Protection

Splash goggles. Lab coat. Dust respirator. Boots. Gloves. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product. Be sure to use a MSHA/NIOSH approved respirator or equivalent.

**Exposure Limits**

Not available.

Section IX. Physical and Chemical Properties**Physical state @ 20°C**

Solid. (White Crystalline Powder.)

Solubility

Soluble in methanol.

Specific Gravity

Not available.

Molecular Weight

364.18

Partition Coefficient

Not available.

Boiling Point

Not available.

Vapor Pressure

Not applicable.

Melting Point

168 °C (334.4 °F)

Vapor Density

Not available.

Refractive Index

Not available.

Volatility

Not available.

Critical Temperature

Not available.

Odor

Not available.

Viscosity

Not available.

Taste

Not available.

Section X. Stability and Reactivity Data**Stability**

This material is stable if stored under proper conditions. (See Section VII for instructions)

Conditions of Instability

Avoid excessive heat and light.

Incompatibilities

Reactive with oxidizing materials, reducing agents, strong acids, organic materials, combustible materials.

Section XI. Toxicological Information**RTECS Number**

Not available.

Routes of Exposure

Eye Contact. Ingestion. Inhalation.

Toxicity Data

Not available.

Chronic Toxic Effects

CARCINOGENIC EFFECTS : Not available.
MUTAGENIC EFFECTS : Not available.
TERATOGENIC EFFECTS : Not available.
DEVELOPMENTAL TOXICITY: Not available.
 Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.

Acute Toxic Effects

Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering.
 Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.

Section XII. Ecological Information

Ecotoxicity Not available.

Environmental Fate Not available.

Section XIII. Disposal Considerations

Waste Disposal Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.

Section XIV. Transport Information

DOT Classification DOT Class 5.1: Oxidizing material.

PIN Number UN1479

Proper Shipping Name Oxidizing solid, n.o.s.

Packing Group (PG) II

DOT Pictograms

**Section XV. Other Regulatory Information and Pictograms**

TSCA Chemical Inventory (EPA) This product is **NOT** on the EPA Toxic Substances Control Act (TSCA) inventory. The following notices are required by 40 CFR 720.36 (C) for those products not on the inventory list:
(i) These products are supplied solely for use in research and development by or under the supervision of a technically qualified individual as defined in 40 CFR 720.0 et sec.
(ii) The health risks of these products have not been fully determined. Any information that is or becomes available will be supplied on an MSDS sheet.

WHMIS Classification (Canada) CLASS C: Oxidizing material.

EINECS Number (EEC) Not available.

EEC Risk Statements
R5- Heating may cause an explosion.
R8- Contact with combustible material may cause fire.
R18- In use, may form flammable/explosive vapor-air mixture.
R36/37/38- Irritating to eyes, respiratory system and skin.

Japanese Regulatory Data Not available.

Section XVI. Other Information**Version 1.0****Validated on 3/20/2007.****Printed 3/20/2007.****Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.