

# Material Safety Data Sheet

HAZARD WARNINGS	RISK PHRASES	PROTECTIVE CLOTHING
	Irritating to skin, eyes, and the respiratory system. Combustible material; avoid heat and sources of ignition. Protect from air. Harmful compound, minimize exposure. Store under nitrogen.	

## Section I. Chemical Product and Company Identification

Chemical Name	<b>alpha-Terpinene</b>		
Catalog Number	M0317	Supplier	TCI America 9211 N. Harbortgate St. Portland OR 1-800-423-8616
Synonym	1-Methyl-4-isopropyl-1,3-cyclohexadiene		
Chemical Formula	C <sub>10</sub> H <sub>16</sub>		
CAS Number	99-86-5	In case of Emergency Call <b>Chemtrec®</b> <b>(800) 424-9300 (U.S.)</b> <b>(703) 527-3887 (International)</b>	

## Section II. Composition and Information on Ingredients

Chemical Name	CAS Number	Percent (%)	TLV/PEL	Toxicology Data
alpha-Terpinene	99-86-5	Min. 90.0 (GC)	Not available.	Rat LD <sub>50</sub> (oral) 1680mg/kg

## Section III. Hazards Identification

Acute Health Effects	Harmful if ingested or inhaled. Minimize exposure to this material. Severe overexposure can result in injury or death. Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering. Absorption into the body leads to the formation of methemoglobin which in sufficient concentration causes cyanosis. Onset may be delayed 2 to 4 hours. Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.
Chronic Health Effects	<b>CARCINOGENIC EFFECTS</b> : Not available. <b>MUTAGENIC EFFECTS</b> : Not available. <b>TERATOGENIC EFFECTS</b> : Not available. <b>DEVELOPMENTAL TOXICITY</b> Reproductive effects: Rat TDLo (oral) 600mg/kg, female 6-15 days of pregnancy. Toxic effects: Specific Developmental Abnormalities - Musculoskeletal system. Effects on Newborn - Behavioral. Rat TDLo (oral) 2500 mg/kg, female 6-15 days of pregnancy. Toxic effects: Maternal Effects - Other effects. Effects on Fertility - Female fertility index. Effects on Embryo or Fetus - Fetotoxicity. Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.

## Section IV. First Aid Measures

Eye Contact	Check for and remove any contact lenses. In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Skin Contact	In case of contact, immediately flush skin with plenty of water. Remove contaminated clothing and shoes. Wash clothing before reuse. Thoroughly clean shoes before reuse. Get medical attention.
Inhalation	If the victim is not breathing, perform mouth-to-mouth resuscitation. Loosen tight clothing such as a collar, tie, belt or waistband. If breathing is difficult, oxygen can be administered. Seek medical attention if respiration problems do not improve.
Ingestion	INDUCE VOMITING by sticking finger in throat. Lower the head so that the vomit will not reenter the mouth and throat. Loosen tight clothing such as a collar, tie, belt or waistband. If the victim is not breathing, perform mouth-to-mouth resuscitation. Examine the lips and mouth to ascertain whether the tissues are damaged, a possible indication that the toxic material was ingested; the absence of such signs, however, is not conclusive. SEEK IMMEDIATE MEDICAL ATTENTION in case of ingestion of a radioactive material.

<b>Section V. Fire and Explosion Data</b>			
Flammability	Combustible.	Auto-Ignition	Not available.
Flash Points	46.11°C (115°F).	Flammable Limits	Not available.
Combustion Products	These products are toxic carbon oxides (CO, CO <sub>2</sub> ).		
Fire Hazards	Not available.		
Explosion Hazards	Risks of explosion of the product in presence of mechanical impact: Not available. Risks of explosion of the product in presence of static discharge: Not available.		
Fire Fighting Media and Instructions	Combustible liquid. SMALL FIRE: Use DRY chemical powder. LARGE FIRE: Use alcohol foam, water spray or fog. Cool containing vessels with water jet in order to prevent pressure build-up, autoignition or explosion. Consult with local fire authorities before attempting large scale fire-fighting operations.		

<b>Section VI. Accidental Release Measures</b>	
Spill Cleanup Instructions	Combustible material. Harmful material. Irritating material. Protect from air. Keep away from heat. Mechanical exhaust required. Stop leak if without risk. Absorb with DRY earth, sand or other non-combustible material. DO NOT touch spilled material. Prevent entry into sewers, basements or confined areas; dike if needed. Consult federal, state, and/or local authorities for assistance on disposal.

<b>Section VII. Handling and Storage</b>	
Handling and Storage Information	COMBUSTIBLE. HARMFUL. IRRITANT. PROTECT FROM AIR. Keep away from heat. Mechanical exhaust required. Avoid excessive heat and light. DO NOT ingest. Do not breathe gas/fumes/ vapor/spray. Wear suitable protective clothing. If ingested, seek medical advice immediately and show the container or the label. Treat symptomatically and supportively. Always store away from incompatible compounds such as acids, alkalis (bases).

<b>Section VIII. Exposure Controls/Personal Protection</b>	
Engineering Controls	Provide exhaust ventilation or other engineering controls to keep the airborne concentrations of vapors below their respective threshold limit value. Ensure that eyewash station and safety shower is proximal to the work-station location.
Personal Protection	Splash goggles. Lab coat. Vapor respirator. Boots. Gloves. Suggested protective clothing might not be sufficient; consult a specialist BEFORE handling this product. Be sure to use a MSHA/NIOSH approved respirator or equivalent.
	
Exposure Limits	Not available.

<b>Section IX. Physical and Chemical Properties</b>			
Physical state @ 20°C	Liquid. (Clear, colorless.)	Solubility	Practically insoluble in water. Miscible in alcohol, ether.
Specific Gravity	0.837 (water=1)		
Molecular Weight	136.23	Partition Coefficient	Not available.
Boiling Point	173 to 175°C (343.4 to 347°F)	Vapor Pressure	Not available.
Melting Point	Not available.	Vapor Density	Not available.
Refractive Index	1.4784 @ 20°C	Volatility	Not available.
Critical Temperature	Not available.	Odor	Not available.
Viscosity	Not available.	Taste	Not available.

<b>Section X. Stability and Reactivity Data</b>	
Stability	This material is stable if stored under proper conditions. (See Section VII for instructions)
Conditions of Instability	Protect from air. Avoid excessive heat and light.
Incompatibilities	Reactive with strong acids, strong alkalis (bases).

**Section XI. Toxicological Information**

RTECS Number	OS8060000
Routes of Exposure	Eye Contact. Ingestion. inhalation.
Toxicity Data	Rat LD <sub>50</sub> (oral) 1680mg/kg
Chronic Toxic Effects	<p><b>CARCINOGENIC EFFECTS</b> : Not available.  <b>MUTAGENIC EFFECTS</b> : Not available.  <b>TERATOGENIC EFFECTS</b> : Not available.  <b>DEVELOPMENTAL TOXICITY</b> Reproductive effects:  Rat TDLo (oral) 600mg/kg, female 6-15 days of pregnancy.  Toxic effects:  Specific Developmental Abnormalities - Musculoskeletal system.  Effects on Newborn - Behavioral.  Rat TDLo (oral) 2500 mg/kg, female 6-15 days of pregnancy.  Toxic effects:  Maternal Effects - Other effects.  Effects on Fertility - Female fertility index.  Effects on Embryo or Fetus - Fetotoxicity.  Repeated or prolonged exposure to this compound is not known to aggravate existing medical conditions.</p>
Acute Toxic Effects	<p>Harmful if ingested or inhaled. Minimize exposure to this material. Severe overexposure can result in injury or death.  Irritating to eyes and skin on contact. Inhalation causes irritation of the lungs and respiratory system. Inflammation of the eye is characterized by redness, watering, and itching. Skin inflammation is characterized by itching, scaling, reddening, or, occasionally, blistering.  Absorption into the body leads to the formation of methemoglobin which in sufficient concentration causes cyanosis.  Onset may be delayed 2 to 4 hours.  Follow safe industrial hygiene practices and always wear proper protective equipment when handling this compound.</p>

**Section XII. Ecological Information**

Ecotoxicity	Not available.
Environmental Fate	Not available.

**Section XIII. Disposal Considerations**

Waste Disposal	Recycle to process, if possible. Consult your local regional authorities. You may be able to dissolve or mix material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.
----------------	---

**Section XIV. Transport Information**

DOT Classification	CLASS 3: Flammable liquid.
PIN Number	UN3295
Proper Shipping Name	Hydrocarbons, liquid, n.o.s.
Packing Group (PG)	III
DOT Pictograms	

**Section XV. Other Regulatory Information and Pictograms**

TSCA Chemical Inventory (EPA)	This compound is <b>ON</b> the EPA Toxic Substances Control Act (TSCA) inventory list.
WHMIS Classification (Canada)	CLASS B-3: Combustible liquid with a flash point between 37.8°C (100°F) and 93.3°C (200°F).
EINECS Number (EEC)	202-795-1
EEC Risk Statements	<p>R10- Flammable.  R18- In use, may form flammable/explosive vapor-air mixture.  R20/21/22- Harmful by inhalation, in contact with skin and if swallowed.  R36/37/38- Irritating to eyes, respiratory system and skin.</p>
Japanese Regulatory Data	Not available.

**Section XVI. Other Information****Version 1.0****Validated on 6/25/2001.****Printed 3/1/2005.****Notice to Reader**

TCI laboratory chemicals are for research purposes only and are NOT intended for use as drugs, food additives, households, or pesticides. The information herein is believed to be correct, but does not claim to be all inclusive and should be used only as a guide. Neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. Final determination of suitability of any material is the sole responsibility of the user. All chemical reagents must be handled with the recognition that their chemical, physiological, toxicological, and hazardous properties have not been fully investigated or determined. All chemical reagents should be handled only by individuals who are familiar with their potential hazards and who have been fully trained in proper safety, laboratory, and chemical handling procedures. Although certain hazards are described herein, we can not guarantee that these are the only hazards which exist. Our MSDS sheets are based only on data available at the time of shipping and are subject to change without notice as new information is obtained. Avoid long storage periods since the product is subject to degradation with age and may become more dangerous or hazardous. It is the responsibility of the user to request updated MSDS sheets for products that are stored for extended periods. Disposal of unused product must be undertaken by qualified personnel who are knowledgeable in all applicable regulations and follow all pertinent safety precautions including the use of appropriate protective equipment (e.g. protective goggles, protective clothing, breathing equipment, facial mask, fume hood). For proper handling and disposal, always comply with federal, state, and local regulations.

Printed 3/1/2005.