

5000M SERIES

DELAYED RESPONSE UTILITY GRADE MOV SURGE ARRESTOR PHOTOCONTROL



SPECIFICATIONS

ON/OFF: Turn-ON is 1 to 3 ft. Turn-OFF to Turn-ON ratio is 5 max.

TIME DELAY: ON and OFF.

CELL: Cadmium sulphide photocell responds to the light spectrum near to that of a human eye. Resists effects of moisture and airborne contaminants.

RELAY: Bi-metal provides positive snap action switching, reducing bounce and prolonging contact life.

SURGE ARRESTOR: 380 joule MOV (metal oxide varistor) exceeds ANSI and NEMA requirements.

LOCKING PRONGS: Solid brass for maximum corrosion resistance and electrical conductivity.

TEMPERATURE RANGE:
-40° to +140°F (-40° to +60°C).

FAIL MODE: ON.

WARRANTY: 3 years.

APPLICATIONS



For use on streets, highways and other luminaries equipped with locking type receptacles, where most stringent surge protection is needed.

FEATURES

OPERATION: Delayed response prevents false switching due to light from vehicles or lighting, etc.

STANDARDS: Meets ANSI C136.10 including color designations. Also meets EEI NEMA standards.

HOUSING: Lexan® UV Stabilized, permanent color with UV resistant clear acrylic window. Models 5026M and 5008M with polypropylene dome. Provides high impact, flammability resistance and electrically safe operation.

ENERGY SAVINGS: Works with screw base CFLs and LED lamps.

ORDERING INFO

CATALOG NO.	UPC CODE	VOLTAGE 50-60Hz	COLOR
5001M	61012	105-130	Grey
5004M	61013	208-277	Maroon
5007M	61014	105-130/208-285	Blue
5008M*	61017	480	Yellow
5021M	61015	105-130	Grey
5024M	61016	208-277	Maroon
5026M**	61045	347	Green

*Not UL listed or CSA certified.

**CSA certified only.

CONTACT RATINGS

CATALOG NO.	LIGHT SENSOR	RATING	
		TUNGSTEN	BALLAST
5001M	1"	2000W	1800VA
5004M	1"	3470-4620W	2080-2770VA
5007M	1/2"	2000W 3470-4620W	1800VA 2080-2770VA
5008M*	1"	1000W	1800VA
5021M	1/2"	2000W	1800VA
5024M	1/2"	3470-4620W	2080-2770VA
5026M**	1/2"	1000W	1800VA

WIRING DIAGRAMS

