



HUTM

Technical Specifications

MODELS in SERIES

- HUTM1860; HUTM1872; HUTM2040; HUTM2448; HUTM2060; HUTM2460; HUTM3060; HUTM3072; HUTM3096; HUTM3672

GENERAL DESCRIPTION OF PRODUCT/SERIES/DRAWING

- Rectangular shaped utility tables with metal apron and legs

FEATURES

- Height—29.5” high (Adjustment of 1/2” using glide)
- Legs are specified as either black or chrome
- Top
 - 1-1/8” thick particle board substrate
 - Finish: thermally-fused melamine surface on both sides
 - 0.024” thick PVC edge banding
 - Square corners (no radius)

DIMENSIONS (All dimensions are in inches, unless noted.)

MODEL	SIZE ()	Overhang (short edge to skirt)	Overhang (long edge to skirt)	Apron height
HUTM1860	17.5 x 59.5	1.68	1.68	3”
HUTM1872	17.5 x 71.5	1.68	1.68	3”
HUTM2040	19.5 x 39.5	1.68	1.68	3”
HUTM2060	19.5 x 59.5	1.68	1.68	3”
HUTM2448	23.5 x 47.5	1.68	1.68	3”
HUTM2460	23.5 x 59.5	1.68	1.68	3”
HUTM3060	29.5 x 59.5	1.68	1.68	3”
HUTM3072	29.5 x 71.5	1.68	1.68	3”
HUTM3096	19.5 x 95.5	1.68	1.68	3”
HUTM3672	35.5 x 71.5	1.68	1.68	3”

MODEL	Distance between legs (short side)	Distance between legs (long side)	Weight capacity (distributed) (lbs)	
HUTM1860	12	54	234	
HUTM1872	12	66	270	
HUTM2040	14	34	240	
HUTM2060	14	54	240	
HUTM2448	18	42	216	
HUTM2460	18	54	252	
HUTM3060	24	54	270	
HUTM3072	24	66	306	
HUTM3096	24	90	378	
HUTM3672	30	66	324	



HUTM Technical Specifications

GAUGES- METAL THICKNESS

- Apron
 - 20 gauge CR Steel
- Corner brackets (underneath top)
 - 18 gauge CR Steel
- Legs
 - 16 gauge CR Steel
 - Square tube are 1.25" x 1.25"
- Glides
 - 5/6 x 1" Screw-in glides

OTHER

▪

CARTON DIMENSIONS/WEIGHTS/CUBES

Model #	Cubes	Carton Outside Dimensions	Weight
HUTM1860	4.9	63-3/16x5-9/16x5-11/16	65
HUTM1872	4.8	75-3/16x20-13/16x5-11/16	73
HUTM2040	3.3	43-3/16x22-13/16x5-11/16	50
HUTM2060	4.9	63-3/16x22-7/8x5-11/16	68
HUTM2448	4.5	51-3/16x26-13/16x5-11/16	65
HUTM2460	5.6	63-3-16x26-13/16x5-11/16	81
HUTM3060	6.5	74-1/2x32-13/16x5-3/4	88
HUTM3072	7.2	86-1/8x32-13/16x5-3/4	106
HUTM3096	10.3	99-1/8x32-13/16x5-3/4	140
HUTM3672	10.4	75-1/8x38-11/16x5-3/4	116