



Plastic Bottle, 16 fl. oz.
078698130521

Plastic Bottle, 5 gal.
078698130545

Plastic Bottle, 54 gal.
078698130552

WINDSHIELD WASHER SOLVENT WITH ANTI-FREEZE

M516, M540, M549

All season formula cleans car windshields year round. Cleans off bugs and road grime leaving your windshield crystal clear.

APPLICATIONS:

- Cleans Off Smears And Bugs
- Streak Free Formula with Ammonia
- Helps Prevent Fluid From Freezing, Protects Down to -30°F

DIRECTIONS: DILUTE IN ACCORDANCE WITH ALL LOCAL, STATE, AND FEDERAL VOLATILE ORGANIC CONTENT (VOC) REGULATIONS. 1) THIS IS A DILUTABLE CONCENTRATE; DO NOT USE WITHOUT PROPER DILUTION. DILUTE ONLY WITH CLEAN WATER. VOC BEFORE DILUTION IS 48% BY WEIGHT. 2) DILUTION RATIOS FOR MOST REGULATED AREAS ARE LISTED IN THE TABLE BELOW:

Dilution Ratio (Water: Conc.)	Amount Water	Amount of Concentrate	Resulting VOC Level	Freeze Protection To:
48:1 (A)	6 gallons	16 fl oz	Less than 1%	32°F
8:1 (B)	1 gallon	16 fl oz	Less than 6%	32°F
6:1 (C)	3 quarts	16 fl oz	Less than 8%	20°F
1.5:1 (D)	24 fl oz	16 fl oz	Less than 21%	5°F
1:1 (E)	16 fl oz	16 fl oz	Less than 25%	-5°F
1:4 (F)	8 fl oz	32 fl oz	Less than 40%	-30°F

(A) Minimum dilution that complies with regulations in all areas of California.

(B) Summer dilution FOR UNREGULATED AREAS ONLY.

(C) Minimum dilution that complies with Georgia regulations for Atlanta and surrounding counties

(D) Minimum dilution that complies with Texas regulations.

(E) Minimum dilution that complies with California regulations for use where freezing conditions exist (Type A areas).

(F) A winter dilution FOR UNREGULATED AREAS ONLY.

NOTE: Certain areas in California where freezing weather occurs (type A areas) can use up to, but not more concentrated, than a 1:1 dilution with water. These areas include Del Norte, Shasta, and Trinity Counties; the Great Basin Valley, Lake Tahoe, Mountain Counties, and Northeast Plateau Air Basins as defined in Title 17, California Code of Regulations.

FOR TEMPERATURES CONSISTENTLY ABOVE 32°F, USE GUNK® WINDSHIELD WASHER SOLVENT WITH AMMONIA, PART NUMBER M506.

A concentrated formula specially designed to protect windshield washer systems from damage caused by temperatures as low as -30°F. A superior solvent for cleaning windshields in any season of the year. Will not harm rubber, metal or painted surfaces when used according to instructions.

NOTE: Undiluted concentrate may attack paint. If accidentally spilled on painted surfaces, immediately wash off with water.

STORAGE, HANDLING & DISPOSAL: Dispose of product, container and residue in accordance with all local, state, and federal regulations.

DANGER: POISON. Cannot be made non-poisonous. FLAMMABLE. DO NOT USE NEAR HEAT, SPARKS, OR FLAME.

CONTINUED ON BACK

NOTICE: While this information is presented in good faith and believed to be accurate, Radiator Specialty Company does not guarantee satisfactory results from reliance thereon. The data is offered solely for your information and Radiator Specialty Company disclaims all liability for any loss or damage from its use. Thoroughly test any application according to the product directions and independently conclude satisfactory performance. Nothing contained herein is to be construed as a recommendation to use the product in violation of any patent.

WINDSHIELD WASHER SOLVENT WITH ANTI-FREEZE

M516, M540, M549

FIRST AID: EYE CONTACT: Flush thoroughly with water for 15 minutes while occasionally lifting eyelids and get prompt medical attention. SKIN CONTACT: Wash thoroughly with soap and water. If irritation develops, get prompt medical attention. INHALATION: Vapor harmful. Move to fresh air. If breathing becomes difficult, get prompt medical attention. INGESTION: If swallowed, do not induce vomiting. Call poison control center, physician, or hospital emergency room immediately.

KEEP AWAY FROM CHILDREN AND ANIMALS

WARNING: This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

PRODUCT INFORMATION SHEET — UPDATED 8/13/2013

NOTICE: While this information is presented in good faith and believed to be accurate, Radiator Specialty Company does not guarantee satisfactory results from reliance thereon. The data is offered solely for your information and Radiator Specialty Company disclaims all liability for any loss or damage from its use. Thoroughly test any application according to the product directions and independently conclude satisfactory performance. Nothing contained herein is to be construed as a recommendation to use the product in violation of any patent.

